



Test Report issued under
the responsibility of:



TEST REPORT
IEC 60950-1
Information technology equipment - Safety -
Part 1: General requirements

Report Reference No : E135494-A48-CB-3

Date of issue : 2015-03-20

Total number of pages : 84

CB Testing Laboratory : UL International Demko A/S

Address : Borupvang 5A, 2750 Ballerup, Denmark

Applicant's name : TDK-LAMBDA UK LTD

Address : KINGSLEY AVE

Address : ILFRACOMBE

Address : EX34 8ES UNITED KINGDOM

Test specification:

Standard : IEC 60950-1:2005 (Second Edition); Am1:2009 + Am2:2013

Test procedure : CB Scheme

Non-standard test method : N/A

Test Report Form No. : IEC60950_1F

Test Report Form originator : SGS Fimko Ltd

Master TRF : Dated 2014-02

Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.


This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.



If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer

The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test item description	Switch Mode Power Supply
Trade Mark	TDK-Lambda
	
Manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Model/Type reference	Alpha 600 series, CA600 series, Alpha 600W series, Alpha-600 series, CA-600 series
Ratings	Nominal Input Voltage Range: 100-240 Vac or 177-326 Vdc. 47-63Hz. 10A AC or 6A DC.
	Output: See Model Differences

Testing procedure and testing location:	
<input checked="" type="checkbox"/> CB Testing Laboratory	Testing location / address: UL International Demko A/S Borupvang 5A, 2750 Ballerup, Denmark
<input type="checkbox"/> Associated CB Test Laboratory	Testing location / address:
	Tested by (name + signature): Mike Burns 
	Approved by (name + signature).....: David Snook 
<input type="checkbox"/> Testing Procedure: TMP/CTF Stage 1	Testing location / address:
	Tested by (name + signature): _____
	Approved by (name + signature).....: _____
<input type="checkbox"/> Testing Procedure: WMT/CTF Stage 2	Testing location / address:
	Tested by (name + signature): _____
	Witnessed by (name + signature) ...: _____
	Approved by (name + signature).....: _____
<input type="checkbox"/> Testing Procedure: SMT/CTF Stage 3 or 4	Testing location / address:
	Tested by (name + signature): _____
	Approved by (name + signature).....: _____
	Supervised by (name + signature) .: _____
<input type="checkbox"/> Testing Procedure: RMT	Testing location / address:
	Tested by (name + signature): _____
	Approved by (name + signature).....: _____
	Supervised by (name + signature) .: _____

List of Attachments
National Differences (50 pages)
Enclosures (104 pages)
Summary of Testing:
All Applicable tests according to the referenced standard(s) have been carried out
Summary of Compliance with National Differences:
Countries outside the CB Scheme membership may also accept this report.

List of countries addressed: AR, AT, AU, BE, BG, BY, CA, CH, CS, CZ, DE, DK, ES, EU, FI, FR, GB, GR, HU, IE, IL, IN, IT, JP, KR, MY, NL, NO, NZ, PL, PT, RO, SA, SE, SI, SK, UA, US, ZA

The product fulfills the requirements of: CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10, UL 60950-1 2nd Ed, 2014-10-14, EN 60950-1:2006 + A11:2009 + A12:2011 + A1:2010 + A2:2013

Copy of Marking Plate

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.



Test item particulars :	
Equipment mobility	for building-in
Connection to the mains	no direct connection to the mains
Operating condition	continuous
Access location	not accessible
Over voltage category (OVC)	OVC II
Mains supply tolerance (%) or absolute mains supply values	90 - 264VAC max; 160 - 358VDC max
Tested for IT power systems	Yes, Norway only
IT testing, phase-phase voltage (V)	230V
Class of equipment	Class I (earthed)
Considered current rating of protective device as part of the building installation (A)	20A
Pollution degree (PD)	PD 2
IP protection class	IP X0
Altitude of operation (m)	3000
Altitude of test laboratory (m)	64m
Mass of equipment (kg)	2.5kg
Possible test case verdicts:	
- test case does not apply to the test object	N / A
- test object does meet the requirement	P(Pass)
- test object does not meet the requirement	F(Fail)
Testing:	
Date(s) of receipt of test item	2010-08-18, 2012-10-28
Date(s) of Performance of tests	2012-11-08
General remarks:	
<p>"(see Enclosure #)" refers to additional information appended to the report. "(see appended table)" refers to a table appended to the report.</p> <p>Throughout this report a point is used as the decimal separator.</p>	
Manufacturer's Declaration per Sub Clause 4.2.5 of IEC60950-1:	
Yes	
<p>The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided</p> <p>When differences exist, they shall be identified in the General Product Information section.</p>	
Name and address of Factory(ies):	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM

PANYU TRIO MICROTRONIC CO LTD
SHIJI INDUSTRIAL ESTATE
DONGYONG
NANSHA
GUANGZHOU GUANGDONG, CHINA

GENERAL PRODUCT INFORMATION:

Report Summary

All applicable tests according to the referenced standard(s) have been carried out.

Product Description

Switch Mode power supply for installation within end equipment. A range of output modules can be mounted in 5 available slots. The primary sub-assembly, including the primary windings of the main barrier transformer, is common to all products in this family. The secondary regulators are built into separate modules and have flexible secondary windings attached to them.

Model Differences

Alpha 600 is identical to CA 600, Alpha-600, CA-600 and Alpha 600W.

(may be prefixed by NS - # / or - where # may be up to any four letters and may be followed by - \$; where \$ may be any number between 000 to 999, indicating non-safety related model differences.)

Alpha 600 may be followed by: A, TL, RL, LL or ML

Where:

A = Class A input filter (Class B fitted as standard)

TL = Tiny leakage input filter

RL = Reduced leakage input filter

LL = Low leakage input filter

ML = Medium leakage input filter

may be followed by: LSF, RA or QF

Where:

LSF = Low speed fan

RA = Reverse air fan

QF = Quiet fan option

@ followed by AA, A, AL, BB, B, CC, C, CL, CM, CH, DD, D, FF, F, GG, G, JJ, J, KK, K, LL, L, MM, M, NN, N, QQ, Q, RR, R, SS, S, TT, T, UU, U, WW, W, ZZ or Z.

or B/S

optionally followed by _MF, MFE, MFU, MFV or _MFV, _PA, _IN, _PP, _RP, RPA, RPB, RPC, RPD, _D or _MG

@/@ (Where / may be replaced with _) followed by: E, EB, EQ, EL, EH, H, P or PL:

Where @ and @/@ = applicable voltage range and the following one or two letters are the module type.

Secondary Options:

_MF, MFE = Mains fail option (may also be called X).

MFU = Mains fail option with uncommitted output connections.

MFV = Mains fail option with VME bus

_PA, _PP, _IN, _RP, RPA, RPB, RPC, RPD, _D and _MG = Secondary module options. (Note: The RPA option can only be used on modules with output voltages rated up to 32V. The RP, RPB, RPC and RPD options can only be used on modules with output voltages rated up to 16V. Not for use with a module voltage range of 18-29V or twin output modules.)

B/S = Blanking slot which occupies one 23mm slot.

Only up to five 23mm slots may be filled up per unit, noting that all modules occupy one 23mm slot except for AA, A, F, FF, G, J, K, R, S and T modules which occupy two 23mm slots.

Valid voltage ranges for @ and @/@ for each module are as follows:

AA @ = 4.5-7V, G, GG @ = 17.5 - 29V
A @ = 4.5-6V, H @/@ = 18 - 32V / 18 - 32V
AL @ = 4.75-5.3V, J, JJ @ = 30 - 48V
BB @ = 4.5-7V, K, KK @ = 18 - 31V
B @ = 4.5-6V, L, LL @ = 1.8 - 3.2V
C, CC @ = 5-16V, M, MM @ = 5 - 16V
CL @ = 4.6-5.6V, N, NN @ = 18 - 32V
CM @ = 5-7V, P @/@ = 18 - 29V / 5 - 16V
CH @ = 11.4-13.5V, PL @ = 22 - 26 / 5 - 7V
D, DD @ = 18-29V, Q, QQ @ = 2.7 - 3.9V
E @/@ = 5-16V / 5-16V, R, RR @ = 2.7 - 3.9V
EB @/@ = 4.5-5.5V / 4.5-5.5V, S, SS @ = 1 - 5.7V
EQ @/@ = 4.5-5.5V / 2.7-3.9V, T, TT @ = 1.8 - 3.2V
EL @ = 5 -7V / 11-13V, U, UU @ = 10 - 21V
EH @ = 11-13V / 11-13V, W, WW @ = 4.5 - 5.5V
F, FF @ = 9-16V, Z, ZZ @ = 4.5 - 5.7V

Additional module limitations:

Notes:

- 1) For C, CH, modules the max output current is 12A for voltages > 12V.
- 2) For E, EH, EL modules the max output current is limited to 7A in slot 3 and 6A in Slot 4.
- 3) For H modules the max output current is limited to 4A in slot 4. For voltages >29V, the output current is limited to 1A
- 4) For P, PL modules the max output current is limited to 5A for channel 1 and for channel 2, 8A in slot 1, 7A in slots 2, 3 and 5, and 6A in slot 4.
- 5) For J modules output current derates by 0.25A per volt above 40V.
- 6) N modules with output voltage greater than 29V have max output current of 1 Amp.
- 7) For S modules the max output current is limited to 75A in slots 2 & 3, 77A in slots 3 & 4, & 80A in slots 4 & 5.
- 8) When using remote sense, the max output voltage will be reduced by 0.5V for L, S, T, Q and R modules, and by 1.0V for C, CH, CL, CM, D, F, G, J, M, K, N, U modules.
- 9) Ampere turns for J module is calculated as $AT = (\text{output current} + 15A) \times 4$.
- 10) For L modules the max. output current is limited to 20A in slot 5.
- 11) Adjusting output voltage beyond the stated range may cause overvoltage protection (OVP) to operate, whereby all outputs will turn off. To reset OVP, turn back the output voltage adjustment and remove the mains supply for 30 seconds and then switch back on.

Unit limitations:

- i) For PSUs fitted with RA option (reverse air flow), the output is limited to 475W and 100AT at a max ambient of 40°C, or 400W, 85AT for a max ambient of 50°C (horizontal only). Operation in any vertical position is not permitted.
- ii) For PSUs fitted with the LSF option, the output is limited to 400W and 88.9AT. The QF option is limited to 600W and 120AT.
- iii) For power supplies having input or output connector housings fitted there is no effect on ratings in any

orientation.

Adjustment and Derating.

The Alpha 600 series is designed to provide a maximum output power of 600W at nominal output voltages. The following procedure must be used to ensure the PSU is operated within its ratings:

- a) Calculate user power for each module (volts x amps).
- b) Add all the individual module powers together. The total power must not exceed the power rating of the converter, 600W.
- c) Calculate secondary transformer turns x amps or each module see outputs table for transformer secondary turns.
- d) Add all the module turns x amps together and this must not exceed 120AT.
- e) If necessary reduce the loading until the conditions are met. i.e. power and ampere-turns maxima.

SELV and Outputs Connected In Series:

- Outputs can be connected in series thus producing non-SELV levels, or in parallel thus producing new energy hazards, and this must be taken into account in the end-use application. When non-seriesed outputs are earthed in the end use equipment they are SELV. If the outputs are not earthed they must be considered hazardous, as a single fault in the secondary may make them exceed the SELV limits between output and earth. If any output is non-SELV then all outputs become non-SELV.
- All outputs have operational spacing to earth, and due consideration must be given to this in the end product design.

Custom Model:

Model: CA600 18G (NS-WAK-001)

Input voltage range: 90-264Vac

Outputs 18V 25A (450W, 100AT total)

Ambient 50°C max

Orientations All except psu vertical with airflow downwards and psu upside down

Model NS-WAK-001 is identical to Model Alpha 600 18G.

Both Models are identical to the standard product, except they may be fitted with a Papst 612NGM fan.

Input Connections:

Input tabs- 6.3mm x 0.8mm, tin plated brass, rated 15A.

Output Connections:

Output Connector Ratings:

1) 6.35mm fastons are rated at 15A.

2) 9.5mm Faston terminals are rated at 32A (tab thickness = 1.0mm, suitable Faston terminals are AMP 151667-2 or AMP 280223-2)

3) M5 screw terminals are rated at 100A subject to the wire and wire connector used to connect them.

Maximum recommended torque setting for M5 screws is 2.5 - 3.0Nm.

Additional Information

This report, to include IEC60950-1 Amd 2:2013, is a reissue of CBTR Ref. No.: E135494-A48-CB-2 dated 2012-11-19 including CB Test Certificate Ref. No. DK-29306-UL dated 2012-11-19. Based on previously conducted testing and the review/update of product technical documentation including photos, schematics, wiring diagrams and similar, it has been determined that the product continues to comply with the standard.

No testing was deemed necessary to include the following changes, assessment to 60950-1 Am 2:2013, addition/deletion and correction to the CCL and update of component licenses

The original testing was carried out on the basis of 5 slots being filled, each slot being one 23mm module space wide. This is the maximum number of module slots allowed under this approval, and provides the worst case situation. Heating tests were carried out with the maximum number of slots filled, but with numerous loading conditions to cover any condition of loading in any slot position. Also, the models tested under Clause 4.5 represent the least efficient, highest current module configurations. Abnormals were carried out on the expected worst case situation for that abnormal, and on as many configurations as considered necessary to represent the entire range of products covered by this approval. For the other tests, the conditions and configurations used were the expected worst case.

These products use optional coatings which are normally applied with a brush and are used within the primary area of the power supply on limited surface therefore deemed as non-safety critical. The coatings are not used for any safety purpose although they improve dielectric strength.

Technical Considerations

- Clearances and Creepage Distances have additionally been assessed for suitability up to 3000 m elevation. --
- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of: 50°C --
- The product is intended for use on the following power systems: TN --
- The equipment disconnect device is considered to be: to be provided in end product --
- The following were investigated as part of the protective earthing/bonding: Printed wiring board trace (refer to Enclosure - Schematics + PWB for layouts) --
- The means of connection to the mains supply is: to be provided in end product --
- The product was investigated to the following additional standards: CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10, UL 60950-1 2nd Ed, 2014-10-14, EN 60950-1:2006 + A11:2009 + A12:2011 + A1:2010 + A2:2013 (which includes all European national differences, including those specified in this test report). --

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- These products were considered to be a component part of a larger piece of Class 1 equipment. Full compliance with the standards will therefore depend on the installation in the final application. Some modules could present an energy hazard. Additionally, outputs can be connected in series thus producing non-SELV levels, or in parallel thus producing new energy hazards, and this must be taken into account in the end-use application. When non-series outputs are earthed in the end use equipment they are SELV. If the outputs are not earthed they must be considered hazardous, as a single fault in the secondary may make them exceed the SELV limits between output and earth. If any output is non-SELV then all outputs become non-SELV. --
- These units are internally forced-air cooled. They require a minimum of 50mm clearance in the vicinity of the ventilation holes. Whilst relatively orientation insensitive, operation of the these units when mounted vertically with the air flow in a downward direction is affected by convection acting against the cooling airflow, and results in slightly hotter temperatures (2 to 5 degrees) than if operated in the horizontal position. As a consequence of this, heating tests were carried out in the vertical orientation with airflow downwards to give the worst case temperatures, unless otherwise stated. No additional air flow during tests was applied, only the internal fans were used. --

- Additional requirement may apply if product used in end application in Restricted Access Location --
- Consideration should be given to measuring the temperatures on power electronic components and transformer windings, when the power supply is installed in the end-use equipment. --
- The following Production-Line tests are conducted for this product: Earthing Continuity , Electric Strength --
- The end-product Electric Strength Test is to be based upon a maximum working voltage of: Primary-SELV: 406 Vrms, 728 Vpk , Primary-Earthed Dead Metal: 380 Vrms, 412 Vpk --
- The power supply terminals and/or connectors are: Suitable for factory wiring only --
- The maximum investigated branch circuit rating is: 20 A --
- The investigated Pollution Degree is: 2 --
- Proper bonding to the end-product main protective earthing termination is: Required. --
- An investigation of the protective bonding terminals has: Not been conducted --
- The following input terminals/connectors must be connected to the end-product supply neutral: input terminal marked "N" --
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY3 insulation system with the indicated rating greater than Class A (105°C): T203 (Class F) --
- The following end-product enclosures are required: Mechanical , Fire , Electrical --
- The following output terminals were referenced to earth during performance testing: For output SELV testing, the positive and negative outputs in turn were connected to earth. , --
- The following secondary output circuits are at hazardous energy levels: All --
- Fans: The fan provided in this sub-assembly is provided with a fan guard to reduce the risk of operator contact with the fan blades. Further evaluation shall be considered in the end product. --
- The following secondary output circuits are at hazardous energy levels: modules A, AA, AL, C, CC, CH, D, DD, F, FF, G, GG, J, JJ, K, KK, R, RR, S, SS, T, TT, U and UU --
- The following secondary output circuits are at non-hazardous energy levels: modules B, BB, CL, CM, E, EB, EH, EL, EQ, H, L, LL, M, MN, N, NN, P, PL, Q, QQ, W, WW, Z and ZZ --

Abbreviations used in the report:

- normal condition	N.C.	- single fault condition	S.F.C
- operational insulation	OP	- basic insulation	BI
- basic insulation between parts of opposite polarity:	BOP	- supplementary insulation	SI
- double insulation	DI	- reinforced insulation	RI

Indicate used abbreviations (if any)