

# Certificate



Certificate no.

TA 50373180 01

**License Holder:**

TDK-Lambda Americas Inc.  
401 Mile of Cars Way, Suite 325,  
National City, CA 91950  
USA

**Manufacturing Plant:**

ZTW1-LinPr-10049856 001

**Test report no.:** ZTW1-SCL 10049856 001

**Client Reference:** RD06-13022017-Co.TDK

**Tested to:** IEC 60601-1:2005+A1  
EN 60601-1:2006+A11+A1+A12

**Certified Product:** (Switching Power Supply)

**License Fee - Units**

Type Designation	: CSS65A-XZZZZZ (TDK-Lambda)	5
X stands for	: 5, 12, 15, 19, 24, 28, 48, 54	1
Z stands for	: a-z, A-Z, 0-9	1
Rated Voltage	: AC 100-240V, 50-60Hz	
Rated Current	: 2-1A	
Output Voltage	: see Appendix	
Output Current	: see Appendix	
max. Ambient Temperature:	50°C	
Protection Class	: I	

Remark: 1. This risk management requirements of the standard were not addressed.  
2. This certificate is valid for maximum 5 years.

7


**Licensed Test mark:**



**TÜV Rheinland Taiwan Ltd**

Signature

Dipl.-Ing. W. Hsu



**Date of Issue**  
(day/mo/yr)

07/03/2017

Appendix to TÜV approved Certificate No.: TA 50373180

**Certified Product** : Switching Power Supply  
**Report Number** : 10049856 001  
**Type Designation** : CSS65A-XZZZZZ  
 (X = 5, 12, 15, 19, 24, 28, 48, 54; Z = a-z, A-Z, 0-9)

Model name	Output rating		
	V	A	W
CSS65A-5ZZZZZ	+5	8	40
CSS65A-12ZZZZZ	+12	5.42	65
CSS65A-15ZZZZZ	+15	4.34	65
CSS65A-19ZZZZZ	+19	3.43	65
CSS65A-24ZZZZZ	+24	2.71	65
CSS65A-28ZZZZZ	+28	2.33	65
CSS65A-48ZZZZZ	+48	1.36	65
CSS65A-54ZZZZZ	+54	1.21	65

Date: 7<sup>th</sup> March, 2017

Certification Body

*W. Hsu*  
Dipl.-Ing. W. Hsu

