

UL TEST REPORT AND PROCEDURE

Standard:	UL 62368-1, 2nd Ed, 2014-12-01 (Audio/video, information and communication technology equipment Part 1: Safety requirements) CAN/CSA C22.2 No. 62368-1-14, 2nd Ed-(Audio/video, information and communication technology equipment Part 1: Safety requirements)
Certification Type:	Component Recognition
CCN:	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
Complementary CCN:	N/A
Product:	Switching Power Supply
Model:	CUS350M-zxxxxxxx, CME350A-zxxxxxxx (z = 12, 18, 24, 36 or 48; xxxxxxx = F, FN, PG, 2, F2, PG2, A, S**, FET, FGE, LN, 0-9, a-z, A-Z, other alphanumeric character, symbol or blank)
Rating:	See the model list on enclosure 7-01 for details
Applicant Name and Address:	TDK-LAMBDA (CHINA) ELECTRONICS CO LTD NO.95,ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028 CHINA

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared By: Star Gu / Project Handler

Reviewed By: Jie Qian / Reviewer

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
- i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The EUTs are a component type switching mode power supplies intended for the class I construction of information technology equipment.

Model Differences

Model CME350A-zzxxxxxxx is identical to model CUS350M-zzxxxxxxx except for model name.

All models are identical, except of the turns of Transformer and the rating of some components that results in different output ratings.

See Enclosed Miscellaneous 7-01 (Model Different List) for details.

Test Item Particulars

Classification of use by	Ordinary person; Instructed person; Skilled person
Supply Connection	AC Mains
Supply % Tolerance	+10%/-10%
Supply Connection – Type	mating connector
Considered current rating of protective device as part of building or equipment installation	20 A; building;
Equipment mobility	for building-in
Over voltage category (OVC)	OVC II
Class of equipment	Class I
Access location	restricted access area
Pollution degree (PD)	PD 2
Manufacturer's specified maximum operating ambient (°C)	up to +70°C (operating temperature depending on equipment's load, mounting position, Refer to Enclosure 6-01 for details).
IP protection class	IPX0
Power Systems	TN
Altitude during operation (m)	5000 m
Altitude of test laboratory (m)	2000 m or less
Mass of equipment (kg)	Approx. 0.8

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer's specification of : up to +70°C (operating temperature depending on equipment's load, mounting position, Refer to Enclosure 6-01 for details).
- The product is intended for use on the following power systems : TN
- Considered current rating of protective device as part of the building installation (A) : 20
- Mains supply tolerance (%) or absolute mains supply values : +10%/-10%
- The Risk Group of a lamp or lamp system (including LEDs) is : Exempt
- The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual
- The product can be operated sea level up to 5000 m; the minimum clearance multiplied by the factor given in Table A.2 of IEC 60664-1: 1.48.
- The input circuit includes one fuse (F1A) in the Line conductor and the other fuse (F1B) is optional in neutral conductor. Overall consideration need to re-checked in the end-use product regarding addition of the second fuse having the same or better characteristics in order to comply with fusing requirements of Clause 8.11.5 of the standard.

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following product-line tests are conducted for this product : Earthing Continuity, Electric Strength
- The end-product Electric Strength Test is to be based upon a maximum working voltage of : T1: Primary-Earthed Dead Metal: 340 Vrms, 640 Vpk, Primary-Secondary: 340 Vrms, 640 Vpk, , T2: Primary-Earthed Dead Metal: 250 Vrms, 567 Vpk, Primary-Secondary: 250 Vrms, 567 Vpk
- The following output circuits are at ES1 energy levels : All output
- The following output circuits are at PS3 energy levels : All output
- The maximum investigated branch circuit rating is : 20 A
- The investigated Pollution Degree is : 2
- Proper bonding to the end-product main protective earthing termination is : Required
- An investigation of the protective bonding terminals has : been conducted
- The following input terminals/connectors must be connected to the end-product supply neutral : N
- The following end-product enclosures are required : Mechanical, Electrical, Fire
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C) : T1 (Class B), T2 (Class F).
- The equipment is suitable for direct connection to : AC mains supply
- The power supply was evaluated to be used at altitudes up to : "5,000 m"
- LIMITED SHORT-CIRCUIT TEST (Annex R) is to be evaluated in end products.

Additional Information

N/A

Additional Standards

The product fulfills the requirements of: N/A

Markings and Instructions

Clause Title	Marking or Instruction Details
Equipment identification marking – Manufacturer identification	Listee's or Recognized companys name, Trade Name, Trademark or File Number

Equipment identification marking – model identification	Model Number
Equipment rating marking – ratings	"Input Ratings (voltage, frequency/dc, current/power)", "Output Ratings (voltage, frequency/dc, current/power)"
Fuses – replaceable by skilled person	(component ID: __F1A/F1B __), '250V, T6.3AH' located on or adjacent to fuse or fuse holder or in service manual.
Special Instructions to UL Representative Inspect the transformer(s) listed in table "Electric Strength Test Special Constructions" per BD1.1: When the tests are conducted at other location, inspect test record and specification sheet provided by the component manufacturer. Verify the specification sheet indicates 100% routine test specified in the table be conducted at the component manufacturer.	

Definition of variable(s):
 CUS350M-zxxxxxxx
 (z = 12, 18, 24 or 48; xxxxxx = F, FN, PG, 2, F2, PG2, A, S**, FGE, FGE, LN, 0-9, a-z, A-Z, other alphanumeric character, symbol or blank)
 Note: Suffix options would be used shown below or used together.

Variable:	Range of variable:	Content:
z	12, 18, 24, 36 or 48	Denotes for different output voltage.
Xxxxxx x	F	Denotes for full function.
	FN	Denotes for fan power terminal.
	PG	Denotes for power good.
	2	Denotes for PWB coating.
	F2	Denotes for full function and PWB coating.
	PG2	Denotes for power good and PWB coating.
	A	Denotes for this model with metal cover.
	S**	Denotes for special modified model, not affect safety.
	FET	Denotes for full function and add M3 mounting holes on chassis.
	FGE	Denotes for full function and Voltage Dip Improvement.
	LN	Denotes for Reduce audio noise.
0-9, a-z, A-Z, other alphanumeric character, symbol or blank	Denotes for market purposes, no construction differences and no safety impact.	
blank	Denotes for standard type.	

Series Model	I/p voltage (Vac)	Freq. (Hz)	I/p current (A)	Minimal output	Rated output (typical)	Maximum output	
						Vo_max1	Vo_max2
For convection cooling							
CUS350M-12xxxxxxx CME350A-12xxxxxxx	100-240	50-60	4.0	11.1 Vdc	12.0 Vdc	12.6 Vdc	13.2 Vdc
				29 A	29 A	27.6 A	24 A
CUS350M-18xxxxxxx CME350A-18xxxxxxx	100-240	50-60	4.0	16.6 Vdc	18.0 Vdc	18.9 Vdc	19.8 Vdc
				19.4 A	19.4 A	18.5 A	16.1 A
CUS350M-24xxxxxxx CME350A-24xxxxxxx	100-240	50-60	4.0	22.1 Vdc	24.0 Vdc	25.2 Vdc	28.3 Vdc
				14.7 A	14.7 A	14 A	11.3 A
CUS350M-36xxxxxxx CME350A-36xxxxxxx	100-240	50-60	4.0	33.1 Vdc	36.0 Vdc	37.8 Vdc	39.6 Vdc
				9.7A	9.7A	9.2A	8.1 A
CUS350M-48xxxxxxx CME350A-48xxxxxxx	100-240	50-60	4.0	44.2 Vdc	48.0 Vdc	50.4 Vdc	52.8 Vdc
				7.3 A	7.3 A	7.0 A	6.1 A
For force air cooling							

CUS350M-12xxxxxxx CME350A-12xxxxxxx	100-240	50-60	4.5	11.1 Vdc	12.0 Vdc	12.6 Vdc	13.2 Vdc
				34.5A	34.5A	32.8A	24 A
CUS350M-18xxxxxxx CME350A-18xxxxxxx	100-240	50-60	4.5	16.6 Vdc	18.0 Vdc	18.9 Vdc	19.8 Vdc
				23A	23A	21.9A	16.1 A
CUS350M-24xxxxxxx CME350A-24xxxxxxx	100-240	50-60	4.5	22.1 Vdc	24.0 Vdc	25.2 Vdc	28.3 Vdc
				17.5A	17.5A	16.6A	11.3 A
CUS350M-36xxxxxxx CME350A-36xxxxxxx	100-240	50-60	4.5	33.1 Vd.c.	36.0 Vdc	37.8 Vdc	39.6 Vdc
				11.5A	11.5A	10.9A	8.1 A
CUS350M-48xxxxxxx CME350A-48xxxxxxx	100-240	50-60	4.5	44.2 Vdc	48.0 Vdc	50.4 Vdc	52.8 Vdc
				8.7A	8.7A	8.3A	6.1 A