

UL TEST REPORT AND PROCEDURE

Standard:	UL 62368-1, 2nd Ed, 2014-12-01 (Audio/video, information and communication technology equipment Part 1: Safety requirements) CAN/CSA C22.2 No. 62368-1-14, 2nd Ed-(Audio/video, information and communication technology equipment Part 1: Safety requirements)
Certification Type:	Component Recognition
CCN:	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
Complementary CCN:	N/A
Product:	Switching Power Supply
Model:	CUS60M-zzxxxxxxx; CME60A-zzxxxxxxx (zz = 5,12,15,18,24,36 or 48; xxxxxxx = A, U, ADJ, M, CO, SF, P or other alphanumeric character)
Rating:	Input: 100-240 Vac, 1.4A, 50-60Hz Output: See the model list in enclosure 7-01 for details
Applicant Name and Address:	TDK-LAMBDA (CHINA) ELECTRONICS CO LTD NO.95,ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028 CHINA

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared By: Star Gu / Project Handler

Reviewed By: Jie Qian / Reviewer

Copyright © 2019

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
 - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The EUT is component type switching mode power supply, which intended for the earthed construction or non-earthed IT equipment in the scope of this standard.

- For earthed construction (Class I), the SMPS need to be reliably earthed and professionally installed and fixed with metal screws.
- For non-earthed construction (Class II), no earthing connection is required. The SMPS need to be fixed so, that it is insulated from any unearthed accessible conductive part by reinforced insulation.

Model Differences

Model CME60A-zzxxxxxxx is identical to model CUS60M-zzxxxxxxx, except for model designation.

All models are identical, except of the optional chassis, cover, turns of Transformer and the rating of some components which results in different output ratings. See Enclosed Miscellaneous 7-01 (Model Different List) for details.

Test Item Particulars

Classification of use by	Ordinary person; Instructed person; Skilled person
Supply Connection	AC Mains
Supply % Tolerance	+10%/-10%
Supply Connection – Type	mating connector
Considered current rating of protective device as part of building or equipment installation	20 A; building;
Equipment mobility	for building-in
Over voltage category (OVC)	OVC II
Class of equipment	Not classified
Access location	restricted access area
Pollution degree (PD)	PD 2
Manufacturer's specified maximum operating ambient (°C)	up to +70°C (operating temperature depending on equipment's load, mounting position, Refer to Enclosure 6-01 and 6-02 for details).
IP protection class	IPX0
Power Systems	TN
Altitude during operation (m)	5000 m
Altitude of test laboratory (m)	2000 m or less

Mass of equipment (kg)	Approx. 0.23kg (with chassis and cover); Approx. 0.14kg (without chassis and cover)
------------------------	---

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer’s specification of : up to +70°C (operating temperature depending on equipment’s load, mounting position, Refer to Enclosure 6-01 and 6-02 for details).
- The product is intended for use on the following power systems : TN
- Considered current rating of protective device as part of the building installation (A) : 20
- Mains supply tolerance (%) or absolute mains supply values : +10%/-10%
- The Risk Group of a lamp or lamp system (including LEDs) is : Exempt
- The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual
- The product can be operated sea level up to 5000 m; the minimum clearance multiplied by the factor given in Table A.2 of IEC 60664-1: 1.48.
- The input circuit includes one fuse (F1A) in the Line conductor and the other fuse (F1B) is optional in neutral conductor. Overall consideration need to re-checked in the end-use product regarding addition of the second fuse having the same or better characteristics in order to comply with fusing requirements of Clause 8.11.5 of the standard.
- The metal enclosure of Class II equipment need to evaluate by end system.

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following product-line tests are conducted for this product : Earthing Continuity, Electric Strength
- The end-product Electric Strength Test is to be based upon a maximum working voltage of : Primary-Earthed Dead Metal: 274 Vrms, 521 Vpk, Primary-Secondary: 274Vrms, 521Vpk
- The following output circuits are at ES1 energy levels : All output
- The following output circuits are at PS2 energy levels : All output
- The maximum investigated branch circuit rating is : 20 A
- The investigated Pollution Degree is : 2
- Proper bonding to the end-product main protective earthing termination is : Required
- An investigation of the protective bonding terminals has : been conducted
- The following input terminals/connectors must be connected to the end-product supply neutral : N
- The following end-product enclosures are required : Mechanical, Electrical, Fire
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C) : T1 (Class F).
- The equipment is suitable for direct connection to : AC mains supply
- The power supply was evaluated to be used at altitudes up to : "5,000 m"
- LIMITED SHORT-CIRCUIT TEST (Annex R) is to be evaluated in end products.

Additional Information

N/A

Additional Standards

The product fulfills the requirements of: N/A

Markings and Instructions

Clause Title	Marking or Instruction Details
--------------	--------------------------------

Equipment identification marking – Manufacturer identification	Listee's or Recognized companys name, Trade Name, Trademark or File Number
Equipment identification marking – model identification	Model Number
Equipment rating marking – ratings	"Input Ratings (voltage, frequency/dc, current/power)", "Output Ratings (voltage, frequency/dc, current/power)"
Fuses – replaceable by skilled person	(component ID: __F1A/F1B __), '250V, T2.0AH' located on or adjacent to fuse or fuse holder or in service manual.
Special Instructions to UL Representative Inspect the transformer(s) listed in table "Electric Strength Test Special Constructions" per BD1.1: When the tests are conducted at other location, inspect test record and specification sheet provided by the component manufacturer. Verify the specification sheet indicates 100% routine test specified in the table be conducted at the component manufacturer.	

Definition of variable(s):
 CUS60M-zzxxxxxxx; CME60A-zzxxxxxxx (zz = 5, 12,15,18,24,36 or 48; xxxxxxx = A, U, ADJ, M, CO, SF, P or other alphanumeric character)
 Note: Suffix options would be used shown below or used together.

Variable:	Range of variable:	Content:
zz	5, 12, 15, 18, 24, 36 or 48	Denotes for output voltage
xxxxxxx	A	Denotes for chassis & cover
	U	Denotes for U shape chassis
	ADJ	Denotes for output adjust
	M	Denotes for Molex connector
	CO	Denotes for PWB coating
	SF	Denotes for single fuse
	P	Denotes for solderable copper pins type.
	other alphanumeric character	For market purposes, no construction differences and no safety impact.

For rating differences between the models see below tables:

Series Model	I/p voltage (Vac)	Freq (Hz)	I/p current (A)	Minimal output	Rated output (typical)	Maximum output
CUS60M-5 xxxxxxx CME60A-5 xxxxxxx	100-240	50-60	1.0	4.85Vdc	5Vdc	5.15Vdc
				6A	6A	5.83A
CUS60M-12 xxxxxxx CME60A-12 xxxxxxx	100-240	50-60	1.4	11.7Vdc	12Vdc	12.3Vdc
				5A	5A	4.88A
CUS60M-15 xxxxxxx CME60A-15 xxxxxxx	100-240	50-60	1.4	14.625Vdc	15Vdc	15.375Vdc
				4A	4A	3.9A
CUS60M-18 xxxxxxx CME60A-18 xxxxxxx	100-240	50-60	1.4	17.55Vdc	18Vdc	18.45Vdc
				3.35A	3.35A	3.27A
CUS60M-24 xxxxxxx CME60A-24 xxxxxxx	100-240	50-60	1.4	23.4Vdc	24Vdc	24.6Vdc
				2.5A	2.5A	2.44A
CUS60M-36 xxxxxxx CME60A-36 xxxxxxx	100-240	50-60	1.4	35.1Vdc	36Vdc	36.9Vdc
				1.68A	1.68A	1.64A
CUS60M-48 xxxxxxx CME60A-48 xxxxxxx	100-240	50-60	1.4	46.8Vdc	48Vdc	49.2Vdc
				1.25A	1.25A	1.22A
	100-240	50-60	1.4	4.5Vdc	5Vdc	5.5Vdc

CUS60M-5/ADJ CME60A-5/ADJ				6A	6A	5.45A
CUS60M-12/ADJ CME60A-12/ADJ	100-240	50-60	1.4	10.8Vdc	12Vdc	13.2Vdc
				5A	5A	4.55A
CUS60M-15/ADJ CME60A-15/ADJ	100-240	50-60	1.4	13.5Vdc	15Vdc	16.5Vdc
				4A	4A	3.64A
CUS60M-18/ADJ CME60A-18ADJ	100-240	50-60	1.4	16.2Vdc	18Vdc	19.8Vdc
				3.35A	3.35A	3.05A
CUS60M-24/ADJ CME60A-24/ADJ	100-240	50-60	1.4	21.6Vdc	24Vdc	26.4Vdc
				2.5A	2.5A	2.27A
CUS60M-36/ADJ CME60A-36/ADJ	100-240	50-60	1.4	32.4Vdc	36Vdc	39.6Vdc
				1.68A	1.68A	1.53A
CUS60M-48/ADJ CME60A-48/ADJ	100-240	50-60	1.4	43.2Vdc	48Vdc	52.8Vdc
				1.25A	1.25A	1.14A
Remark: Operating temp.: up to +70°C (operating temperature depending on equipment's load, mounting position, for details refer to instruction manual).						