Test Report issued under the responsibility of:

TEST REPORT

IEC 60950-1
Information technology equipment – Safety – Part 1: General requirements

Report Number. .....:	E135494-A6031-CB-1
Date of issue .....:	2020-03-27
Total number of pages.....	55
Name of Testing Laboratory preparing the Report .....:	UL International Polska Sp. z o.o. Aleja Krakowska 81, 05-090 Sekocin Nowy, Poland
Applicant's name .....:	TDK-LAMBDA UK LTD
Address .....:	KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM
Test specification:	
Standard.....:	IEC 60950-1:2005, AMD1:2009, AMD2:2013
Test procedure .....:	CB Scheme
Non-standard test method .....:	N/A
Test Report Form No. .....:	IEC60950_1G
Test Report Form(s) Originator ....:	SGS Fimko Ltd
Master TRF.....:	Dated 2019-07-02

Copyright © 2019 IEC System of Conformity Assessment Schemes for Electrotechnical Equipment and Components (IECEE System). All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer:

The test results presented in this report relate only to the object tested.
This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test item description ..... :	AC-DC Power Supply
Trade Mark ..... :	TDK-Lambda
Manufacturer ..... :	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM
Model/Type reference ..... :	Model/type reference: DRB120-XX-1/yyy (where XX can be 12 or 48 for the output voltage and yyy is optional and can be alphanumeric characters or blank and is for non-safety related changes - product ratings unchanged)
Ratings ..... :	Input: 100-240 VAC, 1.5 A, 50/60 Hz Output DRB120-12-1: Rated: 12-13.2 Vdc, 10-9.09 A Peak: 12-13.2 Vdc, 12-10.9 A, Max 10sec. Output DRB120-48-1: Rated: 48-52.8 Vdc, 2.5-2.27 A Peak: 48-52.8 Vdc, 3-2.72 A, Max 10sec.

Responsible Testing Laboratory (as applicable), testing procedure and testing location(s):

☒	**CB Testing Laboratory:**		
Testing location/ address.....:		UL International Polska Sp. z o.o., Aleja Krakowska 81, 05-090 Sekocin Nowy, Poland	
Tested by (name, function, signature).....:		Hubert Koszewski / Project Handler	
Approved by (name, function, signature)...:		Dennis Butcher / Reviewer	
☐	**Testing procedure: CTF Stage 1:**		
Testing location/ address.....:			
Tested by (name, function, signature).....:			
Approved by (name, function, signature)...:			
☐	**Testing procedure: CTF Stage 2:**		
Testing location/ address.....:			

Tested by (name + signature) .....:		
Witnessed by (name, function, signature) .:		
Approved by (name, function, signature)...:		
☐ **Testing procedure: CTF Stage 3:**		
☐ **Testing procedure: CTF Stage 4:**		
Testing location/ address.....:		
Tested by (name, function, signature).....:		
Witnessed by (name, function, signature) .:		
Approved by (name, function, signature)...:		
Supervised by (name, function, signature) :		