



Ref. Certif. No.

DK-125971-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Power Circuit and Motor-mounted Apparatus, Switching Power Supply
Name and address of the applicant	NEXTYS SA Via Luserte sud 6 Quartino 6572 Switzerland
Name and address of the manufacturer	NEXTYS SA Via Luserte sud 6 Quartino 6572 Switzerland
Name and address of the factory	TDK-LAMBDA MALAYSIA SDN BHD LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING KUANTAN, PAHANG, 26070 Malaysia <input type="checkbox"/> Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	DRB120-12-3-XX: Input: 3~400-500Vac, 3x0.5A, 50-60Hz, three phases, Output Nominal: 11.4-15.0Vdc, 10-8A, Output Maximum: 11.4-15.0Vdc, 12.-9.6A <2s. <input checked="" type="checkbox"/> Additional Information on page 2
Trademark (if any)	
Customer's Testing Facility (CTF) Stage used	CTF Stage 2
Model / Type Ref.	DRB120-12-3-XX, DRB120-24-3-XX, DRB240-24-3-XX, DRB240-36-3-XX, DRB240-48-3-XX <input checked="" type="checkbox"/> Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to: EN 61010-1:2010, EN 61010-1:2010/A1:2019 National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61010-1:2010, IEC 61010-1:2010/AMD1:2016, IEC 61010-2-201:2017
As shown in the Test Report Ref. No. which forms part of this Certificate	22-4789227120.3-CB-Reissue-1 issued on 2022-03-02

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2022-04-05

Signature: Jan-Erik Storgaard



Ref. Certif. No.

DK-125971-UL

Additional Model Detail(s):

DRB120-12-3-XX, DRB120-24-3-XX, DRB240-24-3-XX, DRB240-36-3-XX, DRB240-48-3-XX, where XX can be any character or symbol for marketing purposes only with no effect on safety

Additional Ratings:

DRB120-24-3-XX: Input: 3~400-500Vac, 3x0.5A, 50-60Hz, three phases, Output Nominal: 22.5-29.0Vdc, 5-4.1A, Output Maximum: 22.5-29.0Vdc, 6-4.9A <2s

DRB240-24-3-XX:

Input: 3~400-500Vac, 3x0.8A, 50-60Hz, three phases
Output Nominal: 22.5-29.0Vdc, 10-8.2A
Output Maximum: 22.5-29.0Vdc, 12-9.9A <2s

DRB240-36-3-XX:

Input: 3~400-500Vac, 3x0.8A, 50-60Hz, three phases
Output Nominal: 32.0-42.0Vdc, 6.6-5.7A
Output Maximum: 32.0-42.0Vdc, 8-6.9A <2s

DRB240-48-3-XX:

Input: 3~400-500Vac, 3x0.8A, 50-60Hz, three phases
Output Nominal: 45.0-56.0Vdc, 5-4.2A
Output Maximum: 45.0-56.0Vdc, 6-5.1A <2s

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2022-04-05

Signature:

Jan-Erik Storgaard