

File E362999

Project 4789261373

April 21, 2020

REPORT

On

Power Circuit and Motor-mounted Apparatus

TDK-Lambda UK Ltd  
ILFRACOMBE, EX34 8ES UNITED KINGDOM

Copyright © 2020 UL LLC

UL LLC authorizes the above named company to reproduce this Report only for purposes as described in the Conclusion, provided it is reproduced in its entirety.

## DESCRIPTION

## PRODUCT COVERED:

USL/CNL - Open type, Switching Mode Power Supply, Models DRB240-48-1, may be followed by "-", "/" or any alphanumeric characters, may be followed by CO, CO2 or any alphanumeric characters.

## GENERAL:

These devices are open type, switching type power supply modules intended for din rail mounting and to be used in combination with Industrial Control Equipment. The output circuit is isolated from the primary circuit by a switch mode design transformer and optical isolators. These devices are suitable for field wiring and for use in a pollution degree 2 environment / controlled environment.

## ELECTRICAL RATINGS:

Series	Load Condition	Input Ratings	Output Ratings
DRB240-48-1	Normal (#1)	100-240 Vac, 2.7 A, 50/60Hz	48-52.8 Vdc, 5-4.55A, Max. 240 W
	Peak Output (#2)	100-240 Vac, 3.2 A, 50/60Hz	48-52.8 Vdc, 6-5.45A

## Note:

#1 - The derating curve explaining the characteristics between the permissible load and the surrounding air temperature shown in ILL. 10 is the part of the Output ratings.

#2 - The peak output ratings which allow to consume variable output current value up to 6 A, the first up to 10 seconds with the Duty cycle of 35%.

## ENVIRONMENTAL RATINGS:

Max Surrounding Air Temperature: 70°C (#3)

Pollution Degree: 2

## Note:

#3 - The permissible max. surrounding air temperature rating is specified in the derating curve related to the permissible load and the mounting orientation, shown in ILL. 10.

Above 55°C the output is derated linearly to 50% power at 70°C

## NOMENCLATURE:

Example: DRB240-48-1/wxyz

DRB	240	-	48	-	1
I	II		III		IV

I - Product Series Name  
DRB : Block Terminal type

II - Output Power  
240: 240 Watts

III - Output Voltage  
48: 48-52.8 Vdc

IV - Phase  
1: Single

Where w, x, y, z are considered as non-safety related information:  
w can be '-' or '/' or blank or any alphanumeric;  
x can be CO or CO2 or blank or any alphanumeric  
y can be blank or any alphanumeric  
z can be blank or any alphanumeric