

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	DIN Rail Power Supply
Name and address of the applicant	TDK-Lambda UK Ltd. Kingsley Avenue, Ilfracombe, Devon, EX34 8ES, United Kingdom
Name and address of the manufacturer	TDK-Lambda UK Ltd. Kingsley Avenue, Ilfracombe, Devon, EX34 8ES, United Kingdom
Name and address of the factory	TDK-Lambda Malaysia SDN. BHD. Lots 2&3 Kawasan Perindustrian Bandar Baru Jaya Gading, Kuantan MY-26070, Pahang Darul Makmur, Malaysia
<i>Note: When more than one factory, please report on page 2</i>	<input type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See page 2.
Trademark (if any)	TDK-Lambda
Customer's Testing Facility (CTF) Stage used	/
Model / Type Ref.	DRF480-24-1-xyz; DRF480-24-1/HL-xyz; DRF480-24-1/HLIVS (Where x, y and z can be any alphanumeric character or blank and is non safety related information.) HL – designates model provided with coating.
Additional information (if necessary may also be reported on page 2)	Unit also complies with EN 60950-1:2006 + A1:2010 + A2:2013 + A11:2009 + A12:2011 <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60950-1:2005 (2 nd Edition) + A1:2009 + A2:2013
As shown in the Test Report Ref. No. which forms part of this Certificate	T223-0265/17


This CB Test Certificate is issued by the National Certification Body

SIQ Ljubljana, Tržaška cesta 2, SI-1000 Ljubljana, Slovenia
T +386 1 4778 100, F +386 1 4778 444, info@siq.si, www.siq.si

SIQ Ljubljana is accredited by Slovenian Accreditation with accreditation number CP-001 in the field of certification of products, processes and services.

Date: 2017-06-28

Signature: Bojan Pečavar



Ratings and principal characteristics:

DRF480-24-1-xyz and DRF480-24-1/HL-xyz:

Input: 100-240 Vac; 5,4 A; 50/60 Hz

Output: 24-28 Vdc / 20-15,4 A; Max. output power: 480 W

DRF480-24-1/HLIVS:

Input: 100-240 Vac / 108-145 Vdc; 5,4 A; 50/60 Hz

Output: 24 Vdc; 20 A; Max. output power: 480 W

Additional information (if necessary)

This CB Test Certificate substitute previously issued CB Test Certificate No. SI-5558, dated 2017-01-17 due to update of the test report.

Date: 2017-06-28

Signature: Bojan Pečavar

