

UL TEST REPORT AND PROCEDURE

Standard:	UL 62368-1, 2nd Ed, 2014-12-01 (Audio/video, information and communication technology equipment Part 1: Safety requirements) CAN/CSA C22.2 No. 62368-1-14, 2nd Ed, Issued: 2014-12-01 (Audio/video, information and communication technology equipment Part 1: Safety requirements)
Certification Type:	Component Recognition
CCN:	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
Complementary CCN:	N/A
Product:	DIN-rail mounted 3-phase SMPS
Model:	DRBxxx-yy-3-zz (see model differences)
Rating:	Input: DRB120-yy-3-zz: 3~ 400-500 V; 50/60 Hz; 3x0.5 A DRB240-yy-3-zz: 3~ 400-500 V; 50/60 Hz; 3x0.8 A
Applicant Name and Address:	NEXTYS SA VIA LUSERTE 6 6572 QUARTINO SWITZERLAND

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared By: Oreste Buzzetti / Handler

Reviewed By: Isaia Bonavoglia / Reviewer

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

A. Authorization - The Authorization page may include additional Factory Identification Code markings.

B. Generic Inspection Instructions -

- i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
- ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
- iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

Product under evaluation is a series of DIN-rail mounted 3-phase SMPS

Model Differences

All models differ for output power and voltage. Transformers are different for each family.

Nomenclature:

xxx = output power in watts (120 or 240)

yy = output voltage in volts (12 or 24 for 120 series; 24 or 36 or 48 for 240 series)

zz = any character or symbol for marketing purposes only with no effect on safety or blank.

Test Item Particulars

Classification of use by	Instructed person
Supply Connection	AC Mains
Supply % Tolerance	Other + 10 % / - 12.5 %
Supply Connection – Type	permanent connection
Considered current rating of protective device as part of building or equipment installation	20 A; building;
Equipment mobility	for building-in
Over voltage category (OVC)	OVC II
Class of equipment	Class I
Access location	restricted access area
Pollution degree (PD)	PD 2
Manufacturer's specified maximum operating ambient (°C)	55
IP protection class	IPX0
Power Systems	TN TT
Altitude during operation (m)	3000 m
Altitude of test laboratory (m)	2000 m or less
Mass of equipment (kg)	0.5

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer’s specification of : 55°C
- The product is intended for use on the following power systems : TT, TN
- Considered current rating of protective device as part of the building installation (A) : 20
- Mains supply tolerance (%) or absolute mains supply values : +10%/ -12.5%
- The equipment disconnect device is considered to be : To be provided in final installation
- The following were investigated as part of the protective earthing/bonding : Printed wiring board trace (refer to Enclosure - Schematics + PWB for layouts)
- The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual
- The following scope limitations apply to this test report and additional evaluation and/or tests may be required when submitting this CB Report to a National Certification Body (NCB) to obtain a national mark:
 - No EMC tests nor evaluation to EMC Directive 2004/108/EC and 2014/30/EU
 - No evaluation to RoHS Directives 2002/95/EC, 2011/65/EU and (EU) 2016/585
 - No evaluation to Council Recommendation 1999/519/EC nor 2006/25/EC
 - Only English version of markings and instructions provided and reviewed
- Products supplied with tri-phase voltage of 400-500 V between phases and 230-290 V between each phase and earth.

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following product-line tests are conducted for this product : Electric Strength, Earthing Continuity
- The end-product Electric Strength Test is to be based upon a maximum working voltage of : Primary-Secondary: 276 Vrms/816 Vpk (Model DRB120-12), Primary-Secondary: 292 Vrms/752 Vpk (Model DRB120-24), Primary-Secondary: 294 Vrms/952 Vpk (Model DRB240-24), Primary-Secondary: 307 Vrms/912 Vpk (Model DRB240-36), Primary-Secondary: 309 Vrms/896 Vpk (Model DRB240-48)
- The following output circuits are at ES1 energy levels : All outputs of all models
- The following output circuits are at PS3 energy levels : All outputs of all models
- The maximum investigated branch circuit rating is : 20 A
- The investigated Pollution Degree is : 2
- Proper bonding to the end-product main protective earthing termination is : Required
- An investigation of the protective bonding terminals has : been conducted
- The following end-product enclosures are required : Electrical, Fire, Mechanical
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C) : Transformers of all models (TR1 or TR3) are Class B (130°C)
- The equipment is suitable for direct connection to : 3-Phase AC mains supply
- The power supply was evaluated to be used at altitudes up to : "3,000 m"
- Safeguards against capacitor discharge after disconnection of a connector shall be checked in final installation.

Additional Information


-

Additional Standards

The product fulfills the requirements of: EN 62368-1:2014 + A11:2017

Markings and Instructions

Clause Title	Marking or Instruction Details
--------------	--------------------------------

Equipment identification marking – Manufacturer identification	Listee's or Recognized companys name, Trade Name, Trademark or File Number
Equipment identification marking – model identification	Model Number
Equipment rating marking – ratings	"Input Ratings (voltage, frequency/dc, current/power)", "Output Ratings (voltage, frequency/dc, current/power)"
Class I equipment -Terminal for main protective earthing	Provided adjacent to the main protective earthing terminal  (IEC 60417-5019)
Restricted Access Area	"Equipment is intended for installation in Restricted Access Area" (Instruction)/"Les matériels sont destinés à être installés dans des EMPLACEMENTS À ACCÈS RESTREINT" (Instruction)
Disconnect device - Permanently connected equipment	Statement indicating that an appropriate disconnect device shall be incorporated in the building installation wiring. (Instruction)
Special Instructions to UL Representative N/A	

BD1.0	TABLE: Production-Line Testing Requirements					
BD1.1	Electric Strength Test Special Constructions – Refer to Generic Inspection Instructions, Part AC for further information.					
Model	Component	Removable parts	Test probe location	Test V rms	Test V dc	Test Time, s
DRB120-12	Input connector	-	Output connector	-	5350	1
DRB120-24	Input connector	-	Output connector	-	5350	1
DRB240-24	Input connector	-	Output connector	-	5350	1
DRB24036	Input connector	-	Output connector	-	5350	1
DRB240-48	Input connector	-	Output connector	-	5350	1
BD1.2	Earthing Continuity Test Exemptions – This test is not required for the following models:					
	-					
BD1.3	Electric Strength Test Exemptions – This test is not required for the following models:					
	-					
BD1.4	Electric Strength Test Component Exemptions – The following solid-state components may be disconnected from the remainder of the circuitry during the performance of this test.					
	-					

BE1.0	Sample and Test Specifics for Follow-Up Tests at UL				
Model	Component	Material	Test	Sample (s)	Test Specifics
-	-	-	-	-	-