



Test Report issued under the responsibility of:



TEST REPORT
IEC 61010-1
Safety requirements for electrical equipment for measurement, control, and laboratory use
Part 1: General requirements

Report Number.....: 22-4789227120.6
Date of issue.....: 2022-04-01
Total number of pages.....: 166 plus Annexes

Name of Testing Laboratory preparing the Report.....: UL International Germany GmbH

Applicant's name: NEXTYS SA
Address: Via Luserte sud 6, 6572, Quartino, SWITZERLAND

Test specification:
Standard.....: IEC 61010-1:2010, IEC 61010-1:2010/AMD1:2016
Test procedure: CB Scheme
Non-standard test method: N/A

TRF template used: IECEE OD-2020-F1:2020, Ed.1.3
Test Report Form No.: IEC61010_1P
Test Report Form(s) Originator: VDE Prüf- und Zertifizierungsinstitut GmbH
Master TRF.....: 2021-04-12

Copyright © 2021 IEC System of Conformity Assessment Schemes for Electrotechnical Equipment and Components (IECEE System). All rights reserved.


This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.




If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.



This report is not valid as a CB Test Report unless signed by an approved IECEE Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer:

The test results presented in this report relate only to the object tested.
This report shall not be reproduced, except in full, without the written approval of the Issuing NCB. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test item description :	Power Circuit and Motor-mounted Apparatus, Switching Power Supply
Trade Mark :	
Manufacturer	NEXTYS SA, Via Luserte sud 6, 6572, Quartino, SWITZERLAND
Model/Type reference :	DRB480-24-3-XX, DRB480-48-3-XX, DRB480-72-3-XX where XX can be any character or symbol for marketing purposes only with no effect on safety.
Ratings :	<p>DRB480-24-3-XX: Input: 3~400-500Vac / 50-60Hz / 3x1.2A Output Nominal: 480W / 22.5-29Vdc / 20-16.4A</p> <p>DRB480-48-3-XX: Input: 3~400-500Vac / 50-60Hz / 3x1.2A Output Nominal: 480W / 45-56Vdc / 10-8.5A</p> <p>DRB480-72-3-XX: Input: 3~400-500Vac / 50-60Hz / 3x1.2A Output Nominal: 480W / 70-85Vdc / 6.7-5.6A</p>

Responsible Testing Laboratory (as applicable), testing procedure and testing location(s):		
<input checked="" type="checkbox"/>	CB Testing Laboratory:	UL International Germany GmbH
Testing location/ address		Admiral-Rosendahl-Strasse 23, Zeppelinheim 63263 Neu-Isenburg , Germany
Tested by (name, function, signature) :		Ugo Romano (Project handler) 
Approved by (name, function, signature) .. :		Lee Berrecloth (Project Reviewer) 
<input type="checkbox"/>	Testing procedure: CTF Stage 1:	
Testing location/ address		
Tested by (name, function, signature) :		
Approved by (name, function, signature) .. :		
<input checked="" type="checkbox"/>	Testing procedure: CTF Stage 2:	
Testing location/ address		NEXTYS SA, Via Luserte sud 6, 6572, Quartino, SWITZERLAND
Tested by (name + signature) :		Stefano Ferreira (Test handler) 

Witnessed by (name, function, signature) . :		Ugo Romano (Project handler)	
Approved by (name, function, signature) .. :		Lee Berrecloth (Project Reviewer)	
<input type="checkbox"/>	Testing procedure: CTF Stage 3:		
<input type="checkbox"/>	Testing procedure: CTF Stage 4:		
Testing location/ address :			
Tested by (name, function, signature)..... :			
Witnessed by (name, function, signature) . :			
Approved by (name, function, signature) .. :			
Supervised by (name, function, signature) :			

List of Attachments (including a total number of pages in each attachment)		
Document No.	Documents included / attached to this report (description)	Page No.
I	Photographs	4
II	Diagrams + PWB	36
III	Miscellaneous	77
IV	Manuals	6
V	Front and lateral label	5
VI	Particular Standard – (IEC61010_2_201)	31
VII	US National Deviations	7
VIII	CA National Deviations	18
IX	EU National Deviations	1

Documents referenced by this report (available on request):		
Document Name or No.	Documents description	Page No.
N/A		

Summary of testing:	
Clause	Comment
Clause 4.4 - Single Fault Condition Tests	N/A
Clause 4.4.1 - Component Abnormal	
Clause 4.4.2.7.2 - Mains Transformer Short Circuit Test	
Clause 4.4.2.7.3 - Mains Transformer Overload Test	
Clause 4.4.2.8 - Output Abnormal Test	
Clause 5.1.3 - Mains Supply	
Clause 6.2 - Determination Of Accessible Parts	
Clause 6.5.2.5 - Grounding Continuity Test	
Clause 6.7 and Annex K - Insulation Requirements	
Clause 6.8 - Dielectric Voltage Withstand Test	
Clause 6.8.2 - Humidity conditioning test	
Clause 9.4 - Limited Energy Circuit Determination Test	
Clause 10.1-10.4 - Temperature Test	

Test Report History:	
This report may consist of more than one report and is only valid with additional or previous issued reports:	
Report Ref. No.	Item
N/A	
Tests performed (name of test and test clause):	Testing location:
Clause 4.4 - Single Fault Condition Tests Clause 4.4.1 - Component Abnormal Clause 4.4.2.7.2 - Mains Transformer Short Circuit Test Clause 4.4.2.7.3 - Mains Transformer Overload Test Clause 4.4.2.8 - Output Abnormal Test Clause 5.1.3 - Mains Supply Clause 6.2 - Determination Of Accessible Parts Clause 6.5.2.5 - Grounding Continuity Test Clause 6.7 and Annex K - Insulation Requirements Clause 6.8 - Dielectric Voltage Withstand Test Clause 6.8.2 - Humidity conditioning test Clause 9.4 - Limited Energy Circuit Determination Test Clause 10.1-10.4 - Temperature Test	CTF Stage 2: NEXTYS SA Via Luserte sud 6, 6572, Quartino, SWITZERLAND
Summary of compliance with National Differences (List of countries addressed):	
AT, BE, BG, HR, CY, CZ, DK, EE, EU, FI, FR, DE, GR, HU, IS, IE, IT, LV, LT, LU, MT, NL, NO, PL, RO, SK, SI, ES, SE, CH, GB Austria, Belgium, Bulgaria, Croatia, Cyprus, The Czech Republic, Denmark, Estonia, Finland, France, Germany, Greece, Hungary, Iceland, Ireland, Italy, Latvia, Lithuania, Luxembourg, Malta, The Netherlands, Norway, Poland, Portugal, Romania, Slovakia, Slovenia, Spain, Swedem, Switzerland, The United Kingdom	
<input checked="" type="checkbox"/> The product fulfils the requirements of IEC 61010-2:201, 2nd edition, UL 61010-2-201, 2nd edition, CSA 61010-2-201, 2nd edition, EN 61010-1:2010/A1:2019 (Edition 3.1) No more evaluation for UL 61010-2-201, 2nd edition, CSA 61010-2-201, 2nd edition,	

Statement concerning the uncertainty of the measurement systems used for the tests

(may be required by the product standard or client)

Internal procedure used for type testing through which traceability of the measuring uncertainty has been established:

Procedure number, issue date and title:









Calculations leading to the reported values are on file with the NCB and testing laboratory that conducted the testing.

Statement not required by the standard used for type testing

(Note: When IEC or ISO standard requires a statement concerning the uncertainty of the measurement systems used for tests, this should be reported above. The informative text in parenthesis should be delete in both cases after selecting the applicable option)

Copy of marking plate:

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.

<p>TDK-Lambda</p>  <p>Read the operating manual! Lisez le manuel d'utilisation!</p> <p>Surrounding Air Temperature: -25..70°C (-13..158°F) Wiring must be ≥ 90°C (194°F) rated Température de l'environnement: -25..70°C Le câblage doit être ≥ 90°C nominale</p> <p>EU representative: TDK-Lambda Germany GmbH Karl-Bold-Str. 40 77855 Achern DE</p> <p>UK representative: TDK-Lambda UK Ltd. Kingsley Avenue Ilfracombe, Devon EX34 8ES UK</p> <p>www.emea.lambda.tdk.com</p>	<p>DRB480-24-3-A0</p>  <p>DIN-Rail power supply</p> <p>INPUT 3~ 400-500V / 50-60Hz / 3x1.2A</p> <p>OUTPUT 480W / 22.5-29V=== / 20-16.4A</p> <p>Operating temperature -25..70°C (-13..158°F) derating from 55°C (131°F)</p> <p>203NRM 0001 P401 Rev. C02 Fact. ID: P</p> <p>CE UK CA IECEE CB SCHEME 10</p> <p>UL LISTED E336563 IND.CONTEQ</p> <p>UL US C RA US EAC</p> <p>Designed in Switzerland Made in Malaysia</p>	<p>TDK-Lambda</p>  <p>Read the operating manual! Lisez le manuel d'utilisation!</p> <p>Surrounding Air Temperature: -25..70°C (-13..158°F) Wiring must be ≥ 90°C (194°F) rated Température de l'environnement: -25..70°C Le câblage doit être ≥ 90°C nominale</p> <p>EU representative: TDK-Lambda Germany GmbH Karl-Bold-Str. 40 77855 Achern DE</p> <p>UK representative: TDK-Lambda UK Ltd. Kingsley Avenue Ilfracombe, Devon EX34 8ES UK</p> <p>www.emea.lambda.tdk.com</p>	<p>DRB480-48-3-A0</p>  <p>DIN-Rail power supply</p> <p>INPUT 3~ 400-500V / 50-60Hz / 3x1.2A</p> <p>OUTPUT 480W / 45-56V=== / 10-8.5A</p> <p>Operating temperature -25..70°C (-13..158°F) derating from 55°C (131°F)</p> <p>203NRM 0001 P401 Rev. C02 Fact. ID: P</p> <p>CE UK CA IECEE CB SCHEME 10</p> <p>UL LISTED E336563 IND.CONTEQ</p> <p>UL US C RA US EAC</p> <p>Designed in Switzerland Made in Malaysia</p>
<p>TDK-Lambda</p>  <p>Read the operating manual! Lisez le manuel d'utilisation!</p> <p>Surrounding Air Temperature: -25..70°C (-13..158°F) Wiring must be ≥ 90°C (194°F) rated Température de l'environnement: -25..70°C Le câblage doit être ≥ 90°C nominale</p> <p>EU representative: TDK-Lambda Germany GmbH Karl-Bold-Str. 40 77855 Achern DE</p> <p>UK representative: TDK-Lambda UK Ltd. Kingsley Avenue Ilfracombe, Devon EX34 8ES UK</p> <p>www.emea.lambda.tdk.com</p>	<p>DRB480-72-3-A0</p>  <p>DIN-Rail power supply</p> <p>INPUT 3~ 400-500V / 50-60Hz / 3x1.2A</p> <p>OUTPUT 480W / 70-85V=== / 6.7-5.6A</p> <p>Operating temperature -25..70°C (-13..158°F) derating from 55°C (131°F)</p> <p>203NRP 0001 P401 Rev. C02 Fact. ID: P</p> <p>CE UK CA IECEE CB SCHEME 10</p> <p>UL LISTED E336563 IND.CONTEQ</p> <p>UL US C RA US EAC</p> <p>Designed in Switzerland Made in Malaysia</p>	<p>TDK-Lambda</p>  <p>Read the operating manual! Lisez le manuel d'utilisation!</p> <p>Surrounding Air Temperature: -25..70°C (-13..158°F) Wiring must be ≥ 90°C (194°F) rated Température de l'environnement: -25..70°C Le câblage doit être ≥ 90°C nominale</p> <p>EU representative: TDK-Lambda Germany GmbH Karl-Bold-Str. 40 77855 Achern DE</p> <p>UK representative: TDK-Lambda UK Ltd. Kingsley Avenue Ilfracombe, Devon EX34 8ES UK</p> <p>www.emea.lambda.tdk.com</p>	<p>DRB480-48-3-A0</p>  <p>DIN-Rail power supply</p> <p>INPUT 3~ 400-500V / 50-60Hz / 3x1.2A</p> <p>OUTPUT 480W / 45-56V=== / 10-8.5A</p> <p>Operating temperature -25..70°C (-13..158°F) derating from 55°C (131°F)</p> <p>203NRM 0001 P401 Rev. C02 Fact. ID: P</p> <p>CE UK CA IECEE CB SCHEME 10</p> <p>UL LISTED E336563 IND.CONTEQ</p> <p>UL US C RA US EAC</p> <p>Designed in Switzerland Made in Malaysia</p>

Test item particulars:	
Type of item	Power supply unit
Description of equipment function.....	Open-type power supplies intended to be DIN-rail mounted inside an industrial Control Panel or similar Enclosure.
Connection to MAINS supply	Permanently connected equipment
Overvoltage category	II
POLLUTION DEGREE.....	2
Means of protection	Class I (PE connected)
Environmental conditions	Extended (Specify): -25 ÷ 70°C
For use in wet locations.....	No
Equipment mobility.....	Built-in
Operating conditions.....	Continuous
Overall size of equipment (W x D x H).....	65 x 149 x 129 mm
Mass of equipment (kg).....	Approx 1.05 kg
Marked degree of protection to IEC 60529	IP20
Possible test case verdicts:	
- Test case does not apply to the test object	N/A (Not Applicable)
- Test object does meet the requirement.....	P (Pass)
- Test object does not meet the requirement	F (Fail)
Testing:	
Date of receipt of test item.....	2021-11-29
Date (s) of performance of tests	2021-01-11 to 2022-02-03
General remarks:	
<p>The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the issuing testing laboratory. "(see ENCLOSURE #)" refers to additional information appended to the report. "(see Form A.xx)" refers to a Table appended to the report. Bottom lines for measurement Tables Forms A.xx are optional if used as record.</p>	
Throughout this report a <input type="checkbox"/> comma / <input checked="" type="checkbox"/> point is used as the decimal separator.	
Manufacturer's Declaration per sub-clause 4.2.5 of IEC 60335-1:	
The application for obtaining a CB Test Certificate includes more than one factory location and a declaration from the manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided.....	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> Not applicable
When differences exist; they shall be identified in the general product information section.	
Name and address of factory (ies)	TDK-LAMBDA MALAYSIA SDN BHD LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN PAHANG MALAYSIA

General product information and other remarks:

Description of unit:

Open-type power supplies intended to be DIN-rail mounted inside an industrial Control Panel or similar Enclosure.

The product was investigated to the following additional standards: IEC 61010-2-201, 2nd edition
UL 61010-2-201, 2nd edition
CSA 61010-2-201, 2nd edition
EN 61010-1:2010/A1:2019 (Edition 3.1)

Description of model differences:

All the models share the same metal frame, pwb and power supply ratings. Models differ for SMPS transformer (winding ratio), some internal components and output electrical rating.

Description of special features:

(HV circuits, high pressure systems etc.)

Auxiliary output rating (DC OK) – 1A at 24Vdc resistive

Auxiliary input rating (INHIBIT) – 10mA, 5÷30Vdc