



Ref. Certif. No.

SG PSB-IT-00111

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Power supply
(AC-DC Switching Power Supply)

Name and address of the applicant

TDK-Lambda Singapore Pte., Ltd.
1008
Toa Payoh North, #06-01/08 318996
SINGAPORE

Name and address of the manufacturer

TDK-Lambda Singapore Pte., Ltd.
1008, Toa Payoh North, #06-01/08 318996, SINGAPORE

Name and address of the factory

TDK-Lambda Malaysia Sdn.Bhd. Kuantan Plant
LOT 2&3, Kawasan Perindustrian, Bandar Baru Jaya Gading, 26070
Kuantan Pahang, MALAYSIA

Ratings and principal characteristics

Input voltage range: 100~240 Va.c.
Maximum continuous
input current: 2.7 Aa.c.
Rated input a.c. frequency: 50/60 Hz
Output voltage range: 24-28 Vd.c.
Maximum continuous
output current: 10 Ad.c.
Maximum continuous
output power: 240 W
Protective class: I
Operation temperature
range: -25~70°C

Trade mark

See page 2

Model/type Ref.

DRJ240-24-1xy, DRJ240-24-1/xy
[x = E or blank, where E is European terminal type,
blank is block terminal type,
y = CO or CO2 or blank, where CO is model with thin coating
(QMJU2) on one side of PWB, CO2 is model with thin coating
(QMJU2) on both sides of PWB, blank is model with no thin coating
(QMJU2)]A sample of the product was tested and found
to be in conformity with

IEC 62477-1:2012

as shown in the Test Report Ref. No.
which forms part of this certificate

085-180581501-000

This CB Test Certificate is issued by the National Certification Body

CBS 075029 0022 Rev. 00

Date, 2018-10-16

Page 1 of 2

(Frank Zhu)

TÜV SÜD PSB Pte Ltd • 1 Science Park Drive • Singapore 118221



PSB Singapore



Ref. Certif. No.

SG PSB-IT-00111

Trade mark (image)

TDK-Lambda

CBS 075029 0022 Rev. 00

Date, 2018-10-16

Page 2 of 2

TÜV SÜD PSB Pte Ltd • 1 Science Park Drive • Singapore 118221

(Frank Zhu)



PSB Singapore