




Ref. Certif. No.

DK-57566-A3-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	AC-DC Power Supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE, EX34 8ES United Kingdom
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE, EX34 8ES United Kingdom
Name and address of the factory <small>Note: When more than one factory, please report on page 2</small>	Panyu Trio Microtronics Co Ltd SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU, 511453 GUANGDONG China
Ratings and principal characteristics	See Page 2
Trademark / Brand (if any)	TDK-Lambda 
Type of Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	DRB480-24-1-xyz, DRB480-48-1-xyz See Page 2
Additional information (if necessary may also be reported on page 2)	The report was revised to include technical modifications <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60950-1:2005/AMD1:2009, IEC 60950-1:2005/AMD2:2013, IEC 60950-1:2005
As shown in the Test Report Ref. No. which forms part of this Certificate	E135494-A109-CB-1 issued on 2020-07-21

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-07-21
Original Issue Date: 2016-08-29

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-57566-A3-UL

Model Details:

DRB480-24-1-xyz, DRB480-48-1-xyz where x, y, z may be any letter or digit or blank, considered non safety relevant information, see test report model differences

Ratings:

INPUT:

100-240 Vac, 5.4A, 50/60 Hz

OUTPUT

DRB480-24:

24-26.4Vdc, 20-18.2A (max 480W)

DRB480-48:

48-52.8 Vdc, 10-9.09A (max 480W)

Additional Information:

Additionally evaluated to EN 60950-1: 2006 / A11: 2009 / A1: 2010 / A12: 2011 / A2:2013; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:

Critical Component List, clauses and national differences revised.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-07-21

Original Issue Date: 2016-08-29

Signature:

Jan-Erik Storgaard