

# Certificate



Certificate no.

TA 50364837 01

**License Holder:**

TDK-Lambda Americas Inc.  
401 Mile of Cars Way, Suite 325,  
National City, CA 91950  
USA

**Manufacturing Plant:**

ZTW1-LinPr-10052285 001

**Test report no.:** ZTW1-SCL 10052285 001

**Client Reference:** 2Co-license

**Tested to:**

IEC 60601-1:2005+A1  
EN 60601-1:2006+A11+A1+A12

**Certified Product:** AC Power Adapter

**License Fee - Units**

Type Designation	: DTM300PWXXD2-ZZZZZ (TDK-Lambda)	5
XXX stands for	: 120, 190, 240, 280, 480 or 540	1
Z stands for	: 0-9, A-Z or blank	1
Rated Voltage	: AC 100-240V, 50-60Hz	
Rated Current	: 3.3-1.4A	
Outputs	: see Appendix	
max. Power Output	: see Appendix	
max. Ambient Temperature:	: +40°C	
Protection Class	: II	

Remarks: 1. The risk management requirements of the standard were not addressed;  
2. This certificate is valid for maximum 5 years.

7

**Licensed Test mark:**



**TÜV Rheinland Taiwan Ltd**

Signature

**Date of Issue**  
(day/mo/yr)

22/11/2016



Dipl.-Ing. (FH) A. Klinker

Appendix to TÜV approved Certificate No.: TA 50364837

Certified Product : AC Power Adapter  
Report Number : 10052285 001  
Type Designation : DTM300PWXXXD2-ZZZZZ  
(XXX can be 120, 190, 240, 280, 480, or 540, Z can be 0- 9, A-Z or blank)

Model	Output voltage	Output current	Maximum Watt
DTM300PW120D2-ZZZZZ	+12V	25A	300W
DTM301PW190D2-ZZZZZ	+19V	15.79A	300W
DTM302PW240D2-ZZZZZ	+24V	12.5A	300W
DTM303PW280D2-ZZZZZ	+28V	10.71A	300W
DTM304PW480D2-ZZZZZ	+48V	6.25A	300W
DTM305PW540D2-ZZZZZ	+54V	5.56A	300W

Date: 22<sup>nd</sup> Nov., 2016



Certification Body



Dipl.-Ing. (FH) A. Klinker