



Test Report issued under the responsibility of:



TEST REPORT

IEC 62368-1

Audio/video, information and communication technology equipment

Part 1: Safety requirements

Report Number	E135494-A6042-CB-1
Date of issue.....	2020-04-30
Total number of pages	71

Applicant's name	TDK-LAMBDA UK LTD
Address	KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM

Name of Test Laboratory preparing the Report	UL International Polska Sp. z o.o. Aleja Krakowska 81, 05-090 Sekocin Nowy, Poland
--	---

Test specification:	
Standard	IEC 62368-1:2014 (Second Edition)
Test procedure	CB Scheme
Non-standard test method.....	N/A

Test Report Form No.	IEC62368_1B
Test Report Form(s) Originator	UL(US)
Master TRF.....	2014-03

Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.




This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer:

The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test Item description	:	AC-DC Power Supply	
Trade Mark	:	TDK Lambda 	
Manufacturer	:	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM	
Model/Type reference	:	DRF120-24-1-xyz, DRF120-24-1/HL-xyz, Where x, y and z can be any alphanumeric character or blank and is non safety related information. HL - designates model provided with coating.	
Ratings	:	I/P: 100-240 Vac; 1.5 A; 50/60 Hz O/P: 24-28 Vdc; 5-4.3 A Max. power 120W	
Testing procedure and testing location:			
<input checked="" type="checkbox"/>	CB Testing Laboratory:		
Testing location/ address	:	UL International Polska Sp. z o.o., Aleja Krakowska 81, 05-090 Sekocin Nowy, Poland	
Tested by (name + signature)	:	Piotr A. Bizunowicz / Project Handler	
Approved by (name + signature)	:	Hubert Koszewski / Reviewer	
<input type="checkbox"/>	Testing procedure: CTF Stage 1		
Testing location/ address	:		
Tested by (name + signature)	:		
Approved by (name + signature)	:		
<input type="checkbox"/>	Testing procedure: CTF Stage 2		
Testing location/ address	:		
Tested by (name + signature)	:		
Witnessed by (name + signature)	:		
Approved by (name + signature)	:		
<input type="checkbox"/>	Testing procedure: CTF Stage 3		

<input type="checkbox"/>	Testing procedure: CTF Stage 4		
Testing location/ address..... :			
Tested by (name + signature).....:			
Witnessed by (name + signature).....:			
Approved by (name + signature)			
Supervised by (name + signature)			

List of Attachments (including a total number of pages in each attachment):

National Differences (30 pages)
 Enclosures (39 pages)

Summary of testing:

Tests performed (name of test and test clause):

Testing Location:

CBTL: UL International Polska Sp. z o.o., Aleja Krakowska 81, 05-090 Sekocin Nowy, Poland

STEADY FORCE TEST, 30 N (4.4.4.2, ANNEX T.3)

See enclosure 7-05 for detail

CLASSIFICATION OF ELECTRICAL ENERGY SOURCES (5.2, 5.7)

See enclosure 7-05 for detail

TEST FOR HYGROSCOPIC MATERIALS (5.4.1.3)

See enclosure 7-05 for detail

MAXIMUM OPERATING TEMPERATURE FOR MATERIALS, COMPONENTS AND SYSTEMS (5.4.1.4, Annex B.2)

See enclosure 7-05 for detail

DETERMINATION OF WORKING VOLTAGE (5.4.1.8)

See enclosure 7-05 for detail

HUMIDITY CONDITIONING (5.4.8)

See enclosure 7-05 for detail

ELECTRIC STRENGTH TEST (5.4.9)

See enclosure 7-05 for detail

SAFEGUARDS AGAINST CAPACITOR DISCHARGE AFTER DISCONNECTION OF A CONNECTOR (5.5.2.2)

See enclosure 7-05 for detail

PROTECTIVE BONDING CONDUCTORS: LIMITED SHORT CIRCUIT TEST (5.6.4, Annex R)

See enclosure 7-05 for detail

RESISTANCE OF THE PROTECTIVE BONDING SYSTEM (5.6.6.2)

See enclosure 7-05 for detail

PROSPECTIVE TOUCH VOLTAGE AND TOUCH CURRENT MEASUREMENT (5.7)

See enclosure 7-05 for detail

INPUT TEST: SINGLE PHASE (B.2.5)

See enclosure 7-05 for detail

SIMULATED ABNORMAL OPERATING CONDITIONS (B.3)

See enclosure 7-05 for detail

SIMULATED SINGLE FAULT CONDITIONS (B.4)

See enclosure 7-05 for detail

TEST FOR THE PERMANENCE OF MARKINGS (ANNEX F.3.10)

See enclosure 7-05 for detail

TRANSFORMER OVERLOAD (ANNEX G.5.3.3)

See enclosure 7-05 for detail

LIMITED SHORT CIRCUIT TEST (ANNEX R.1, 5.6.4.1, 5.6.4.4, 5.6.5.1)

See enclosure 7-05 for detail

Summary of compliance with National Differences:

List of countries addressed: Australia / New Zealand, EU Group and National Differences, Japan, USA / Canada

EU Group and National Differences applies to CENELEC member countries: Austria , Belgium, Bulgaria, Croatia, Cyprus, the Czech Republic, Denmark, Estonia, Finland, France, Germany, Greece, Hungary, Iceland, Ireland, Italy, Latvia, Lithuania, Luxembourg, Malta, the Netherlands, Norway, Poland, Portugal, Republic of North Macedonia, Romania, Serbia, Slovakia, Slovenia, Spain, Sweden, Switzerland, Turkey and the United Kingdom

The product fulfils the requirements of: EN 62368-1:2014 + A11:2017

Copy of Marking Plate - Refer to Enclosure titled Marking Plate for copy.

TEST ITEM PARTICULARS:	
Classification of use by	Skilled person, Instructed person
Supply Connection	AC Mains
Supply % Tolerance	+10%/-10%
Supply Connection – Type	Unit for building in: to be determined in End Product
Considered current rating of protective device as part of building or equipment installation	20 A; building;
Equipment mobility	for building-in
Over voltage category (OVC)	OVC II
Class of equipment	Class I
Access location	n/a (for building-in)
Pollution degree (PD)	PD 2
Manufacturer’s specified maximum operating ambient (°C)	70
IP protection class	IPX0
Power Systems	TN TT IT - 230 V L-L
Altitude during operation (m)	3000 m
Altitude of test laboratory (m)	less than 2000 meters m
Mass of equipment (kg)	approx. 0.6 kg
POSSIBLE TEST CASE VERDICTS:	
- test case does not apply to the test object..... :	N/A
- test object does meet the requirement :	P (Pass)
- test object does not meet the requirement :	F (Fail)
TESTING:	
Date of receipt of test item..... :	2019-09-24, 2019-12-16
Date (s) of performance of tests..... :	2020-03-16, 2020-03-17
GENERAL REMARKS:	
<p>“(See Enclosure #)” refers to additional information appended to the report. “(See appended table)” refers to a table appended to the report.</p> <p>Throughout this report a <input type="checkbox"/> comma / <input checked="" type="checkbox"/> point is used as the decimal separator.</p>	
Manufacturer’s Declaration per sub-clause 4.2.5 of IEC 60335-1:	

The application for obtaining a CB Test Certificate includes more than one factory location and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided :	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> Not applicable
When differences exist; they shall be identified in the General product information section.	
Name and address of factory (ies) :	TDK-LAMBDA MALAYSIA SDN BHD LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN PAHANG MALAYSIA
GENERAL PRODUCT INFORMATION:	
Report Summary	
All applicable tests according to the referenced standard(s) have been carried out.	
Product Description	
The product is a switching power supply intended for building-in, mounting on DIN rail, provided with terminal blocks suitable for field wiring. Output voltage can be adjusted from 24V to 28V with total output power max. 120W.	
Model Differences	
DRF120-24-1-xyz, DRF120-24-1/HL-xyz represent family of same construction with no differences affecting safety, model with suffix HL designates version with coating.	
Additional application considerations – (Considerations used to test a component or sub-assembly) -	
Power supply has been additionally tested with duty cycle defined as peak output power 180 W for 4 seconds and resting time 7.3 seconds at 68.64 W load, which equals total rms power 120 W.	
Maximum Normal Load:	
A- 60°C: 24 Vdc / 5A; Max. output power: 120 W	
B- 60°C: 28 Vdc / 4.3 A; Max. output power: 120 W	
C- 70°C: 24 Vdc / 3.75 A; Max. output power: 90 W	
D- 65°C: 24 Vdc / 4.37A; Max. output power: 105 W	
E- 60°C: 24 Vdc; 7.5 A/4 sec./180 W, 2.86 A/7.43 sec./68.64 W;	
This report is based on previously conducted testing (as listed below) and the review of product construction of original report E135494-A95-UL last revised 2016-01-21.	
Refer to Section “Test performed (name of test and test clause)” and enclosure 7-05 covering all applicable performance tests and rationale for waived tests.	

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of : 70 °C with derating of 2.5%/°C between 60 and 70 °C.
- The product is intended for use on the following power systems : TT, TN, IT
- Considered current rating of protective device as part of the building installation (A) : 20
- Mains supply tolerance (%) or absolute mains supply values : +10%/-10%
- The equipment disconnect device is considered to be : part of end product evaluation whether device or installation instructions are provided
- The following were investigated as part of the protective earthing/bonding : Printed wiring board trace (refer to Enclosure - Schematics + PWB for layouts)
- The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual
- The product was investigated to the following additional standard : EN 62368-1:2014 + A11:2017
- The following scope limitations apply to this test report and are confirmed by Applicant to be covered separately. Additional evaluation and/or tests may be required when submitting this CB Report to a National Certification Body (NCB) to obtain a national mark:
 - 1) no EMC tests nor evaluation to EMC Directive 2004/108/EC and 2014/30/EU,
 - 2) no evaluation to RoHS Directives 2002/95/EC, 2011/65/EU and (EU) 2016/585,
 - 3) no evaluation to Council Recommendation 1999/519/EC nor 2006/25/EC,
 - 4) only English version of markings and instructions provided and reviewed,
 - 5) no evaluation to Directive 96/29/Euratom.

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The following product-line tests are conducted for this product : Electric Strength, Earthing Continuity
- The end-product Electric Strength Test is to be based upon a maximum working voltage of : Primary-SELV: 427 Vrms, 880 Vpk, Primary-Earthed Dead Metal: 413 Vrms, 850 Vpk
- The following output circuits are at ES1 energy levels : Main output
- The following output circuits are at PS2 energy levels : Signal connector
- The following output circuits are at PS3 energy levels : main output
- The maximum investigated branch circuit rating is : 20 A
- The investigated Pollution Degree is : 2
- Proper bonding to the end-product main protective earthing termination is : Required
- An investigation of the protective bonding terminals has : Been conducted
- The following input terminals/connectors must be connected to the end-product supply neutral : pin2 of CN1 terminal block
- The following end-product enclosures are required : Mechanical, Fire, Electrical
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJ2 insulation system with the indicated rating greater than Class A (105°C) : T101 (155 °C), T401 (155 °C)
- The following components require special consideration during end-product Thermal (Heating) tests due to the indicated maximum temperature measurements during component-level testing : metal chassis (100.1 °C)
- Power supply has been additionally tested for intermittent operation. See Additional Information in the beginning of this test report. Additional duty cycle marking to be evaluated in end product.
- The Clearances and Creepage Distances have additionally been assessed for suitability up to 3 000 m elevation.