Test Report issued under the responsibility of:

TEST REPORT
IEC 62368-1
Audio/video, information and communication technology equipment
Part 1: Safety requirements

Report Number .....:	E135494-A6020-CB-1
Date of issue.....:	2020-03-18 ; Amendment 1 : 2021-02-04
Total number of pages .....:	8
Applicant's name.....:	**TDK-LAMBDA UK LTD**
Address .....:	**KINGSLEY AVE** **ILFRACOMBE** **EX34 8ES UNITED KINGDOM**
Name of Test Laboratory preparing the Report .....:	UL VS Limited Unit 1-3 Horizon, Wade Road, Kingsland Business Park, Basingstoke RG24 8AH, United Kingdom
Test specification:	
Standard.....:	IEC 62368-1:2014 (Second Edition)
Test procedure .....:	CB Scheme
Non-standard test method.....:	N/A
Test Report Form No.....:	IEC62368_1B
Test Report Form(s) Originator .....:	UL(US)
Master TRF.....:	2014-03

Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.


If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer:

The test results presented in this report relate only to the object tested.
This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory.
The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test Item description :	Power supply
Trade Mark .....:	TDK-Lambda
Manufacturer .....:	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM
Model/Type reference .....:	DRL10-12-1-xyz and DRL10-24-1-xyz and LOX-10-24-1-xyz (where x,y and z can be any alphanumeric character or blank and is not safety relevant information)
Ratings .....:	Input: 100-240 Vac; 0.25 A; 50/60 Hz Output: DRL10-12-1-xyz: 12 Vdc; 0.84 A (10.08 W) DRL10-24-1-xyz: 24 Vdc; 0.42 A (10.08 W) LOX-10-24-1-xyz : 24 Vdc; 0.42 A (10.08 W)

Testing procedure and testing location:			
☒	CB Testing Laboratory:		
Testing location/ address ..... :		UL VS Limited, Unit 1-3 Horizon, Wade Road, Kingsland Business Park, Basingstoke RG24 8AH, United Kingdom	
Tested by (name + signature).....:		Mark John De Sagun / Project Handler	
Approved by (name + signature) .....:		Roland Koehler / Reviewer	
☐	Testing procedure: CTF Stage 1		
Testing location/ address..... :			
Tested by (name + signature).....:			
Approved by (name + signature) .....:			
☐	Testing procedure: CTF Stage 2		
Testing location/ address..... :			
Tested by (name + signature).....:			

Witnessed by (name + signature).....:		
Approved by (name + signature).....:		
☐ Testing procedure: CTF Stage 3		
☐ Testing procedure: CTF Stage 4		
Testing location/ address..... :		
Tested by (name + signature).....:		
Witnessed by (name + signature).....:		
Approved by (name + signature).....:		
Supervised by (name + signature) .....:		

List of Attachments (including a total number of pages in each attachment):

National Differences (0 pages)
Enclosures (0 pages)

Summary of testing:

Tests performed (name of test and test clause): **None**	**Testing Location: None**

Summary of compliance with National Differences:

List of countries addressed: EU Group and National Differences, USA / Canada

EU Group and National Differences applies to CENELEC member countries: Austria , Belgium, Bulgaria, Croatia, Cyprus, the Czech Republic, Denmark, Estonia, Finland, France, Germany, Greece, Hungary, Iceland, Ireland, Italy, Latvia, Lithuania, Luxembourg, Malta, the Netherlands, Norway, Poland, Portugal, Republic of North Macedonia, Romania, Serbia, Slovakia, Slovenia, Spain, Sweden, Switzerland, Turkey and the United Kingdom

☒ **The product fulfils the requirements of:** EN 62368-1:2014 + A11:2017, CSA CAN/CSA-C22.2 No. 62368-1 2nd Edition, Issued December 1, 2014, BS EN 62368-1:2014 + A11:2017