

# DEMKO CERTIFICATE

<b>Certificate No.</b>	D-07807
<b>Page</b>	1/3
<b>Date of Issue</b>	2020-03-16
<b>Certificate Holder</b>	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
<b>Manufacturer</b>	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
<b>Production site</b>	TDK-LAMBDA CORP 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN  See Page 2
<b>Certified Product Model</b>	Switching Power Supply JWT100-axy See Page 2
<b>Trademark</b>	<b><i>TDK-Lambda</i></b> or <b><i>TDK-Lambda</i></b>
<b>Rated Voltage / Frequency</b>	See Page 2
<b>Rated Current / Power</b>	See Page 2
<b>Insulation Class</b>	Class I
<b>Degree of protection (IP)</b>	IP is not classified (for building-in)
<b>Tested acc. to</b>	EN 62368-1:2014/A11:2017, EN 62368-1:2014
<b>Test Report No.</b>	E122103-A6052-CB-1 issued on 2020-03-12
<b>Additional</b>	for building-in
<b>Expire date</b>	2030-03-15

**Certification Manager**  
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D Mark Requirements. The Designated Certificate holder is entitled to use the d or for cables <DEMKO> for the Certified Product manufactured at the production site(s) identified above, in accordance with the D Mark Service Agreement, including without limitation the D Mark Testing and Certification Services Service Terms. Only those Products bearing the D Mark should be considered as being covered by UL's D Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the expiration date.

**Certification Body**

UL International Demko A/S, Borupvang 5A, DK-2750  
Ballerup, Denmark, Tel. +45 44 85 65 65,  
info.dk@ul.com  
www.ul-europe.com



# Appendix DEMKO CERTIFICATE

**Certificate No.** D-07807  
**Page** 2/3  
**Date of Issue** 2020-03-16

**Model Details:**

JWT100-axy  
a = 522, 5FF, 525  
x = / or /R or blank.  
y = A, B, C or blank.

**Production Sites:**

TDK-LAMBDA MALAYSIA SDN BHD  
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI JOHOR  
MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD  
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN PAHANG  
MALAYSIA

TDK-LAMBDA (CHINA) ELECTRONICS CO.,LTD.  
NO.95 ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028  
CHINA

SENDAN ELECTRONICS MFG CO LTD  
1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756  
JAPAN

ALPS LOGISTICS FACILITIES CO LTD  
593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831  
JAPAN

**Ratings:**

**Input:**  
AC 100-240 V, 50/60 Hz, 1.6 A

**Output:**  
JWT100-522xy DC +5V 13A, DC +12V 5.5A, DC -12V 1A  
JWT100-5FFxy DC +5V 13A, DC +15V 4.5A, DC -15V 1A  
JWT100-525xy DC +5V 13A, DC +12V 5.5A, DC -5V 1A  
All current values are maximum values, of separate outputs.  
The maximum total output power for each model:100W

---


**Certification Body**

UL International Demko A/S, Borupvang 5A, DK-2750  
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com  
www.ul-europe.com



# Appendix DEMKO CERTIFICATE

Certificate No. D-07807  
Page 3/3  
Date of Issue 2020-03-16



---

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750  
Ballerup, Denmark, Tel. +45 44 85 65 65,  
info.dk@ul.com  
www.ul-europe.com

