



Ref. Certif. No.

SI-3328

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST  
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEMESYSTEME CEI D'ACCEPTATION MUTUELLE DE  
CERTIFICATS D'ESSAIS DES EQUIPEMENTS  
ELECTRIQUES (IECEE) METHODE OC

## CB TEST CERTIFICATE

## CERTIFICAT D'ESSAI OC

Product  
Produit

Switching Power Supply for building-in

Name and address of the applicant  
Nom et adresse du demandeurArch Electronics Corp.  
3F., No. 79, Sec. 1, Hsin Tai Wu Rd., Sijhih City, Taipei County  
221, TaiwanName and address of the manufacturer  
Nom et adresse du fabricantArch Electronics Corp.  
3F., No. 79, Sec. 1, Hsin Tai Wu Rd., Sijhih City, Taipei County  
221, TaiwanName and address of the factory  
Nom et adresse de l'usineArch Electronics Corp.  
3F., No. 79, Sec. 1, Hsin Tai Wu Rd., Sijhih City, Taipei County  
221, TaiwanNote: When more than one factory, please report on page 2  
Note: Lorsque il y a plus d'une usine, veuillez utiliser la 2<sup>ème</sup> page Additional Information on page 2Ratings and principal characteristics  
Valeurs nominales et caractéristiques principales

I/P: 100-240 Vac; 47-63 Hz; 0,32-0,17 A

O/P:  Additional Information on page 2Trademark (if any)  
Marque de fabrication (si elle existe)**TDK-Lambda**Type of Manufacturer's Testing Laboratories used  
Type de programme du laboratoire d'essais constructeur

/

Model / Type Ref.  
Ref. De type

KMx15-y

 Additional Information on page 2Additional information (if necessary may also be reported  
on page 2)Les informations complémentaires (si nécessaire, peuvent  
être indiqués sur la 2<sup>ème</sup> pageThe risk management requirements of the standard were not  
addressed. Additional Information on page 2A sample of the product was tested and found  
to be in conformity withUn échantillon de ce produit a été essayé et a été  
considéré conforme à la

IEC 60601-1:2005 (3rd Ed.)

As shown in the Test Report Ref. No. which forms part of  
this CertificateComme indiqué dans le Rapport d'essais numéro de  
référence qui constitue partie de ce Certificat

T223-0163/12, dated 2012-06-06

This CB Test Certificate is issued by the National Certification Body

Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**Slovenski institut za kakovost in meroslovje  
Slovenian Institute of Quality and Metrology  
Tržaška c. 2, SI-1000 Ljubljana, Slovenia  
Product Certification Body is accredited by Slovenian Accreditation, Reg. No. CP-001

Date: 2012-06-06

Signature: Zoran Svetik



**Model / Type Ref.:**

KMx15-y

‘x’ can be S, D or T

S= Single output

D= Dual output

T= Triple output

‘y’ can be 3P3, 5, 7P35, 9, 12, 15, 24, 55, 1212, 1515, 51212 or 51515

**Ratings and principal characteristics:**

I/P: 100-240 Vac; 47-63 Hz; 0,32-0,17 A

O/P:

Model Name	Output Ratings (output dc voltage / output current)
KMS15-3P3	3,3 V / 3 A
KMS15-5	5 V / 3 A
KMS15-7P35	7,35 V / 2,04 A
KMS15-9	9 V / 1,666 A
KMS15-12	12 V / 1,25 A
KMS15-15	15 V / 1 A
KMS15-24	24 V / 0,625 A
KMD15-55	+ 5 V / 1,5 A; - 5 V / 1,5 A
KMD15-1212	+ 12 V / 0,625 A; - 12 V / 0,625 A
KMD15-1515	+ 15 V / 0,5 A; - 15 V / 0,5 A
KMT15-51212	+ 5 V / 2 A; + 12 V / 0,2 A; - 12 V / 0,2 A
KMT15-51515	+ 5 V / 2 A; + 15 V / 0,15 A; - 15 V / 0,15 A

**Additional information (if necessary)****Information complémentaire (si nécessaire)**

Date: 2012-06-06

Signature: Zoran Svetik

