

UL TEST REPORT AND PROCEDURE

Standard:	UL 60950-1, 2nd Edition, 2014-10-14 (Information Technology Equipment - Safety - Part 1: General Requirements) CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10 (Information Technology Equipment - Safety - Part 1: General Requirements)
Certification Type:	Component Recognition
CCN:	QQGQ2, QQGQ8 (Power Supplies for Information Technology Equipment Including Electrical Business Equipment)
Product:	Switching Power Supply for building-in
Model:	LS200-X / YYYYY, where X can be 3.3 or 5 and / YYYYY can be / L, / F, / CO, / CO2, / COL, / CO2L, / COF, / CO2F, / LPY or blank. LS200-X / YYYYYY, where X can be 7.5, 12, 15, 18, 24, 28, 36, 40, 48 or 56 and / YYYYYY can be / B, / BCO, / BCO2, / BCOL, / BCO2L, / BM, / BMCO, / BMCO2, / BMCOL, / BMCO2L, / BL, / BML, / L, / F, / CO, / CO2, / COL, / CO2L, / COF, / CO2F, / BF, / BMF, / BCOF, / BCO2F, / BMCOF, / BMCO2F, / LPY or blank.
Rating:	Input: 100-240 V ac, 3.5 A, 50/60 Hz Output: LS200-3.3: 3.3 Vdc (+3 - +3.6 Vdc), 40 A; LS200-5: 5 Vdc (+4.75 - +5.5 Vdc), 40 A or 26 A; LS200-7.5: 7.5 Vdc (+6.8 - +8.2 Vdc), 26.7 A; LS200-12: 12 Vdc (+10.8 - +14.4 Vdc), 16.7 A; LS200-15: 15 Vdc (+13.5 - +16.5 Vdc), 13.4 A or 9.3 A; LS200-18: 18 Vdc, 11.2 A; LS200-24: 24 Vdc (+22.0 - +28.8 Vdc), 8.4 A; LS200-28: 28 Vdc, 7.2 A; LS200-36: 36 Vdc (+32.0 - +40.0 Vdc), 5.6 A or 3.9 A; LS200-40: 40 Vdc, 5 A; LS200-48: 48 Vdc (+42.0 - +57.6 Vdc), 4.2 A; LS200-56: 56 Vdc, 3.6 A
Applicant Name and Address:	TDK-LAMBDA SINGAPORE PTE LTD #06-01/08 1008 TOA PAYOH NORTH SINGAPORE 318996 SINGAPORE

Issue Date: 2010-01-18
2017-03-29

Page 2 of 16

Report Reference #

E252373-A29-UL

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared by: Chai Ming Yuo, Project Handler

Reviewed by: Chiang Shiau Hui, Reviewer

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
 - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

Electronic components mounted on PWB and housed with metal enclosure.

Model Differences

All Models are similar to each other, except the following:-

- a) Output rating;
- b) Transformer (T1) Secondary winding;
- c) Model designation.

LS200-X / YYYY, where X can be 3.3 or 5 and / YYYY can be / L, / F, / CO, / CO2, / COL, / CO2L, / COF, / CO2F, / LPY or blank.

LS200-X / YYYYYYY, where X can be 7.5, 12, 15, 18, 24, 28, 36, 40, 48 or 56 and / YYYYYYY can be / B, / BCO, / BCO2, / BCOL, / BCO2L, / BM, / BMCO, / BMCO2, / BMCOL, / BMCO2L, / BL, / BML, / L, / F, / CO, / CO2, / COL, / CO2L, / COF, / CO2F, / BF, / BMF, / BCOF, / BCO2F, / BMCOF, / BMCO2F, / LPY or blank.

- 1) B => Input Connector (CN3) and Output connector (CN4) are from JST;
- 2) BM => Input Connector (CN3) and Output connector (CN4) are from Molex;
- 3) CO => PCB with one (1) side coating;
- 4) CO2 => PCB with two (2) sides coating;
- 5) L => Open frame (Cover removed);
- 6) blank => Input connector and output connector using terminal block TB1 and with fan
- 7) F => perforated cover, without fan
- 8) LPY => for internal customer reference

Technical Considerations

- Equipment mobility : for building-in
- Connection to the mains : not directly connected to the mains
- Operating condition : continuous
- Access location : operator accessible
- Over voltage category (OVC) : OVC II
- Mains supply tolerance (%) or absolute mains supply values : +10%, -10% (manufacturer declare)

- Tested for IT power systems : No
- IT testing, phase-phase voltage (V) : N/A
- Class of equipment : Class I (earthed)
- Considered current rating of protective device as part of the building installation (A) : 20
- Pollution degree (PD) : PD 2
- IP protection class : IP X0
- Altitude of operation (m) : at 2000 meters
- Altitude of test laboratory (m) : less than 2000 meters
- Mass of equipment (kg) : Open frame: 0.60 kg, Metal enclosure with ventilation: 0.63 kg, With Fan: 0.68 kg
- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of: Models LS200-3.3, LS200-5, LS200-7.5, LS200-12, LS200-15, LS200-24, LS200-36 and LS200-48: 50 °C for 100 % load (Condition A and B), Mounting Position A, B and C; 70 °C for 60 % load (Condition E and F), Mounting Position A, B and C; , , Models LS200/L-3.3, LS200/L-5 and LS200/L-7.5: 30 °C for 65 % load (Condition C and D), Mounting Position B, C, E and F; 40 °C for 65 % load (Condition C and D), Mounting Position A; 65 °C for 40 % load (Condition G and H), Mounting Position A; 65 °C for 30 % load (Condition I and J), Mounting Position B, C, E and F; , , Models LS200/L-12, LS200/L-15, LS200/L-24, LS200/L-36 and LS200/L-48: 40 °C for 70 % load (Condition C and D), Mounting Position B, C, E and F; 50 °C for 70 % load (Condition C and D), Mounting Position A; 70 °C for 35 % load (Condition G and H), Mounting Position A, B, C, E and F; , , Other Models: Forced Air 50 °C, Conventional cooling 30 °C
- The product is intended for use on the following power systems: TN
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this test report).
- The following accessible locations (with circuit/schematic designation) are within a limited current circuit: Secondary side of C50
- The following were investigated as part of the protective earthing/bonding: Printed wiring board trace point A to point B (refer to Enclosure, Miscellaneous 7-03),
- LEDs provided in the product are considered low power devices: Yes
- The combination pulse of 2.5kV/1.25kA is selected from sub-clause 2.3.6 of IEC 61051-2:1991 with Amendment 1:2009.
- The output voltage range and derating for Models LS200-3.3, LS200-5, LS200-7.5, LS200-12, LS200-15, LS200-24, LS200-36 and LS200-48 were evaluated based on current not exceeding rated output current. Refer to enclosure 7-07 for maximum normal load details.

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following Production-Line tests are conducted for this product: Electric Strength, Earthing Continuity
- The end-product Electric Strength Test is to be based upon a maximum working voltage of: Primary-SELV: 438.656 Vrms, 783.203 Vpk, Primary-Earthed Dead Metal: 236.751 Vrms, 340.365 Vpk ,
- The following secondary output circuits are SELV: LS200-3.3: 3.3 Vdc; LS200-5: 5 Vdc; LS200-7.5: 7.5 Vdc; LS200-12: 12 Vdc; LS200-15: 15 Vdc; LS200-18: 18 Vdc; LS200-24: 24 Vdc; LS200-28: 28 Vdc; LS200-36: 36 Vdc; LS200-40: 40 Vdc; LS200-48: 48 Vdc; LS200-56: 56 Vdc,

- The following secondary output circuits are at hazardous energy levels: LS200-5: 5 Vdc (+4.75 - +5.5 Vdc); LS200-7.5: 7.5 Vdc (+6.8 - +8.2 Vdc); LS200-12: 12 Vdc (+10.8 - +14.4 Vdc); LS200-15: 15 Vdc (+13.5 - +16.5 Vdc); LS200-18: 18 Vdc; LS200-24: 24 Vdc (+22.0 - +28.8 Vdc); LS200-28: 28 Vdc; LS200-36: 36 Vdc (+32.0 - +40.0 Vdc); LS200-40: 40 Vdc; LS200-48: 48 Vdc (+42.0 - +57.6 Vdc); LS200-56: 56 Vdc
- The following secondary output circuits are at non-hazardous energy levels: LS200-3.3: 3.3 Vdc (+3 - +3.6 Vdc)
- The following secondary output circuits are Limited Current Circuits: Secondary side of C50
- The following output terminals were referenced to earth during performance testing: T1 Pin 9, 10
- The power supply terminals and/or connectors are: Suitable for factory wiring only
- The maximum investigated branch circuit rating is: 20 A
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required
- An investigation of the protective bonding terminals has: Been conducted
- The following input terminals/connectors must be connected to the end-product supply neutral: TB1 pin 2 or CN3 pin 2.
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJ2 insulation system with the indicated rating greater than Class A (105°C): T1 (Class B)
- The following end-product enclosures are required: Mechanical, Fire, Electrical
- The following LEDs operate within the exempt group per IEC 62471: Indicator LED
- Models LS200-3.3, LS200-5, LS200-7.5, LS200-12, LS200-15, LS200-24, LS200-36 and LS200-48 were evaluated to mounting position A, B and C. Models LS200/L-3.3, LS200/L-5, LS200/L-7.5, LS200/L-12, LS200/L-15, LS200/L-24, LS200/L-36 and LS200/L-48 were evaluated to mounting position A, B, C, E and F. Other Models only evaluated at mounting position A. Refer to enclosure 4-20 for details.

Additional Information

N/A

Additional Standards

The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013

Markings and instructions

Clause Title	Marking or Instruction Details
Power rating - Ratings	Ratings (voltage, frequency/dc, current)
Power rating - Company identification	Listee's or Recognized company's name, Trade Name, Trademark or File Number
Power rating - Model	Model Number
Fuses - Rating	