



Ref. Certif. No.

JP-25240-M1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Name and address of the applicant

Name and address of the manufacturer

Name and address of the factory

Note: When more than one factory, please report on page 2

Switching Power Supply

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN

TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-1195 JAPAN

Ratings and principal characteristics

See Page 2

Trademark (if any)



Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

JWT75-522, JWT75-5FF, JWT75-525
(may be provided with suffix: "/A", "/B", "/C", "/R", "/RA", "/RB" or "/RC")

Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modifications. Additionally evaluated to EN IEC 62368-1:2020/ A11:2020. National Differences specified in the CB Test Report.

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2018

As shown in the Test Report Ref. No. which forms part of this Certificate

E122103-A6114-CB-1 issued on 2022-02-20

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2022-02-21
Original Issue Date: 2021-06-07

Signature:
Masamichi Takagi



Ref. Certif. No.

JP-25240-M1-UL

Factory(ies):

TDK-LAMBDA (CHINA) ELECTRONICS CO.,LTD.
NO.95 ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028
CHINA

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN PAHANG
MALAYSIA

ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831
JAPAN

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI JOHOR
MALAYSIA

SENDAN ELECTRONICS MFG CO LTD
1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756
JAPAN

Ratings:

Input:
AC 100-240V, 50/60Hz, 1.4A

Output:
JWT75-522: +5Vdc/8.0A, +12Vdc/4.0A, -12Vdc/0.5A
JWT75-5FF: +5Vdc/8.0A, +15Vdc/3.2A, -15Vdc/0.5A
JWT75-525: +5Vdc/8.0A, +12Vdc/4.0A, -5Vdc/0.5A

All current values are maximum values, of separate outputs.
The maximum total output power for each model: 75W

Summary of Modifications:

- Addition of an alternative Y-capacitor (C2, C3, C8).
Mfr.: TDK Corporation, Type: CD.


Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2022-02-21
Original Issue Date: 2021-06-07

Signature: 
Masamichi Takagi