



Ref. Certif. No.

SI-3328

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEMESYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product
Produit

Switching Power Supply for building-in

Name and address of the applicant
Nom et adresse du demandeurArch Electronics Corp.
3F., No. 79, Sec. 1, Hsin Tai Wu Rd., Sijhih City, Taipei County
221, TaiwanName and address of the manufacturer
Nom et adresse du fabricantArch Electronics Corp.
3F., No. 79, Sec. 1, Hsin Tai Wu Rd., Sijhih City, Taipei County
221, TaiwanName and address of the factory
Nom et adresse de l'usineArch Electronics Corp.
3F., No. 79, Sec. 1, Hsin Tai Wu Rd., Sijhih City, Taipei County
221, TaiwanNote: When more than one factory, please report on page 2
Note: Lorsque il y a plus d'une usine, veuillez utiliser la 2^{ème} page Additional Information on page 2Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

I/P: 100-240 Vac; 47-63 Hz; 0,32-0,17 A

O/P: Additional Information on page 2Trademark (if any)
Marque de fabrication (si elle existe)**TDK-Lambda**Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur

/

Model / Type Ref.
Ref. De type

KMx15-y

 Additional Information on page 2Additional information (if necessary may also be reported
on page 2)Les informations complémentaires (si nécessaire, peuvent
être indiqués sur la 2^{ème} pageThe risk management requirements of the standard were not
addressed. Additional Information on page 2A sample of the product was tested and found
to be in conformity withUn échantillon de ce produit a été essayé et a été
considéré conforme à la

IEC 60601-1:2005 (3rd Ed.)

As shown in the Test Report Ref. No. which forms part of
this CertificateComme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

T223-0163/12, dated 2012-06-06

This CB Test Certificate is issued by the National Certification Body

Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**Slovenski institut za kakovost in meroslovje
Slovenian Institute of Quality and Metrology
Tržaška c. 2, SI-1000 Ljubljana, Slovenia
Product Certification Body is accredited by Slovenian Accreditation, Reg. No. CP-001

Date: 2012-06-06

Signature: Zoran Svetik

Model / Type Ref.:

KMx15-y

‘x’ can be S, D or T

S= Single output

D= Dual output

T= Triple output

‘y’ can be 3P3, 5, 7P35, 9, 12, 15, 24, 55, 1212, 1515, 51212 or 51515

Ratings and principal characteristics:

I/P: 100-240 Vac; 47-63 Hz; 0,32-0,17 A

O/P:

Model Name	Output Ratings (output dc voltage / output current)
KMS15-3P3	3,3 V / 3 A
KMS15-5	5 V / 3 A
KMS15-7P35	7,35 V / 2,04 A
KMS15-9	9 V / 1,666 A
KMS15-12	12 V / 1,25 A
KMS15-15	15 V / 1 A
KMS15-24	24 V / 0,625 A
KMD15-55	+ 5 V / 1,5 A; - 5 V / 1,5 A
KMD15-1212	+ 12 V / 0,625 A; - 12 V / 0,625 A
KMD15-1515	+ 15 V / 0,5 A; - 15 V / 0,5 A
KMT15-51212	+ 5 V / 2 A; + 12 V / 0,2 A; - 12 V / 0,2 A
KMT15-51515	+ 5 V / 2 A; + 15 V / 0,15 A; - 15 V / 0,15 A

Additional information (if necessary)**Information complémentaire (si nécessaire)**

Date: 2012-06-06

Signature: Zoran Svetik

