



Ref. Certif. No.

DK-16200

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEMESYSTEME CEI D'ACCEPTATION MUTUELLE DE CERTIFICATS
D'ESSAIS DES EQUIPEMENTS ELECTRIQUES (IECEE)
METHODE OCCB TEST CERTIFICATE
CERTIFICAT D'ESSAI OCProduct
Produit

Switching Power Supply for building-in

Name and address of the applicant
Nom et adresse du demandeurTDK-LAMBDA SINGAPORE PTE LTD
#06-01/08, 1008 TOA PAYOH NORTH
SINGAPORE 318996 SINGAPOREName and address of the manufacturer
Nom et adresse du fabricantTDK-LAMBDA SINGAPORE PTE LTD
#06-01/08, 1008 TOA PAYOH NORTH
SINGAPORE 318996 SINGAPOREName and address of the factory
Nom et adresse de l'usine

See appendix

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{me} pageRatings and principal characteristics
Valeurs nominales et caractéristiques principales

100-240 V ac, 0.8 A, 50/60 Hz, Class I, IP X0

Trademark (if any)
Marque de fabrique (si elle existe)**TDK-Lambda**Model / Type Ref.
Ref. De typeLS35-X /YYYYYY, where X can be 3.3, 5, 7, 12, 15, 18, 24, 28,
36, 40, 48, or 56 and /YYYYYY can be /B, /BCO, /BCO2, /BCOL,
/BCO2L, /BM, /BMCO, /BMCO2, /BMCOL, /BMCO2L, /BL, /BML,
/CO, /CO2, /COL, /CO2L, /L or blank.Additional information (if necessary may also be reported
on page 2)
Les informations complémentaires (si nécessaire, peuvent
être indiqués sur la 2^{me} page)Output Rating: see appendix, for building-in. Testing done
under the Testing at Manufacturer's Premises (TMP)
procedure. Also investigated to EN 60950-1:2006.A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à laPUBLICATION
IEC 60950-1:2005EDITION
2ndAs shown in the Test Report Ref. No. which forms part of
this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

E252373-A19-CB-2 issue date 2009-07-06

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme National de CertificationUnderwriters
Laboratories

UL International Demko A/S

Lyskaer 8, P.O. Box 514, DK-2730 Herlev, Denmark
Tel: +45 44856565, Fax: +45 44856500

Date:

2009-07-08

Signature:

Jan-Erik Storgaard
Certification manager



Ref. Certif. No.

DK-16200

Output Rating:

LS35-3.3: 3.3 V dc, 7 A;
LS35-5: 5 V dc, 7 A;
LS35-7: 7 V dc, 5 A;
LS35-12: 12 V dc, 3 A;
LS35-15: 15 V dc, 2.4 A;
LS35-18: 18 V dc, 2 A;
LS35-24: 24 V dc, 1.5 A;
LS35-28: 28 V dc, 1.3 A;
LS35-36: 36 V dc, 1 A;
LS35-40: 40 V dc, 0.9 A;
LS35-48: 48 V dc, 0.8 A;
LS35-56: 56 V dc, 0.7.

Production Sites:

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI
81400 SENAI MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4
KAWASAN PERINDUSTRIAN
BANDAR BARU JAYA GADING
26070 KUANTAN MALAYSIA

WUXI TDK-LAMBDA ELECTRONICS CO LTD
LOT 107 WUXI SINGAPORE INDUSTRIAL PARK
XING CHUANG ERLU WUXI,
JIANGSU 214028 CHINA

VIETTRONICS BINH HOA CO
204 NO TRANG LONG ST
BINH THANH
HO CHI MINH CITY VIETNAM

Additional information (if necessary)
Information complémentaire (si nécessaire)



Date:
2009-07-08

UL International Demko A/S

Lyskaer 8, P.O. Box 514, DK-2730 Herlev, Denmark
Tel: +45 44856565, Fax: +45 44856500

Signature:

Jan-Erik Storgaard
Certification manager