

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product
Produit

Switching Power Supply for building-in

Name and address of the applicant
Nom et adresse du demandeur

Arch Electronics Corp.
3F., No. 79, Sec. 1, Hsin Tai Wu Rd., Sijhih City, Taipei County
221, Taiwan

Name and address of the manufacturer
Nom et adresse du fabricant

Arch Electronics Corp.
3F., No. 79, Sec. 1, Hsin Tai Wu Rd., Sijhih City, Taipei County
221, Taiwan

Name and address of the factory
Nom et adresse de l'usine

Arch Electronics Corp.
3F., No. 79, Sec. 1, Hsin Tai Wu Rd., Sijhih City, Taipei County
221, Taiwan

Note: When more than one factory, please report on page 2
Note: Lorsque il y a plus d'une usine, veuillez utiliser la 2^{ème} page

Additional Information on page 2

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

I/P: 100-240 Vac; 47-63 Hz; 0,8-0,4 A
O/P: Additional Information on page 2

Trademark (if any)
Marque de fabrique (si elle existe)

TDK·Lambda

Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur

/

Model / Type Ref.
Ref. De type

KMx40-y
 Additional Information on page 2

Additional information (if necessary may also be reported
on page 2)
Les informations complémentaires (si nécessaire,, peuvent
être indiqués sur la 2^{ème} page

The risk management requirements of the standard were not
addressed.

Additional Information on page 2

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

IEC 60601-1:2005 (3rd Ed.)

As shown in the Test Report Ref. No. which forms part of
this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

T223-0384/11, dated 2012-01-09

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme National de Certification



Slovenski institut za kakovost in meroslovje
Slovenian Institute of Quality and Metrology
Tržaška c. 2, SI-1000 Ljubljana, Slovenia
Product Certification Body is accredited by Slovenian Accreditation, Reg. No.: CP-001

Date: 2012-01-09

Signature: Alja Pregl

Model / Type Ref.:

KMx40-y

"x" can be S, D or T

S= Single output

D= Dual output

T= Triple output

"y" can be 3P3, 5, 9, 12, 15, 24, 55, 1212, 1515, 512, 524, 51212 or 51515

Ratings and principal characteristics:

I/P: 100-240 Vac; 47-63 Hz; 0,8-0,4 A

O/P:

Model Name	Output Ratings (output dc voltage / output current)
KMS40-3P3	3,3 V / 8 A
KMS40-5	5 V / 8 A
KMS40-9	9 V / 4,444 A
KMS40-12	12 V / 3,333 A
KMS40-15	15 V / 2,666 A
KMS40-24	24 V / 1,667 A
KMD40-55	+5 V / 4 A, -5 V / 4 A
KMD40-1212	+12 V / 1,666 A, -12 V / 1,666 A
KMD40-1515	+15 V / 1,333 A, -15 V / 1,333 A
KMD40-512	+5 V / 5 A, +12 V / 1,25 A
KMD40-524	+5 V / 5 A, +24 V / 0,625 A
KMT40-51212	+5 V / 5 A, +12 V / 0,6 A, -12 V / 0,6 A
KMT40-51515	+5 V / 5 A, +15 V / 0,5 A, -15 V / 0,5 A

Additional information (if necessary)**Information complémentaire (si nécessaire)**

Date: 2012-01-09

Signature: Alja Pregl

