

DEMKO CERTIFICATE

Certificate No. D-07842-M1
Page 1/4
Date of Issue 2020-09-24



Certificate Holder TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Manufacturer TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Production site TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR
BARU JAYA GADING 26070 KUANTAN PAHANG
MALAYSIA

See Page 2

Certified Product Model Switching Power supply
1) LWT50H-5FF and LWT50H-5FF/SCC, 2) LWT50H-522,
3) LWT50H-525, 4) LWT50H-6FF/SCC, 5) LWT50H-522/KE

Trademark DENSEI-LAMBDA or DENSEI-LAMBDA or  **NEMIC-LAMBDA**
or  **NEMIC-LAMBDA** or **TDK-Lambda**

Rated Voltage / Frequency See Page 2

Rated Current / Power See Page 2

Insulation Class Class I

Degree of protection (IP) IP is not classified (for building-in)

Tested acc. to EN 62368-1:2014/A11:2017, EN 62368-1:2014

Test Report No. E122103-A6089-CB-1 issued on 2020-09-22

Additional for building-in.

The report was revised to include technical modification(s).

Expire date 2030-03-29

Certification Manager
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D-Mark Requirements. As specified in the respective appendix below the Designated Certificate holder is entitled to use the D-Mark, or its alternative for cables, for the Certified Product manufactured at the production site(s) identified above, in accordance with the D-Mark Service Agreement, including without limitation the D-Mark Testing and Certification Services Service Terms. Only those Products bearing the D-Mark should be considered as being covered by UL's D-Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the expiration date.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-07842-M1
Page 2/4
Date of Issue 2020-09-24

Production Sites:

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD
NO.15 TONGXIN RD, ZHAOFENG ECONOMIC DEVELOPMENT ZONE, LEYU TOWN ZHANGJIAGANG JIANGSU
215622
CHINA

TDK-LAMBDA (CHINA) ELECTRONICS CO LTD
NO.95,ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028
CHINA

Ratings:

Input
100-240 VAC, 1.5 A, 50/60 Hz

Output:

1) LWT50H-5FF and LWT50H-5FF/SCC
5 VDC, 8 A, +15 VDC, 1.5 A, -15 VDC, 1.0 A

2) LWT50H-522
5 VDC, 8 A, +12 VDC, 1.5 A, -12 VDC, 1.0 A

3) LWT50H-525
5 VDC, 8 A, +12 VDC, 1.5 A, -5 VDC, 1.0A

4) LWT50H-6FF/SCC
6.5 VDC, 3.0 A, +15 VDC, 1.6 A, -15 VDC, 0.7 A

5) LWT50H-522/KE
5 VDC, 8.0 A, +12 VDC, 2.0 A, -12 VDC, 1.0 A

Total Output Power:

50 W MAX. (except for model LWT50H-6FF/SCC)
54 W MAX. (only for model LWT50H-6FF/SCC)

LWT50H-5FF maybe provided with additional identification of "SAF" denoting minor variation.

Additional Information:

This certificate replaces the certificate No. D-07842, issued on 2020-03-30 due to:

- Addition of Insulation Tube of Fuse (F1) (Optional), SUMITOMO ELECTRIC FINE POLYMER INC, Type Sumitube F2(Z).
- Addition of Alternate Insulation Tube of Fuse (F1) (Optional), TYCO ELECTRONICS CORP, Type Versafit V2.
- Addition of Insulation Tape of Fuse (F1) [Alternative construction for Insulation Tube] (Optional), Nitto Denko Corp.,

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-07842-M1
Page 3/4
Date of Issue 2020-09-24

Type 3161-F.

- Update Table 5.4.2.2, 5.4.2.4 and 5.4.3 and Table 5.4.2.3 due to revision of measured clearance value at "F1 Body (Fuse Cap) to Chassis (FG)".

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-07842-M1
Page 4/4
Date of Issue 2020-09-24

Certification Mark D-Mark

The D-Mark, as displayed below, shall appear on certified products only. Minimum size is not specified, as long as the Mark is legible.



The size of the Mark may be reduced or enlarged on the condition that it remains readable and that the proportions of width and height are kept. The use of dark text for the D-Mark on light backgrounds and light text on dark backgrounds is permitted.

When putting the product on the EU market, the manufacturer's name, trademark or mark of origin must be affixed in a clearly visible location and position on the product, on the package and in the user manual. It can be affixed by label, be directly imprinted, or cast or molded into the product.

Alternate certification Mark for cables

As an alternative to the D-Mark specified above the alternate D-Mark, displayed below, can appear on certified cables only. Minimum size is not specified, as long as the mark is legible.

◁DEMKO▷

The alternate D-Mark may be cast, stamped or moulded into the cable and continue throughout the length of the cable as specified in the applicable cable standard.

All content shall be in accordance with the details provided on this D-Mark Certificate.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com

