

DEMKO CERTIFICATE

Certificate No. D-07501
Page 1/3
Date of Issue 2019-09-18

Certificate Holder TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Manufacturer TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Production site TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI
MALAYSIA

See Page 2

Certified Product Model Switching Power Supply
MTW30-51212xy, MTW30-51515xy
See Page 2

Trademark TDK-Lambda

TDK-Lambda

Rated Voltage / Frequency

See Page 2

Rated Current / Power

See Page 2

Insulation Class

Not classified

Degree of protection (IP)

IP is not classified (for building-in)

Tested acc. to

EN 62368-1:2014/A11:2017, EN 62368-1:2014

Test Report No.

E122103-A6049-CB-1 issued on 2019-09-17

Additional

Expire date

2029-09-17

Certification Manager
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D Mark Requirements. The Designated Certificate holder is entitled to use the d or for cables <DEMKO> for the Certified Product manufactured at the production site(s) identified above, in accordance with the D Mark Service Agreement, including without limitation the D Mark Testing and Certification Services Service Terms. Only those Products bearing the D Mark should be considered as being covered by UL's D Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior to the expiration date.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.ul-europe.com



Appendix DEMKO CERTIFICATE

Certificate No. D-07501
Page 2/3
Date of Issue 2019-09-18

Model Details:

MTW30-51212xy, MTW30-51515xy x = "-" or blank. y = 0-9, A-Z or blank

Production Sites:

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN
MALAYSIA

ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831
JAPAN

Ratings:

Input
100-240 Vac, 0.8-0.4 A, 50-60 Hz

Output:

MTW30-51212xy
+5 V dc, 3.0 A (4.5 A Peak)
+12 V dc, 1.2 A (2.0 A Peak)
-12 V dc, 0.3 A (0.45 A Peak)
Total Output 30 W max.

Model MTW30-51515xy
+5 V dc, 3.0 A (4.5 A Peak)
+15 V dc, 0.8 A (2.0 A Peak)
-15 V dc, 0.3 A (0.45 A Peak)
Total Output 31.5 W max.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul-europe.com



Appendix DEMKO CERTIFICATE

Certificate No. D-07501
Page 3/3
Date of Issue 2019-09-18



Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul-europe.com

