

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

AC-DC Switch Mode Power Supply

Name and address of the applicant

TDK-LAMBDA UK LTD
KINGSLEY AVE
ILFRACOMBE, EX34 8ES United Kingdom

Name and address of the manufacturer

TDK-LAMBDA UK LTD
KINGSLEY AVE
ILFRACOMBE, EX34 8ES United Kingdom

Name and address of the factory

Note: When more than one factory, please report on page 2

Panyu Trio Microtronics Co Ltd
SHIJI INDUSTRIAL ESTATE
DONGYONG
NANSHA
GUANGZHOU, 511453 GUANGDONG China Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

NV-175 Series, NV1-1G000, NV175 Series
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014 / A11: 2017; National Differences specified in the CB Test Report.

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E135494-A6003-CB-1 issued on 2018-12-12

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-12-13

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-79117-UL

Model Details:

NV-175 Series, NV1-1G000, NV175 Series See test report for details

Factories:

TDK-LAMBDA UK LTD
KINGSLEY AVE
ILFRACOMBE, EX34 8ES United Kingdom

Ratings:

NV175 Series; NV-175 Series:
100-240Vac (Nominal), 90-264V (Full Tolerance), 45-440Hz, 3Arms
NV175 Series; NV-175 Series:
133-318Vdc (Nominal), 120-350Vdc (Full Tolerance), 2.2A dc
NV1-1G000 only:
88.9-240Vac (Nominal), 80-264Vac (Full Tolerance), 45-440Hz, 3Arms
(See test report Model Differences for details)

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-12-13

Signature:

Jan-Erik Storgaard