

DEMKO CERTIFICATE

Certificate No. D-07172
Page 1/3
Date of Issue 2019-03-21

Certificate Holder TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI, 940-1195 NIIGATA Japan

Manufacturer TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI, 940-1195 NIIGATA Japan

Production site ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI
TSUKUBA-SHI, 305-0831 IBARAKI-KEN Japan

See Page 2

Certified Product Model Switching Power Supply
MTW60-51212xy, MTW60-51515xy
See Page 2

Trademark

TDK-Lambda

Rated Voltage / Frequency 100-240 Vac, 50-60 Hz

Rated Current / Power 1.4-0.8 A

Insulation Class I

Degree of protection (IP) IP is not classified (for building-in)

Tested acc. to EN 62368-1:2014/A11:2017, EN 62368-1:2014

Test Report No. E122103-A6056-CB-1 issued on 2019-03-19

Additional See Page 2

Expire date 2029-03-20

Certification Manager
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D Mark Requirements. The Designated Certificate holder is entitled to use the d or for cables <DEMKO> for the Certified Product manufactured at the production site(s) identified above, in accordance with the D Mark Service Agreement, including without limitation the D Mark Testing and Certification Services Service Terms. Only those Products bearing the D Mark should be considered as being covered by UL's D Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior to the expiration date.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.ul-europe.com



Appendix DEMKO CERTIFICATE

Certificate No. D-07172
Page 2/3
Date of Issue 2019-03-21

Model Details:

MTW60-51212xy, MTW60-51515xy x = "-" or blank. y = 0-9, A-Z or blank

Factories:

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI
SENAI, 81400 JOHOR Malaysia

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4
KAWASAN PERINDUSTRIAN
BANDAR BARU JAYA GADING
KUANTAN, 26070 PAHANG Malaysia

Additional Information:

Output:

<MTW60-51212xy>

+5 Vdc, 5.0 A (7.0 A peak)

+12 Vdc, 2.5 A (3.5 A peak)

-12 Vdc, 0.5 A (0.7 A peak)

Total maximum output power: 60 W (peak current for 10 seconds maximum, total power shall not exceed 60 W during peak load.)

<MTW60-51515xy>

+5 Vdc, 5.0 A (7.0 A peak)

+15 Vdc, 2.0 A (3.5 A peak)

-15 Vdc, 0.5 A (0.7 A peak)

Total maximum output power: 62.5 W (peak current for 10 seconds maximum, total power shall not exceed 62.5 W during peak load.)


Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul-europe.com



Appendix DEMKO CERTIFICATE

Certificate No. D-07172
Page 3/3
Date of Issue 2019-03-21



Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul-europe.com

