



Ref. Certif. No.

DK-148210-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Switch mode power supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES United Kingdom
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES United Kingdom
Name and address of the factory	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES United Kingdom <input checked="" type="checkbox"/> Additional Information on page 2
Note: <i>When more than one factory, please report on page 2</i>	
Ratings and principal characteristics	NV175 Series, NV-175 Series: 100-240Vac (Nominal), 90-264V (Full Tolerance), 45-63Hz, 3Arms <input checked="" type="checkbox"/> Additional Information on page 2
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	NV175 Series, NV-175 Series, NV1-1G000 <input checked="" type="checkbox"/> Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	The risk management requirements of the standard were not addressed <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60601-1:2005, IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005/AMD2:2020
As shown in the Test Report Ref. No. which forms part of this Certificate	E349607-D1109-1/A0/C0-CB issued on 2023-12-07

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2023-12-08

Signature:
Thomas Wilson



Ref. Certif. No.

DK-148210-UL

Factory(ies):

Panyu Trio Microtronics Co Ltd
SHIJI INDUSTRIAL ESTATE
DONGYONG
NANSHA GUANGZHOU, Guangdong Sheng, 511453
China

Trio-Tronics (Thailand) Ltd
7/295 Mu. 6
Map Yang Phon Sub-District Pluak Daeng District, Rayong,
Thailand

Additional Model Detail(s):

NV175 Series, NV-175 Series, NV1-1G000, (see test report Model Differences for details)

Additional Ratings:

NV1-1G000 only: 88.9-240Vac (Nominal), 80-264V (Full Tolerance), 45-63Hz, 3Arms
(see test report Model Differences for details)

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2023-12-08

Signature:

Thomas Wilson