


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Power Supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Name and address of the factory <small>Note: When more than one factory, please report on page 2</small>	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM <input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	100-240 Vac See Page 2
Trademark (if any)	TDK-Lambda 
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	NV700 or NV-700 Range, RA-PFC-001 (see test report Model Differences for details of NV700 Range model configurations)
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 60950-1: 2006 / A11: 2009 / A1: 2010 / A12: 2011 / A2:2013; National Differences specified in the CB Test Report. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1, IEC 60950-1(ed.2);am2
As shown in the Test Report Ref. No. which forms part of this Certificate	E135494-A53-CB-3 issued on 2018-01-18

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-01-19
Original Issue Date: 2014-12-10

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-42330-A2-UL

Factories:
PANYU TRIO MICROTRONIC CO. LTD
SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG
CHINA

Ratings:
NV700 or NV-700 Range:
100-240Vac nominal (90-264V max. tolerance), 47-440Hz, 11A
(see test report Model Differences for details of model ratings)
RA-PFC-001:
input: 100-240Vac nominal (90-264V max. tolerance), 47-63Hz, 11A
max.
output: 350Vdc, 2.3A max.

Additional Information:
The original report was modified to include the following changes/additions:
addition of an alternate boost capacitor, update of the critical components table and model differences.

Additional information (if necessary)



- UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-01-19
Original Issue Date: 2014-12-10

Signature: 
Jan-Erik Storgaard