


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

## CB TEST CERTIFICATE

Product	Switch Mode Power Supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE DEVON EX34 8ES, UNITED KINGDOM
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE, EX34 8ES United Kingdom
Name and address of the factory	Panyu Trio Microtronics Co Ltd SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU, 511453 GUANGDONG China
<i>Note: When more than one factory, please report on page 2</i>	
Ratings and principal characteristics	<input checked="" type="checkbox"/> Additional Information on page 2 See Page 2
Trademark / Brand (if any)	TDK-Lambda  
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	KQM5001V-x, QI4, QI5, QI7, QI8, QI8B, See Page 2
Additional information (if necessary may also be reported on page 2)	The report was revised to include technical modifications; <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60950-1:2005/AMD1:2009, IEC 60950-1:2005/AMD2:2013, IEC 60950-1:2005
As shown in the Test Report Ref. No. which forms part of this Certificate	E135494-A111-CB-2 issued on 2020-09-23

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-09-23

Original Issue Date: 2018-05-15

Signature:

Jan-Erik Storgaard

## Model Details:

KQM5001V-x, QI4, QI5, QI7, QI8, QI8B, QM4, QM5, QM7, QM8, QM8B, QS4, QS5, QS7 switch mode power supplies (followed by alphanumeric characters - see Model Differences section in Test Report for details of models and nomenclature)

## Factories:

TDK-LAMBDA UK LTD  
KINGSLEY AVE  
ILFRACOMBE, EX34 8ES United Kingdom

Trio-Tronics (Thailand) Ltd  
7/295 Mu. 6  
Map Yang Phon Sub-District  
Pluak Daeng District, Rayong Province Thailand

## Ratings:

QM4, QI4 or QS4 (550W): 144-318Vdc nom, 6Adc max  
QM4, QI4 or QS4 (650W): 239-318Vdc nom, 5Adc max  
QM5, QI5 or QS5 (700W): 144-318Vdc nom, 7Adc max  
QM5, QI5 or QS5 (800W): 239-318Vdc nom, 7Adc max  
QM5H, QI5H or QS5H (700W): 144-318Vdc nom, 7Adc max  
QM5H, QI5H or QS5H (800W): 239-318Vdc nom, 7Adc max  
QM5H, QI5H or QS5H (1200W): 239-318Vdc nom, 7Adc max  
QM7, QI7 or QS7 (1200W): 144-318Vdc nom, 13Adc max  
QM7, QI7 or QS7 (1500W): 239-318Vdc, 9Adc max  
QM8, QI8 (1200W): 144-318Vdc nom, 13Adc max  
QM8, QI8 (1500W): 239-318Vdc, 10Adc max  
QM8B, QI8B (1200W): 144-318Vdc nom, 13Adc max  
QM8B, QI8B (1500W): 239-318Vdc, 10Adc max  
QM8B, QI8B (2000W): 239-318Vdc, 12Adc max

## Additional Information:

Additionally evaluated to EN 60950-1: 2006 / A11: 2009 / A1: 2010 / A12: 2011 / A2: 2013; National Differences specified in the CB Test Report.

## For DC variants

The original report was modified to include the following changes/additions:  
Models, addresses ratings and critical components revised. See test report for details.

## Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-09-23

Original Issue Date: 2018-05-15

Signature:



Jan-Erik Storgaard