

Test Report issued under the responsibility of:



TEST REPORT IEC 62368-1

Audio/video, information and communication technology equipment Part 1: Safety requirements

Report Number: 31981014.300

Date of issue 04/27/2020

Applicant's name: TDK-Lambda Americas Inc.

Test specification:

Standard.....: IEC 62368-1:2014 (Second Edition)

Test procedure.....: CB Scheme

Non-standard test method.....: N/A

Test Report Form No.....: IEC62368_1B

Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer:

The test results presented in this report relate only to the object tested.

This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test I	tem description:	Power supply	
Trade	Mark:	TDK·Lambda	
Manu	facturer	Same as applicant	
Mode	l/Type reference:		A-Z, 0-9 or blank; denoting number etic changes or for marketing oduct safety)
Ratin	gs:	Input: 3 Phase ~ 400 – 48 Watts max.	30 V, 80A / Phase, 50-60 Hz, 46400
		Output: 45000W max., 38 Table)	35VDC, 117A (See Output Ratings
Testi	ng procedure and testing location:		
	CB Testing Laboratory:	TUV Rheinland of North A	America, Inc.
Testi	ng location/ address:	1279 Quarry Lane, Ste. A	A, Pleasanton, CA 94566 USA
	Associated CB Testing Laboratory:		
Testi	ng location/ address:		
,	Tested by (name + signature):		
	Approved by (name + signature):		
	Testing procedure: TMP/CTF Stage 1		
Testi	ng location/ address:		
,	Tested by (name + signature):		
	Approved by (name + signature):		
\boxtimes	Testing procedure: WMT/CTF Stage 2	TDK-Lambda Americas,	Inc
Testi	ng location/ address:	401 Mile of Cars Way, Son National City, CA 91950	uite 325
,	Tested by (name + signature):	Anthony Villasenor	A Villasenor
	Witnessed by (name + signature):	Dan Aquino	
	Approved by (name + signature):	James Howell	
	Testing procedure: SMT/CTF Stage 3 or 4		
Testi	ng location/ address:		
,	Tested by (name + signature):		
	Approved by (name + signature):		
	Supervised by (name + signature):		

List of Attachments (including a total number of pages in each attachment):

Attachment 1: National Differences (33 pages)

Attachment 2: Photos (6 pages)

Attachment 3: Mechanical Drawings (6 pages)

Attachment 4: Schematics (14 pages) Attachment 5: PCB Layouts (6 pages)

Attachment 6: Product Documentation (2 pages)

Attachment 7: User Manual (16 pages)

Attachment 8: Transformer/Inductor Construction Sheet (6 pages)

Attachment 9: IEC/UL/CSA 60950-1 Limited Power Source Measurement (4 pages)

Summary of testing:

The test data was taken from the TUV CB report 31981014.001 and 31981014.003 which is in accordance with IEC 60950-1 for the model TPF45000-385-xxx.

The product was tested on a bench top with full load which drew the output power to the max. rated value. Refer to body of report and appended tables for details of each test.

Tests performed (name of test and test clause):

31981014.300

Electrical Strength Test (5.4.9)

Safeguards Against Capacitor Discharge after Disconnection of a Capacitor (5.5.2.2)

Protective Conductor Current (5.7.5)

31981014.003

Safeguards Against Capacitor Discharge after Disconnection of a Capacitor (5.5.2.2)

Humidity Conditioning (5.4.8)

Maximum operating temperatures for materials, components and systems (5.4.1.4, 6.3.2, 9.0, B.2.6)

Ball Pressure Test (5.4.1.10.3)

Touch Current Test (5.7.2)

Electrical Strength Test (5.4.9)

Simulated Abnormal operating condition tests (B.3)

Simulated single fault conditions (B.4)

31981014.001

Maximum Output Voltage, Current, and Volt-Ampere Measurement Test (1.2.2.1)

Input Test (B.2.5)

Safeguards Against Capacitor Discharge after

Testing location:

31981014.003

TDK-Lambda Americas, Inc. 401 Mile of Cars Way, Suite 325 National City, CA 91950

31981014.003

TDK-Lambda Americas, Inc. 401 Mile of Cars Way, Suite 325 National City, CA 91950

31981014.001

TDK-Lambda Americas, Inc. 401 Mile of Cars Way, Suite 325 National City, CA 91950 Disconnection of a Capacitor (5.5.2.2)

Resistance of the protective bonding system (5.6.6)

Humidity Conditioning (5.4.8)

Determination of working voltage (5.4.1.8)

Maximum operating temperatures for materials, components and systems (5.4.1.4, 6.3.2, 9.0, B.2.6)

Ball Pressure Test (5.4.1.10.3)

Touch Current Test (5.7.2)

Electrical Strength Test (5.4.9)

Simulated single fault conditions (B.4)

Simulated Abnormal operating condition tests (B.3)

Transformer Abnormal Operation (G.5)

Power Supply Output Short-Circuit / Overload Test (5.3.7)

Summary of compliance with National Differences:


List of countries addressed

EU Group Differences, EU Special National Conditions, CA, DK, US, AU, NZ, IT, JP Explanation of used codes: CA = Canada, DK = Denmark, US = United States of America, AU = Australia, NZ = New Zealand, IT = Italy, JP = Japan

☑ The product fulfils the requirements of EN 62368-1:2014+A11:2017.

Copy of marking plate:

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.



6. BAR CODE & SERIAL NUMBER SPECIFICATIONS: CODE 39 FORMAT DOES NOT CONTAIN THE LETTER "O" SERIAL NUMBER SHOULD BE ASSIGNED BASED ON STANDARD PRACTICES AT FACTORY OF MANUFACTURER BUT MUST INCLUDE A UNIQUE IDENTIFIER TO DIFFERENTIATE ONE UNIT FROM ANOTHER.

Output Ratings Table

Output Ratings (DC)					
Voltage (V) Current (A) Max Power (W) Max Ambient (°C) Ma					
385 117		45,000	60		
385	82	31,500	70		

TEST ITEM PARTICULARS:	
Classification of use by:	☑ Ordinary person☑ Instructed person☑ Skilled person☐ Children likely to be present
Supply Connection:	☑ AC Mains☐ DC Mains☐ External Circuit - not Mains connected- ☐ ES1☐ ES2☑ ES3
Supply % Tolerance:	□ +10%/-10%□ +20%/-15%□ +%/%□ None
Supply Connection – Type:	 □ pluggable equipment type A - □ non-detachable supply cord □ appliance coupler □ direct plug-in □ mating connector ☑ pluggable equipment type B - □ non-detachable supply cord □ appliance coupler □ permanent connection ☑ mating connector □ other:
Considered current rating of protective device as part of building or equipment installation:	Not relying on protective device as part of the building installation, power supply has 90A circuit breakers for overcurrent protection. Installation location: ☑ building; ☐ equipment
Equipment mobility:	 ☐ movable ☐ hand-held ☐ transportable ☐ stationary ☐ for building-in ☐ direct plugin ☐ rack-mounting ☐ wall-mounted
Over voltage category (OVC):	□ OVC I □ OVC III □ OVC IV □ other:
Class of equipment:	☐ Class II ☐ Class III
Access location:	☐ restricted access location ☐ N/A Operator Accessible.
Pollution degree (PD):	□ PD1 □ PD3
Manufacturer's specified maxium operating ambient:	60°C at max. 45,000W or 70°C at max. 31,500W
IP protection class:	☑ IPX0 □ IP
Power Systems:	⊠ TN □ Π □ IT V _{L-L}
Altitude during operation (m)	☐ 2000 m or less ☐ 4000 m
Altitude of test laboratory (m):	☐ 2000 m or less ☐ 20 m
Mass of equipment (kg):	☑ 25 kg
POSSIBLE TEST CASE VERDICTS:	
- test case does not apply to the test object:	N/A

- test object does meet the requirement:	P (Pass)	
- test object does not meet the requirement:	F (Fail)	
TESTING:		
Date of receipt of test item:	3/12/2020 (31981014.300)	
	8/12/2019 (31981014.003)	
	05/20/2018, 08/08/2018, 10/24/2018 (31981014.001)	
Date (s) of performance of tests:	3/12/2020 (31981014.300)	
	8/12/2019 (31981014.003)	
	06/19/2018 - 11/14/2018 (31981014.001)	
GENERAL REMARKS:		
"(See Enclosure #)" refers to additional information		
"(See appended table)" refers to a table appended	to the report.	
Throughout this report a ☐ comma / ☒ point is u	sed as the decimal separator.	
Manufacturer's Declaration per sub-clause 4.2.5 of IECEE 02:		
The application for obtaining a CB Test Certificate	⊠ Yes	
includes more than one factory location and a declaration from the Manufacturer stating that the	☐ Not applicable	
sample(s) submitted for evaluation is (are)		
representative of the products from each factory has		
been provided		
When differences exist; they shall be identified in t		
Name and address of factory (ies)	TDK-Lambda (Malaysia) SDN BHD	
	LOT 2 & 3, BATU 9 3/4	
	KAWASAN PERINDUSTRIAN	
	BANDAR BARU JAYA GADING	
	26070 KUANTAN, MALAYSIA	
	TDK-Lambda America Inc.	
	405 Essex Road,	
	Neptune, NJ 07753 USA	

GENERAL PRODUCT INFORMATION:

Product Description:

The TPF non-isolated series is a 45kW 3Phase input 385VDC industrial power supply for distributed architecture for the semiconductor test market.

Unit is Class I, evaluated for use in Installation Category II and Pollution Degree 2 environments. The units have Hazardous Energy Level output and intended application is to be determined in end installation access location. Units consist of a steel box-type frame enclosure and steel cover.

Input range = 400/440/480VAC, 50/60Hz (nominal) 3 phase delta or wye

-40°C (start up) to +70°C operation

10 PSs in 2U 19" rack (not hot swap)

98% efficiency

OVP (Over Voltage Protection), OCP (Over Current Protection), OTP (Over Temperature Protection)

I2C option (PMBus communication protocol compatible)

ORing FET for redundancy

Output Ratings Table:

Output Ratings (DC)							
Voltage (V)	Voltage (V) Current (A) Max Power (W) Max Ambient (°C) Max						
385 117		45,000	60				
385	82	31,500	70				

History of CB report:

31981014.300 - Original IEC/EN 62368-1 CB report

ENERGY SOURCE IDENTIFICATION AND CLASSIFICATION TABLE:

(Note 1: Identify the following six (6) energy source forms based on the origin of the energy.)

(Note 2: The identified classification e.g., ES2, TS1, should be with respect to its ability to cause pain or injury on the body or its ability to ignite a combustible material. Any energy source can be declared Class 3 as a worse case classification e.g. PS3, ES3.

Electrically-caused injury (Clause 5):

(Note: Identify type of source, list sub-assembly or circuit designation and corresponding energy source classification)

Example: +5 V dc input ES1

Source of electrical energy	Corresponding classification (ES)	
Primary circuit	ES3	
Output circuit	ES3	

Electrically-caused fire (Clause 6):

(Note: List sub-assembly or circuit designation and corresponding energy source classification) Example: Battery pack (maximum 85 watts):

PS2

Source of power or PIS	Corresponding classification (PS)	
Power Supply Primary circuit	PS3	
Power Supply Output circuit	PS3	

Injury caused by hazardous substances (Clause 7)

(Note: Specify hazardous chemicals, whether produces ozone or other chemical construction not addressed as part of the component evaluation.)

Example: Liquid in filled component Glycol

Source of hazardous substances	Corresponding chemical	
No hazardous substances present in the product.	N/A	

Mechanically-caused injury (Clause 8)

(Note: List moving part(s), fan, special installations, etc. & corresponding MS classification based on Table 35.) Example: Wall mount unit MS2

Source of kinetic/mechanical energy	Corresponding classification (MS)	
Equipment Weight/Mass	MS3	
Sharp Edges	MS1	

Thermal burn injury (Clause 9)

(Note: Identify the surface or support, and corresponding energy source classification based on type of part, location, operating temperature and contact time in Table 38.)


Example: Hand-held scanner – thermoplastic enclosure TS1

Source of thermal energy	Corresponding classification (TS)	
Power Supply Enclosure	TS1	

Radiation (Clause 10)

(Note: List the types of radiation present in the product and the corresponding energy source classification.) Example: DVD – Class 1 Laser Product RS1

Type of radiation	Corresponding classification (RS)
No ionizing radiation produced in the product.	N/A



OVERVIEW OF EMPLOYED SAFE	GUARDS			
Clause	Possible Hazard			
5.1	Electrically-caused injury			
Body Part	Energy Source	Safeguards		
(e.g. Ordinary)	(ES3: Primary Filter circuit)	Basic	Supplementary	Reinforced (Enclosure)
Ordinary	ES3: primary circuit	Enclosure	Earth	Insulation/ Enclosure
Ordinary	ES3: power supply output	Enclosure	Earth	Insulation/ Enclosure
6.1	Electrically-caused fire			
Material part	Energy Source		Safeguards	
(e.g. mouse enclosure)	(PS2: 100 Watt circuit)	Basic	Supplementary	Reinforced
Input	PS3: Mains circuits	Components and selection of materials	Equipment Enclosure	Insulation/ Enclosure
Output	PS3: Output	Components and selection of materials	Equipment Enclosure	Insulation/ Enclosure
7.1	Injury caused by hazardou	s substances		
Body Part	Energy Source	Safeguards		
(e.g., skilled)	(hazardous material)	Basic	Supplementary	Reinforced
No hazardous substances present in the product.	-	-	-	-
8.1	Mechanically-caused injury	у		
Body Part	Energy Source	Safeguards		
(e.g. Ordinary)	(MS3:High Pressure Lamp)	Basic	Supplementary	Reinforced (Enclosure)
Ordinary	MS3: Mass of Equipment	Enclosure	-	-
Ordinary	MS1: Sharp Edges	Enclosure	-	-
9.1	Thermal Burn			
Body Part	Energy Source	Safeguards		
(e.g., Ordinary)	(TS2)	Basic	Supplementary	Reinforced
Ordinary	TS1: Accessible surfaces	Enclosure	-	-
10.1	Radiation			
Body Part	Energy Source		Safeguards	
(e.g., Ordinary)	(Output from audio port)	Basic	Supplementary	Reinforced
No ionizing radiation produced in the product.	-	-	-	-
Supplementary Information:	•	-	•	

Supplementary Information:

- (1) See attached energy source diagram for additional details.
- (2) "N" Normal Condition; "A" Abnormal Condition; "S" Single Fault