Ref. Certif. No.

JP-28935-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Switching Power Supply
Name and address of the applicant	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Name and address of the manufacturer	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Name and address of the factory Note: *When more than one factory, please report on page 2*	ALPS LOGISTICS FACILITIES CO LTD 593-1 NISHIOOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831 JAPAN ☒ Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark / Brand (if any)	TDK-Lambda
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	VS150E-xyz (x = 3, 5, 12, 15, 24, 48. y = / or blank, z = A, L or blank)
Additional information (if necessary may also be reported on page 2)	Evaluated to National Differences declared for: EN IEC 62368-1:2024/A11:2024 National Differences specified in the CB Test Report. ☐ Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2023
As shown in the Test Report Ref. No. which forms part of this Certificate	E122103-A6371-CB-1 issued on 2026-09-03

This CB Test Certificate is issued by the National Certification Body

UL Solutions

☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
☐ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
☒ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-09-04

Signature: M. Takagi

Masamichi Takagi

Ref. Certif. No.

JP-28935-UL

Factory(ies):
TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-1195
JAPAN

SENDAN ELECTRONICS MFG CO LTD
1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756
JAPAN

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN PAHANG
MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI JOHOR
MALAYSIA

TDK-LAMBDA (CHINA) ELECTRONICS CO LTD
NO.95, ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028
CHINA

Ratings:
Input:
100-120VAC, 50/60Hz, 2.4A (for models suffix x = 3)
3.2A (for the other models)

Output:
VS150E-3 DC 3.3V (2.97-3.63V), 30 A, 99.0W
VS150E-5 DC 5V (4.5 - 5.5V), 30A, 150W
VS150E-12 DC 12V (10.8 - 13.2V), 12.5A, 150W
VS150E-15 DC 15V (13.5 - 16.5V), 10.0A, 150W
VS150E-24 DC 24V (21.6 - 26.4V), 6.3A, 151W
VS150E-48 DC 48V (43.2 - 52.8V), 3.2A, 154W

Additional information (if necessary)

☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
☐ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
☒ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-09-04

Signature:

Masamichi Takagi