

DEMKO CERTIFICATE

Certificate No. D-06883-M2
Page 1/3
Date of Issue 2020-02-13

Certificate Holder TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-
MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN

Manufacturer TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-
MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN

Production site ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831
JAPAN

See Page 2

Certified Product Model Switching Power Supply
CME1500A-12, CME1500A-15, CME1500A-24, CME1500A-36,
CME1500A-48, CUS1500M-12, See Page 2

Trademark

TDK-Lambda

Rated Voltage / Frequency 100-240 Vac, 50-60 Hz

Rated Current / Power 19.0 A

Insulation Class Class I

Degree of protection (IP) IPX0

Tested acc. to EN 62368-1:2014/A11:2017, EN 62368-1:2014

Test Report No. E122103-A6022-CB-1 issued on 2020-02-04

Additional The report was revised to include technical modifications

Expire date 2028-11-06

Certification Manager
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D Mark Requirements. The Designated Certificate holder is entitled to use the d or for cables <DEMKO> for the Certified Product manufactured at the production site(s) identified above, in accordance with the D Mark Service Agreement, including without limitation the D Mark Testing and Certification Services Service Terms. Only those Products bearing the D Mark should be considered as being covered by UL's D Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior to the expiration date.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.ul-europe.com



Appendix DEMKO CERTIFICATE

Certificate No. D-06883-M2
Page 2/3
Date of Issue 2020-02-13

Model Details:

RWS1500B-12, RWS1500B-15, RWS1500B-24, RWS1500B-36, RWS1500B-48

Maybe followed by suffix "abcde" (a is /, b is R or S, c is CO2, d is FO, e is RF and "a", "b", "c", "d" and "e" may be blank)

CME1500A-12, CME1500A-15, CME1500A-24, CME1500A-36, CME1500A-48, CUS1500M-12, CUS1500M-15, CUS1500M-24, CUS1500M-36, CUS1500M-48, may be followed by suffix "vwxy" (v is /, w is CO2, x is RF, y is SF; and "v", "w", "x", "y" may be blank)

Production Sites:

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD
NO.15 TONGXIN RD, ZHAOFENG ECONOMIC DEVELOPMENT ZONE, LEYU TOWN ZHANGJIAGANG
JIANGSU215622
CHINA

TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-1195
JAPAN

SENDAN ELECTRONICS MFG CO LTD
1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756
JAPAN

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN PAHANG
MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI JOHOR
MALAYSIA

TDK-LAMBDA (CHINA) ELECTRONICS CO LTD
NO.95, ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028
CHINA

Additional Information:

for building-in

This Certificate replace earlier issued Demko certificate No. D-06883 issued on 2018-11-07 due to:

- Revision of Object/Part or Description, Type TLP385.
- Addition of evaluation for Australia / New Zealand and Japan National Differences.
- Change of factory address


Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul-europe.com



Appendix DEMKO CERTIFICATE

Certificate No. D-06883-M2
Page 3/3
Date of Issue 2020-02-13



Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul-europe.com

