

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Switch mode power supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE DEVON, EX34 8ES UNITED KINGDOM
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE DEVON, EX34 8ES UNITED KINGDOM
Name and address of the factory	TDK-LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE DEVON, EX34 8ES UNITED KINGDOM
<i>Note: When more than one factory, please report on page 2</i>	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See page 2
Trademark (if any)	TDK-Lambda
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Vega 450, Vega 650, Vega 900, Vega Lite 550 and Vega Lite 750.
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 61010-1:2010. National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61010-1:2010
As shown in the Test Report Ref. No. which forms part of this Certificate	E331788-D1000-1/A0/C0-CB issued on 2018-07-27

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2018-08-29

Signature:

For full legal entity names see www.ul.com/ncbnames

Jan-Erik Storgaard



Ref. Certif. No.

DK-76098-UL

Factories:

PANYU TRIO MICROTRONICS CO LTD
SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG, 511453
CHINA

Ratings:

Vega 450 and Vega Lite 550.

PSUs with cooling option F and without xFW and xEW options:

Input voltage: 94.5-240 V ac nom., 47-63 Hz, 8.5 A rms max.

All other PSUs:

Input voltage: 100-240 V ac nom., 47-63 Hz, 8.5 A rms max.

Vega 650, Vega Lite 750 and Vega 900.

PSUs with cooling option F and without xFW and xEW options:

Input voltage: 94.5-240 V ac nom., 47-63 Hz, 12 A rms max.

All other PSUs:

Input voltage: 100-240 V ac nom., 47-63 Hz, 11 A rms max.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-08-29

Signature:
Jan-Erik Storgaard