



Ref. Certif. No.

DK-106721-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Switch Mode Power Supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE, DEVON, EX34 8ES UNITED KINGDOM
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE, DEVON, EX34 8ES UNITED KINGDOM
Name and address of the factory <small>Note: When more than one factory, please report on page 2</small>	TDK-LAMBDA UK LTD KINGSLEY AVENUE ILFRACOMBE, DEVON, EX34 8ES UNITED KINGDOM
Ratings and principal characteristics	See Page 2
Trademark / Brand (if any)	TDK-Lambda
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	XMS-350, XMS-500, XMS-500P, XMS350, XMS500, XMS500A, See Page 2
Additional information (if necessary may also be reported on page 2)	National Differences specified in the CB Test Report. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005
As shown in the Test Report Ref. No. which forms part of this Certificate	E349607-D1000-3/A0/C0-CB issued on 2020-11-27

Additional Information on page 2

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-12-04

Signature:

Jan-Erik Storgaard

Model Details:

XMS350 or XMS-350 and XMS500, XMS-500, XMS500P, XMS-500P, XMS500A, XMS500AP series switch mode power supplies (see report Model Differences for details of nomenclature)

Factories:

PANYU TRIO MICROTRONIC CO. LTD
SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG
CHINA

TRIO-TRONICS (THAILAND) LTD.

7/295 MU. 6 MAP YANG PHON SUB-DISTRICT PLUAK DAENG DISTRICT RAYONG PROVINCE
THAILAND

Ratings:

XMS350, XMS-350: 100-240Vac nom., 47-63Hz, 5.3A rms max.

XMS500, XMS-500, XMS500P, XMS-500P, XMS500A, XMS500AP: 100-240Vac nom., 47-63Hz, 7A rms max.
(see report Model Differences for details of nomenclature)

Additional Information:

Risk Management requirements of the standard were not addressed.

Additionally evaluated to EN 60601-1:2006/ A1:2013/ A12:2014.

Additional information (if necessary)

- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-12-04

Signature:


Jan-Erik Storgaard