

DEMKO CERTIFICATE

Certificate No.	D-06595-M3
Page	1/5
Date of Issue	2022-01-24
Certificate Holder	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI, NIIGATA, 940-1195 JAPAN
Manufacturer	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI, NIIGATA, 940-1195 JAPAN
Production site	TDK-LAMBDA CORP 2704-1 SETTAYA-MACHI NAGAOKA-SHI, NIIGATA-KEN, 940-1195 JAPAN
Certified Product	See Page 2 for additional information Switching Power Supply
Model	ZWS100BAF-abcdefgh See page 2 for additional Information
Trademark	TDK·Lambda
Ratings	Input: AC 100-240V, 50/60Hz, 1.0A (for models with suffix a = 3) 1.3A (other than models with suffix a = 3) See page 2 for additional ratings
Tested according to	EN 62368-1:2014, EN 62368-1:2014/A11:2017
Test Report No.	E122103-A6231-CB-1 issued on 2022-01-13
Additional	The report was revised to include technical modification. Additionally evaluated to EN 50178:1997. This Certificate replaces earlier issued certificate No. D-06595-A4 dated 2021-10-14 due to addition of reference information for alternate material of Input connector.
Expire date	2023-01-06

Certification Manager
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D-Mark Requirements. As specified in the respective appendix below the Designated Certificate holder is entitled to use the D-Mark, or its alternative for cables, for the Certified Product manufactured at the production site(s) identified above, in accordance with the D-Mark Service Agreement, including without limitation the D-Mark Testing and Certification Services Service Terms. Only those Products bearing the D-Mark should be considered as being covered by UL's D-Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the expiration date.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-06595-M3
Page 2/5
Date of Issue 2022-01-24

Factories:

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI SENAI, JOHOR, 81400
MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4
KAWASAN PERINDUSTRIAN
BANDAR BARU JAYA GADING KUANTAN, PAHANG, 26070
MALAYSIA

TDK-LAMBDA (CHINA) ELECTRONICS CO LTD
NO.95,ZHUJIANG RD, XINWU DISTRICT WUXI, JIANGSU, 214028
CHINA

ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI TSUKUBA-SHI, IBARAKI-KEN, 305-0831
JAPAN

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD
NO.15 TONGXIN RD, ZHAOFENG ECONOMIC DEVELOPMENT ZONE,
LEYU TOWN ZHANGJIAGANG, JIANGSU, 215622
CHINA

YOKOTE SEIKO CO.,LTD.
1-71 ARAYATORIKIMACHI AKITA-SHI, AKITA, 010-1633
JAPAN

Additional Model(s):

Series: ZWS100BAF-abcdefgh

a = 3, 5, 12, 15, 24, 36 or 48. b = "/" or blank. c = "R" or blank. d = "A", "L" or blank. e = "CO2" or blank, f = "FG" or blank. g = "FV" or blank, h = "FGM" or blank

Ratings:

Output:

DC3.3V, 20A ZWS100BAF-3
(DC 2.64V – 3.63V, max. 20A, max. 66.0W)
DC5V, 20A ZWS100BAF-5
(DC 4.0 – 5.5V, max. 20A, max. 100W)
DC12V, 8.5A ZWS100BAF-12
(DC 9.6 – 13.2V, max. 8.5A, max. 102W)
DC15V, 6.7A ZWS100BAF-15
(DC 12.0 – 16.5V, max. 6.7A, max. 100.5W)
DC24V, 4.3A ZWS100BAF-24

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-06595-M3

Page 3/5

Date of Issue 2022-01-24

(DC 19.2 – 26.4V, max. 4.3A, max. 103.2W)

DC36V, 2.8A ZWS100BAF-36

(DC 32.4 – 39.6V, max. 2.8A, max. 100.8W)

DC48V, 2.1A ZWS100BAF-48

(DC 38.4 – 52.8V, max. 2.1A, max. 100.8W)

Output voltage of parenthesis can be changed with the adjustable variable resistor (VR51) within the range.
Class I, IPX0, for building-in.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE


Certificate No. D-06595-M3

Page 4/5

Date of Issue 2022-01-24

Certification Mark D-Mark

The D-Mark, as displayed below, shall appear on certified products only. Except as specified below the Mark shall be legible and no Minimum size is specified.



The D-Mark may appear on a label, nameplate, or may be cast, stamped or molded into the product. When appearing on a label or nameplate, the Manufacturer's name or trademark along with a model number are also required on that same label or nameplate. If cast, stamped or molded, the Certificate Manufacturer's name or trademark and model number shall also appear elsewhere on the product

When putting the product on the EU market, the manufacturer's name, trademark or mark of origin must be affixed in a clearly visible location and position on the product, on the package and in the user manual. It can be affixed by label, be directly imprinted, or cast or molded into the product.

Where the size of the product does not allow the Mark, the manufacturer's name, trademark, mark of origin and model number to be legible, and appearance on a label is not desired, it is allowed to cast, stamp or mold the Mark into the product, in a size which is not visible to the naked eye, provided the legible Mark, the manufacturer's name, trademark or mark of origin and model number appears on the package and in the user manual

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-06595-M3

Page 5/5

Date of Issue 2022-01-24

Alternate certification Mark for cables

As an alternative to the D-Mark specified above the alternate D-Mark, displayed below, can appear on certified cables only. Minimum size is not specified, as long as the mark is legible.

<DEMKO>

The alternate D-Mark may be cast, stamped or molded into the cable and continue throughout the length of the cable as specified in the applicable cable standard.

All content shall be in accordance with the details provided on this D-Mark Certificate.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com

