

CUS100MB**SPECIFICATIONS**

CA833-01-01C

ITEMS		MODEL	CUS100 MB-5	CUS100 MB-12	CUS100 MB-15	CUS100 MB-18	CUS100 MB-24	CUS100 MB-28	CUS100 MB-36	CUS100 MB-48
1	Nominal Output Voltage	V	5	12	15	18	24	28	36	48
2	Maximum Output Current @ Convection cooling	A	12	6.7	5.4	4.5	4.2	3.6	2.8	2.1
	Maximum Output Current @ Force air cooling	A	16	8.4	6.7	5.6				
3	Maximum Output Power @ Convection cooling	W	60.0	80.4	81.0	81.0				
	Maximum Output Power @ Force air cooling	W	80.0	100.8	100.5	100.8				
4	Efficiency @ Convection cooling (Typ.) 115/230 VAC (*1)	%	83 / 84	87 / 89	88 / 89	88 / 89				
	Efficiency @ Force air cooling (Typ.) 115/230 VAC (*1)	%	81 / 83	87 / 88	87 / 89	87 / 89	88 / 90	88 / 90	88 / 90	88 / 90
5	Input Voltage Range (*2)	-					85 - 265 VAC (47-63Hz)			
6	Input Current @ Convection cooling (Typ.) 115/230 VAC (*1)	A	1.2 / 0.8		1.5 / 0.9				1.8 / 1.1	
	Input Current @ Force air cooling (Typ.) 115/230 VAC (*1)	A	1.5 / 0.9		1.8 / 1.1					
7	In-rush Current (Typ.) (*1)(*3)	A					30 / 60 at Cold Start			
8	Output Voltage Range	%					-10 / +10			
9	Maximum Ripple & Noise (*1)(*4)(*5)	mV	120	120	150	150	150	200	200	200
10	Maximum Ripple & Noise (0%~35% Load) (*4)(*5)	mV	240	280	280	280	280	400	400	480
11	Maximum Line Regulation (*4)(*6)	mV	20	48	60	72	96	112	144	192
12	Maximum Load Regulation (*4)(*7)	mV	40	96	120	144	192	224	288	384
13	No Load Power Consumption	W					< 0.5 @ 230VAC , Ta=25°C, Nominal Output Voltage			
14	Temperature Coefficient (*4)	-					Less than 0.02% / °C			
15	Over Current Protection (*8)	A	>16.9	> 8.7	> 7.0	> 5.8	> 4.4	> 3.7	> 2.9	> 2.2
16	Over Voltage Protection (*9)	V	5.75 - 7.25	13.8 - 17.4	17.25 - 21.75	20.7 - 26.1	27.6 - 34.8	32.2 - 40.6	41.4 - 52.2	55.2 - 69.6
17	Hold-up time (Typ.) (*1)	ms					10 / 60			
18	Leakage Current (*10)	-					0.3mA max @265VAC,60Hz			
19	Parallel Operation	-					No			
20	Series Operation	-					Possible			
21	Operating Temperature (*11)	-					-20°C ~ +70°C, start up at -30°C			
22	Operating Humidity	-					10 - 90%RH (No condensing)			
23	Storage Temperature	-					-40°C ~ +85°C			
24	Storage Humidity	-					10 - 90%RH (No condensing)			
25	Cooling (*12)	-					Convection or Force Air Cooling			
26	Withstand Voltage	-					Input-FG : 2kVAC (20mA) 1xMOPP, Input-Output : 4kVAC (20mA) 2xMOPP, Output-FG : 1.5kVAC (20mA) 1xMOPP			
27	Isolation Resistance	-					More than 100MΩ at 25°C,70%RH, Output - FG : 500VDC			
28	Vibration	-					At no operating, 10-500Hz (Sweep for 1min.) Maximum 19.6m/s ² X,Y,Z 1 hour each			
29	Shock	-					Less than 196m/s ² , MIL-STD-810F			
30	Safety	-					Approved by IEC/ES/CSA/EN 60601-1(cTUVus), IEC/UL/CSA/EN 62368-1(cURus), Designed to meet GB4943.1			
31	EMI (*1)	-					Designed to meet EN55011-B, EN55032-B, FCC-Class B			
32	Immunity	-					Designed to meet IEC61000-4-2 (Level 2,3), IEC61000-4-3 (Level 3), IEC61000-4-4 (Level 3), IEC61000-4-5 (Level 3,4), IEC61000-4-6 (Level 3), IEC61000-4-8 (Level 4), IEC61000-4-11			
33	Weight (Typ.)	g					Designed to meet IEC60601-1-2 Ed.4.1			
34	Size (L x W x H)	mm					101.6 x 50.8 x 25.4 (Refer to Outline Drawing)			

*Read instruction manual carefully, before using the power supply unit.

=NOTES=

*1. At 115VAC/230VAC, Ta=25°C, nominal output voltage and maximum output power.

*2. For cases where conformance to various safety specs (UL, CSA, EN) are required, input voltage range will be 100 ~ 240VAC (50-60Hz).

Output derating required when Vin is less than 115VAC, refer output derating curve for details.

*3. Not applicable for the in-rush current to noise filter for less than 0.2ms.

*4. Please refer to Fig. A for measurement of Vo, line and load regulation and ripple voltage.

*5. Ripple & noise are measured at 20MHz by using a 150mm twisted pair of load wires terminated with a 0.1uF and 100uF capacitor.

*6. 85~265VAC, constant load.

*7. No load - full load, constant input voltage.

*8. Hiccup with automatic recovery.

Avoid operating at over load or short circuit condition.

*9. OVP circuit shut down the output, manual reset (Re power on) to get output voltage.


*10. Measured by the each measuring method of UL, CSA, and EN (at 60Hz), Ta=25°C.

*11. Refer to output derating curve for details of output derating versus input voltage, ambient temperature and mounting method .

- Load (%) is percent of maximum output power or maximum output current. Do not exceed its derating of maximum Load.

- Maximum load start up at -30°C is possible. However, it may not fulfill all the specifications.

*12. Force air cooling with air velocity more than 1.2m/s (measured at component side of PCB, air must flow through component side).



CUS100MB**OUTPUT DERATING**


CA833-01-02A

OUTPUT DERATING VERSUS OPERATING AMBIENT TEMPERATURE (Ta)**1. CUS100MB-5**

Convection Cooling: Mounting A,B,C,D
 & Force Air Cooling: Mounting A,B,C,D,E


Ta (°C)	Load (%)
-20 - +40	100
50	90
60	75
70	50

Ta (°C)	Load (%)
-20 - +35	100
45	90
55	75
65	50

**2. CUS100MB-12, -15, -18**

Convection and Force Air Cooling
 Mounting: A,B,C,D,E

Ta (°C)	Load (%)
-20 - +50	100
70	50



CUS100MB**OUTPUT DERATING**

CA833-01-03A

3. CUS100MB-24

Convection Cooling


Mounting: A,B,C,D,E

Ta (°C)	Load (%)
-20 - +40	100
70	40

Force Air Cooling

Mounting: A,B,C,D,E

Ta (°C)	Load (%)
-20 - +50	100
70	50

**4. CUS100MB-28**

Convection Cooling

Mounting: A,B,C,D

Ta (°C)	Load (%)
-20 - +40	100
50	80
70	40


Mounting: E

Ta (°C)	Load (%)
-20 - +35	100
50	80
70	40

Force Air Cooling

Mounting: A,B,C,D,E

Ta (°C)	Load (%)
-20 - +50	100
70	50



CUS100MB

OUTPUT DERATING

CA833-01-04

5. CUS100MB-36

Convection Cooling


Mounting: A,B,C,D,E

Ta (°C)	Load (%)
-20 - +35	100
50	80
70	40

Force Air Cooling

Mounting: A,B,C,D,E

Ta (°C)	Load (%)
-20 - +50	100
70	50

**6. CUS100MB-48**

Convection Cooling


Mounting: A,B,C,D,E

Ta (°C)	Load (%)
-20 - +30	100
50	80
70	40

Force Air Cooling

Mounting: A,B,C,D,E

Ta (°C)	Load (%)
-20 - +50	100
70	50



CUS100MB**OUTPUT DERATING**

CA833-01-05

OUTPUT DERATING VERSUS INPUT VOLTAGE

CUS100MB-5

Mounting A,B,C,D,E

Input Voltage (VAC)	Load (%)
85	80
100~265	100

CUS100MB-12, -15, -18, -24, -28, -36, -48

Mounting A,B,C,D,E

Input Voltage (VAC)	Load (%)
85	80
115~265	100

