

HWS100A/A

SPECIFICATIONS

A258-01-01/A-C

ITEMS		MODEL	HWS100A -3/A	HWS100A -5/A	HWS100A -12/A	HWS100A -15/A	HWS100A -24/A	HWS100A -48/A	
1	Nominal Output Voltage	V	3.3	5	12	15	24	48	
2	Maximum Output Current	A	20	20	8.5	7	4.5	2.1	
3	Maximum Output Power	W	66.0	100.0	102.0	105.0	108.0	100.8	
4	Efficiency (Typ.) (*1)	100VAC	%	82	84	86	86	87	88
		200VAC	%	84	86	88	88	89	90
5	Input Voltage Range (*2)(*3)	-	85 - 265VAC (47 - 63Hz) or 120 - 370VDC						
6	Input Current (Typ.) (*1)	A	0.9/0.45	1.3/0.65					
7	Inrush Current (Typ.) (*1)(*4)	-	14A at 100VAC, 28A at 200VAC, Ta=25°C, Cold Start						
8	PFHC	-	Designed to meet IEC61000-3-2						
9	Power Factor (Typ.) (*1)	-	0.96/0.89	0.98/0.93					
10	Output Voltage Range	V	2.97 - 3.96	4.0 - 6.0	9.6 - 14.4	12.0 - 18.0	19.2 - 28.8	38.4 - 52.8	
11	Maximum Ripple & Noise (*5)	0≤Ta<70°C	mV	120	120	150	150	150	200
		-10≤Ta<0°C	mV	160	160	180	180	180	240
12	Maximum Line Regulation (*6)	mV	20	20	48	60	96	192	
13	Maximum Load Regulation (*7)	mV	40	40	96	120	150	240	
14	Temperature Coefficient	-	Less than 0.02% / °C						
15	Over Current Protection (*8)	A	21.0 ≤	21.0 ≤	8.92 ≤	7.35 ≤	4.72 ≤	2.20 ≤	
16	Over Voltage Protection (*9)	V	4.13 - 4.95	6.25 - 7.25	15.0 - 17.4	18.8 - 21.8	30.0 - 34.8	55.2 - 64.8	
17	Hold-up Time (Typ.) (*1)	-	20ms						
18	Leakage Current (*10)	-	Less than 0.5mA. 0.2mA (Typ) at 100VAC / 0.4mA (Typ) at 230VAC						
19	Remote Sensing	-	Possible						
20	Parallel Operation	-	-						
21	Series Operation	-	Possible						
22	Operating Temperature (*11)	-	-10 to +70°C (-10 to +50°C:100%, +60°C:60%, +70°C:20%)						
23	Operating Humidity	-	30 to 90%RH (No Condensing)						
24	Storage Temperature	-	-30 to +85°C						
25	Storage Humidity	-	10 to 95%RH (No Condensing)						
26	Cooling	-	Convection Cooling						
27	Withstand Voltage	-	Input - FG : 2kVAC (20mA), Input - Output : 3kVAC (20mA) Output - FG : 500VAC (20mA) for 1min						
28	Isolation Resistance	-	More than 100MΩ at 25°C and 70%RH Output - FG : 500VDC						
29	Vibration	-	At no operating, 10 - 55Hz (Sweep for 1min) 19.6m/s ² Constant, X,Y,Z 1hour each.						
30	Shock	-	Less than 196.1m/s ²						
31	Safety	-	Approved by UL62368-1, CSA62368-1, EN62368-1, UL60950-1, CSA60950-1, EN60950-1 (Expire date of 60950-1 : 20/12/2020) UL508, CSA C22.2 No.107.1-01. Designed to meet Den-an Appendix 8 at 100VAC only.						
32	Line DIP	-	Designed to meet SEMI-F47 (200VAC Line only)						
33	Conducted Emission (*12)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B						
34	Radiated Emission (*12)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B						
35	Immunity (*12)	-	Designed to meet IEC61000-6-2 IEC61000-4-2, -3, -4, -5, -6, -8, -11						
36	Weight (Typ)	-	470g						
37	Size (W x H x D)	mm	33.5 x 83 x 160.5 (Refer to Outline Drawing)						

*Read instruction manual carefully, before using the power supply unit.

=NOTES=

*1. At 100VAC/200VAC, Ta=25°C, nominal output voltage and maximum output power.

*2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 - 240VAC(50 - 60Hz).

*3. Output derating needed when input voltage less than 90VAC. Refer to OUTPUT DERATING CURVE (A258-01-02/A-).

*4. Not applicable for the inrush current to Noise Filter for less than 0.2ms.

*5. Measure with JEITA RC-9131B probe, Bandwidth of scope :100MHz.

*6. 85 - 265VAC, constant load.

*7. No load-Full load, constant input voltage.

*8. Constant current limit and Hiccup with automatic recovery.

Avoid to operate at over load or short circuit condition.

*9. OVP circuit will shut down output, manual reset (Re power on).

*10. Measured by the each measuring method of UL, CSA, EN and Den-an (at 60Hz), Ta=25°C.

*11. Output Derating

- Derating at standard mounting. Refer to OUTPUT DERATING CURVE (A258-01-02/A-).

- Load (%) is percent of maximum output power or maximum output current, do not exceed its derating of maximum load.

*12. The power supply is considered a component which will be installed into a final equipment.

The final equipment should be re-evaluated that it meets EMC directives.

HWS100A/A

OUTPUT DERATING

A258-01-02/A

Ta (°C)	LOAD (%)			
	MOUNTING A	MOUNTING B	MOUNTING C	MOUNTING D
-10 - +30	100	100	100	100
35	100	100	92	100
50	100	65	65	65
60	60	37	37	42
70	20	10	10	20

*Refer to dotted line for output derating curve, when input voltage range is " $85 \leq V_{in} < 90$ " for the MOUNTING A.

