## **SPECIFICATIONS**

## A226-01-01/ME

MODEL				HWS50	HWS50	HWS50	HWS50	HWS50
ITEMS				-5/ME	-12/ME	-15/ME	-24/ME	-48/ME
1 Nominal Output Voltage			V	5	12	15	24	48
2 N				10	4.3	3.5	2.2	1.1
	Maximum Output Power		W	50	51.6	52.5	52.8	52.8
4 F	Efficiency (Typ) (*1)	100VAC	%	82	81	81	82	83
		200VAC	%	84	83	83	84	85
	5 Input Voltage Range (*2)			85 - 265VAC (47 - 63Hz) or 120 - 370VDC				
	6 Input Current (100/200VAC)(Typ) (*1) A			0.7/0.35				
	Inrush Current(Typ) (*3)			14A at 100VAC, 28A at 200VAC, Ta=25°C, Cold Start				
	PFHC			Designed to meet IEC61000-3-2				
	Voltage Fluctuations / Flicker Emissions			Designed to meet IEC61000-3-3				
	Power Factor (100/200VAC)(Typ) (*1) -			0.99/0.95				
	Output Voltage Range		V	4.0 - 6.0	9.6 - 14.4	12.0 - 18.0	19.2 - 28.8	38.4 - 52.8
12 N	Maximum Ripple & Noise	0 <u>&lt;</u> Ta <u>&lt;</u> 70°C		120	150	150	150	200
		-10 <u>&lt;</u> Ta<0°C		160	180	180	180	240
	Maximum Line Regulation	(*5)		20	48	60	96	192
	Maximum Load Regulation	(*6)	mV	40	96	120	192	384
	Temperature Coefficient -			Less than 0.02% / °C				
	Over Current Protection	(*7)	Α	10.5 <u>≤</u>	4.51 ≤	3.67 ≤	2.31 ≤	1.15 <u>&lt;</u>
	Over Voltage Protection	(*8)	V	6.25 - 7.25	15.0 - 17.4	18.8 - 21.8	30.0 - 34.8	55.2 - 64.8
	Hold-up Time (Typ)	(*9)	-	20ms				
	Leakage Current	(*10)	-	Less than 0.5mA. 0.2mA(Typ) at 100VAC / 0.4mA(Typ) at 230VAC				
	Remote Sensing		-	-				
	rallel Operation							
	Series Operation -			Possible				
	Operating Temperature (*11) -			-10 to +70°C (-10 to +50°C:100%,+60°C:60%,+70°C:20%)				
	Operating Humidity		30 to 90% RH (No dewdrop)					
	Storage Temperature -			-30 to +85°C				
	Storage Humidity -			10 to 95%RH (No dewdrop)				
	Cooling -			Convection cooling				
28 V	Withstand Voltage -			Input - FG : 2kVAC (20mA), Input - Output : 3kVAC (20mA)				
oxdot				Output - FG: 500VAC (100mA) for 1min				
	Isolation Resistance		-	More than $100 \text{M}\Omega$ at $25^{\circ}\text{C}$ and $70\%\text{RH}$ Output - FG : $500 \text{VDC}$				
30 V	Vibration		-	At no operating, 10 - 55Hz (Sweep for 1min)				
				19.6m/s <sup>2</sup> Constant, X,Y,Z 1hour each.				
	Shock (In package)		-	Less than 196.1m/s <sup>2</sup>				
	Safety	(*12)	-	Approved by UL60601-1, EN60601-1, CSA-C22.2 No.601.1-M90				
	Line DIP		-	Designed to meet SEMI-F47 (200VAC Line only)				
	Conducted Emission		-	Designed to meet EN55011/EN55022-B, FCC-B, VCCI-B				
	Radiated Emission		-	Designed to meet EN55011/EN55022-B, FCC-B, VCCI-B				
36 I	Immunity							
		-5(Level 3,4), -6(Level 4), -11						
	Weight(Typ.)	280g						
38 5	Size (W x H x D)		mm		26.5 x 82 x 12	20 (Refer to Out	line Drawing)	

\*Read instruction manual carefully, before using the power supply unit.

=NOTES=

- \*1. At 100/200VAC, Ta=25°C and maximum output power.
- \*2. For cases where conformance to various safety specs (UL, EN, CSA) are required, to be described as 100 230VAC(50/60Hz).
- \*3. Not applicable for the in-rush current to Noise Filter for less than 0.2ms.
- \*4. Measure with JEITA RC-9131A probe, Bandwidth of scope :100MHz.
- \*5. 85 265VAC, constant load.
- \*6. No load-Full load, constant input voltage.
- \*7. Constant current limit and Hiccup with automatic recovery.

  Not operate at over load or dead short condition for more than 30seconds.
- \*8. OVP circuit will shutdown output, manual reset (Re power on).
- \*9. At 100/200VAC, nominal output voltage and maximum output current.
- \*10. Measured by the each measuring method of UL,EN and CSA(at 60Hz).

When using it as a patient care equipment, all outer surfaces of the equipment shall be constructed of nonconductive material. See clause 19.5DV.2 of UL60601-1.

- \*11. Ratings Derating at standard mounting.
  - Load (%) is percent of maximum output power or maximum output current, whichever is greater.
  - As for other mountings, refer to derating curve (A226-01-02\_).
- \*12. As for UL60601-1, EN60601-1 and CSA-C22.2 No.601.1-M90, basic insulation.