

**HWS50A/B**

A257-01-01/B-A

**SPECIFICATIONS**

ITEMS		MODEL	HWS50A -3/B	HWS50A -5/B	HWS50A -12/B	HWS50A -15/B	HWS50A -24/B	HWS50A -48/B
1	Nominal Output Voltage	V	3.3	5	12	15	24	48
2	Maximum Output Current	A	10	10	4.3	3.5	2.2	1.1
3	Maximum Output Power	W	33.0	50.0	51.6	52.5	52.8	52.8
4	Efficiency (Typ.) (*1)	100VAC	% 76	82	83	83	84	84
		200VAC	% 78	84	85	86	87	86
5	Input Voltage Range (*2)	-	85 - 265VAC (47 - 63Hz) or 120 - 370VDC					
6	Input Current (Typ.) (*1)	A	0.45/0.25 0.65/0.35					
7	Inrush Current (Typ.) (*1)(*3)	-	14A at 100VAC, 28A at 200VAC, Ta=25°C, Cold Start					
8	PFHC	-	Designed to meet IEC61000-3-2					
9	Power Factor (Typ.) (*1)	-	0.96/0.85 0.97/0.91					
10	Output Voltage Range	V	2.97 - 3.96	4.0 - 6.0	9.6 - 14.4	12.0 - 18.0	19.2 - 28.8	38.4 - 52.8
11	Maximum Ripple & Noise (*4)	0≤Ta≤70°C	mV 120	120	150	150	150	200
		-10≤Ta<0°C	mV 160	160	180	180	180	240
12	Maximum Line Regulation (*5)	mV	20	20	48	60	96	192
13	Maximum Load Regulation (*6)	mV	40	40	96	120	150	240
14	Temperature Coefficient	-	Less than 0.02% / °C					
15	Over Current Protection (*7)	A	10.5 ≤	10.5 ≤	4.51 ≤	3.67 ≤	2.31 ≤	1.15 ≤
16	Over Voltage Protection (*8)	V	4.13 - 4.95	6.25 - 7.25	15.0 - 17.4	18.8 - 21.8	30.0 - 34.8	55.2 - 64.8
17	Hold-up Time (Typ.) (*1)	-	20ms					
18	Leakage Current (*9)	-	Less than 0.5mA. 0.2mA (Typ) at 100VAC / 0.4mA (Typ) at 230VAC					
19	Remote Sensing	-	-					
20	Parallel Operation	-	-					
21	Series Operation	-	Possible					
22	Operating Temperature (*10)	-	-10 to +70°C (-10 to +50°C:100%, +60°C:70%, +70°C:40%)					
23	Operating Humidity	-	30 to 90%RH (No Condensing)					
24	Storage Temperature	-	-30 to +85°C					
25	Storage Humidity	-	10 to 95%RH (No Condensing)					
26	Cooling	-	Convection Cooling					
27	Withstand Voltage	-	Input - FG : 2kVAC (20mA), Input - Output : 3kVAC (20mA) Output - FG : 500VAC (20mA) for 1min					
28	Isolation Resistance	-	More than 100MΩ at 25°C and 70%RH Output - FG : 500VDC					
29	Vibration	-	At no operating, 10 - 55Hz (Sweep for 1min) 19.6m/s <sup>2</sup> Constant, X,Y,Z 1hour each.					
30	Shock	-	Less than 196.1m/s <sup>2</sup>					
31	Safety	-	Approved by UL62368-1, CSA62368-1, EN62368-1, UL60950-1, CSA60950-1, EN60950-1 (Expire date of 60950-1 : 20/12/2020) Designed to meet Den-an Appendix 8 at 100VAC only.					
32	Line DIP	-	Designed to meet SEMI-F47 (200VAC Line only)					
33	Conducted Emission (*11)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B					
34	Radiated Emission (*11)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B					
35	Immunity (*11)	-	Designed to meet IEC61000-6-2 IEC61000-4-2, -3, -4, -5, -6, -8, -11					
36	Weight (Typ.)	-	260g					
37	Size (W x H x D)	mm	26.5 x 82 x 120 ( Refer to Outline Drawing )					

\*Read instruction manual carefully, before using the power supply unit.

=NOTES=

\*1. At 100VAC/200VAC, Ta=25°C, nominal output voltage and maximum output power.

\*2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 - 240VAC(50 - 60Hz).

\*3. Not applicable for the inrush current to Noise Filter for less than 0.2ms.

\*4. Measure with JEITA RC-9131B probe, Bandwidth of scope :100MHz. (Specified at connector Pin)

\*5. 85 - 265VAC, constant load.

\*6. No load-Full load, constant input voltage. (Specified at connector Pin)

\*7. Hiccup with automatic recovery.

Avoid to operate at over load or short circuit condition.

\*8. OVP circuit will shut down output, manual reset (Re power on).

\*9. Measured by the each measuring method of UL, CSA, EN and Den-an (at 60Hz), Ta=25°C.

\*10. Output Derating

- Derating at standard mounting. Refer to OUTPUT DERATING CURVE (A257-01-02\_).

- Load (%) is percent of maximum output power or maximum output current, do not exceed its derating of maximum load.

\*11. The power supply is considered a component which will be installed into a final equipment.

The final equipment should be re-evaluated that it meets EMC directives.