

HWS150A/A

SPECIFICATIONS

A259-01-01/A-B

ITEMS		MODEL	HWS150A -3/A	HWS150A -5/A	HWS150A -12/A	HWS150A -15/A	HWS150A -24/A	HWS150A -48/A	
1	Nominal Output Voltage	V	3.3	5	12	15	24	48	
2	Maximum Output Current	A	30	30	13	10	6.5	3.3	
3	Maximum Output Power	W	99.0	150.0	156.0	150.0	156.0	158.4	
4	Efficiency (Typ.)	(*1) 100VAC	%	82	85	85	86	88	89
		200VAC	%	84	87	88	89	90	91
5	Input Voltage Range	(*2)(*3)	-						85 - 265VAC (47 - 63Hz) or 120 - 370VDC
6	Input Current (Typ.)	(*1)	A	1.3/0.65	1.9/0.95				
7	Inrush Current (Typ.)	(*1)(*4)	-						14A at 100VAC, 28A at 200VAC, Ta=25°C, Cold Start
8	PFHC	-	-						Designed to meet IEC61000-3-2
9	Power Factor (Typ.)	(*1)	-	0.96/0.89	0.98/0.93				
10	Output Voltage Range	V	2.97 - 3.96	4.0 - 6.0	9.6 - 14.4	12.0 - 18.0	19.2 - 28.8	38.4 - 52.8	
11	Maximum Ripple & Noise	0≤Ta≤70°C	mV	120	120	150	150	150	200
		(*5) -10≤Ta<0°C	mV	160	160	180	180	180	240
12	Maximum Line Regulation	(*6)	mV	20	20	48	60	96	192
13	Maximum Load Regulation	(*7)	mV	40	40	96	120	150	240
14	Temperature Coefficient	-	-						Less than 0.02% / °C
15	Over Current Protection	(*8)	A	31.5 ≤	31.5 ≤	13.6 ≤	10.5 ≤	6.82 ≤	3.46 ≤
16	Over Voltage Protection	(*9)	V	4.13 - 4.95	6.25 - 7.25	15.0 - 17.4	18.8 - 21.8	30.0 - 34.8	55.2 - 64.8
17	Hold-up Time (Typ.)	(*1)	-	-					20ms
18	Leakage Current	(*10)	-	-					Less than 0.5mA. 0.2mA (Typ) at 100VAC / 0.4mA (Typ) at 230VAC
19	Remote Sensing	-	-						Possible
20	Parallel Operation	-	-						-
21	Series Operation	-	-						Possible
22	Operating Temperature	(*11)	-	-					-10 to +70°C (-10 to +50°C:100%, +60°C:60%, +70°C:20%)
23	Operating Humidity	-	-						30 to 90%RH (No Condensing)
24	Storage Temperature	-	-						-30 to +85°C
25	Storage Humidity	-	-						10 to 95%RH (No Condensing)
26	Cooling	-	-						Convection Cooling
27	Withstand Voltage	-	-						Input - FG : 2kVAC (20mA), Input - Output : 3kVAC (20mA) Output - FG : 500VAC (20mA) for 1min
28	Isolation Resistance	-	-						More than 100MΩ at 25°C and 70%RH Output - FG : 500VDC
29	Vibration	-	-						At no operating, 10 - 55Hz (Sweep for 1min) 19.6m/s ² Constant, X,Y,Z 1hour each.
30	Shock	-	-						Less than 196.1m/s ²
31	Safety	-	-						Approved by UL/CSA/EN62368-1, EN62477-1 (OVCI)(24V only), UL/CSA60950-1, EN60950-1 (Expire date of 60950-1 : 20/12/2020), UL508, CSA C22.2 No.107.1-01. Designed to meet Den-an Appendix 8 at 100VAC only.
32	Line DIP	-	-						Designed to meet SEMI-F47 (200VAC Line only)
33	Conducted Emission	(*12)	-	-					Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B
34	Radiated Emission	(*12)	-	-					Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B
35	Immunity	(*12)	-	-					Designed to meet IEC61000-6-2 IEC61000-4-2, -3, -4, -5, -6, -8, -11
36	Weight (Typ)	-	-						520g
37	Size (W x H x D)	mm	-						42 x 82 x 160 (Refer to Outline Drawing)

*Read instruction manual carefully, before using the power supply unit.

=NOTES=

- *1. At 100VAC/200VAC, Ta=25°C, nominal output voltage and maximum output power.
- *2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 - 240VAC(50 - 60Hz).
- *3. Output derating needed when input voltage less than 90VAC. Refer to OUTPUT DERATING CURVE (A259-01-02/A-).
- *4. Not applicable for the inrush current to Noise Filter for less than 0.2ms.
- *5. Measure with JEITA RC-9131B probe, Bandwidth of scope :100MHz.
- *6. 85 - 265VAC, constant load.
- *7. No load-Full load, constant input voltage.
- *8. Constant current limit and Hiccup with automatic recovery.
Avoid to operate at over load or short circuit condition.
- *9. OVP circuit will shut down output, manual reset (Re power on).
- *10. Measured by the each measuring method of UL, CSA, EN and Den-an (at 60Hz), Ta=25°C.
- *11. Output Derating
- Derating at standard mounting. Refer to OUTPUT DERATING CURVE (A259-01-02/A-).
- Load (%) is percent of maximum output power or maximum output current, do not exceed its derating of maximum load.
- *12. The power supply is considered a component which will be installed into a final equipment.
The final equipment should be re-evaluated that it meets EMC directives.

HWS150A/A

OUTPUT DERATING

A259-01-02/A

Ta (°C)	LOAD (%)	
	MOUNTING A	MOUNTING B, C, D
-10 - +30	100	100
50	100	60
60	60	35
70	20	10

*Refer to dotted line for output derating curve, when input voltage range is " $85 \leq V_{in} < 90$ " for the MOUNTING A.

