HWS80/A

SPECIFICATIONS

A233-01-01/A-B

MODEL	HWS80	HWS80	HWS80	HWS80	HWS80	HWS80		
ITEMS		-3/A	-5/A	-12/A	-15/A	-24/A	-48/A	
1 Nominal Output Voltage		3.3	5	12	15	24	48	
2 Maximum Output Current		16	16	6.7	5.4	3.4	1.7	
3 Maximum Output Power		52.8	80	80.4	81	81.6	81.6	
4 Efficiency (Typ) (*1) 100V		77	82	82	82	83	84	
200V	AC %	79	85	85	85	85	86	
5 Input Voltage Range (*2)		85 - 265VAC (47 - 63Hz) or 120 - 370VDC						
6 Input Current (100/200VAC)(Typ) (*1)		0.72/0.36 1.04/0.52						
7 Inrush Current(Typ) (*3)		14A at 100VAC, 28A at 200VAC, Ta=25°C, Cold Start						
8 PFHC		Designed to meet IEC61000-3-2						
9 Power Factor (100/200VAC)(Typ) (*1)		0.98/0.90 0.99/0.95						
10 Output Voltage Range	V	2.97-3.96	4.0-6.0	9.6-14.4	12.0-18.0	19.2-28.8	38.4-52.8	
	60°C mV		120	150	150	150	200	
(*4) -10 <u><</u> Ta<	<0°C mV		160	180	180	180	240	
	(*5) mV		20	48	60	96	192	
	(*6) mV	40	40	96	120	192	384	
14 Temperature Coefficient			Less than 0.02% / °C					
	(*7) A	16.8 <u><</u>	16.8 <u><</u>	7.04 <u><</u>	5.67 <u><</u>	3.57 <u><</u>	1.79 <u><</u>	
16 Over Voltage Protection	(*8) V	4.13-4.95	6.25-7.25	15.0-17.4	18.8-21.8	30.0-34.8	55.2-64.8	
17 Hold-up Time (Typ) (*9)		20ms						
18 Leakage Current (*10)		Less than 0.5mA. 0.2mA(Typ) at 100VAC / 0.4mA(Typ) at 230VAC						
9 Remote Sensing		Possible						
20 Parallel Operation			-					
21 Series Operation		Possible						
22 Operating Temperature (*11)		-10 to +60°C (-10 to +40°C:100%,+50°C:60%,+60°C:20%)						
23 Operating Humidity		30 to 90%RH (No dewdrop)						
24 Storage Temperature		-30 to +85°C						
25 Storage Humidity		10 to 95%RH (No dewdrop)						
26 Cooling		Convection Cooling						
27 Withstand Voltage		Input - FG : 2kVAC (20mA), Input - Output : 3kVAC (20mA)						
					AC (100mA)			
28 Isolation Resistance			More than $100M\Omega$ at 25° C and 70% RH Output - FG : 500 VDC					
29 Vibration		At no operating, 10 - 55Hz (Sweep for 1min)						
			19.6m		X,Y,Z 1hou	r each.		
30 Shock (In package)		Less than 196.1m/s ²						
31 Safety (*12) -		Approved by UL60950-1, CSA60950-1, EN60950-1, EN50178,						
		UL:	508, CSA C2				NAN	
32 Line DIP -		Designed to meet SEMI-F47 (200VAC Line only)						
33 Conducted Emission	-		Designed to meet EN55011/EN55022-B, FCC-B, VCCI-B					
	Radiated Emission -		Designed to meet EN55011/EN55022-B, FCC-B, VCCI-B					
35 Immunity -		Designed to meet IEC61000-4-2(Level 2,3), -3(Level 3), -4(Level 3),						
			-5(Level		el 3), -8(Leve	el 4), -11		
36 Weight(Typ.)				50	00g			
37 Size (W x H x D)	mn	1	33 x 82	x 160 (Refer	to Outline D	Orawing)		

^{*}Read instruction manual carefully, before using the power supply unit.

=NOTES=

- *1. At 100/200VAC, Ta=25°C and maximum output power.
- *2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 240VAC(50/60Hz).
- *3. Not applicable for the in-rush current to Noise Filter for less than 0.2ms.
- *4. Measure with JEITA RC-9131A probe, Bandwidth of scope :100MHz.
- *5.85 265VAC, constant load.
- *6. No load-Full load, constant input voltage.
- *7. Constant current limit and Hiccup with automatic recovery.

 Not operate at over load or dead short condition for more than 30seconds.
- *8. OVP circuit will shutdown output, manual reset (Re power on).
- *9. At 100/200VAC, nominal output voltage and maximum output current.
- *10. Measured by the each measuring method of UL,CSA,EN and DENAN(at 60Hz).
- *11. Ratings Derating at standard mounting.
 - Load (%) is percent of maximum output power or maximum output current, whichever is greater.
 - As for other mountings, refer to derating curve (A233-01-02/A-_).
- *12. As for DENAN, designed to meet at 100VAC.

HWS80/A

OUTPUT DERATING

A233-01-02/A

	LOAD(%)		
Ta(°C)	MOUNTING A	MOUNTING B,C,D	
-10 to +30	100	100	
40	100	80	
50	60	60	
60	20	20	



