TDK-Lambda

<u>JWS 70P</u>

SPECIFICATIONS

A180-01-01C

	ITEMS MODEL		JWS70P-24	JWS70P-48
	Nominal Output Voltage	V	24	48
	Average Output Current	Α	3	1.5
	Peak Output Current (*1)	Α	6	3
	Average Output Power	W	72	72
	Peak Output Power (*1)	W	144	144
	Efficiency (Typ) (*2)	%	80	80
	Input Voltage Range (*3) -		85 - 265VAC (47 - 63Hz)	
8	Input Current (100/200VAC)(Typ) (*2)		1.0/0.5	
	Inrush Current(Typ)		14A at 100VAC, 28A at 200VAC, Ta=25°C, Cold Start	
	PFHC	-	Designed to meet EN61000-3-2	
	Power Factor (100/200VAC)(Typ) (*2)	-	0.98/0.92	
	Output Voltage Range	V	21.6 - 26.4	43.2 - 52.8
13		mV	240	480
	(*4) -10 - 0°C		360	720
	Maximum Line Regulation (*5)	mV	96	192
	Maximum Load Regulation (*6)	mV	192	384
	Temperature Coefficient	-	Less than 0.02%/°C	
	Over Current Protection (*7)	Α	6.12 -	3.06 -
	Over Voltage Protection (*8)	V	27.6 - 32.4	55.2 - 64.8
	Hold-up Time (Typ) (*9)	-	20m	~
20	Leakage Current (*10)	-	0.75mA MAX, 0.2mA(Typ) at 100VAC / 0.44mA(Typ) at 230VAC	
	Thermal protection (*11)	-	Built-in	
	Remote Sensing	-	Possible	
23	Parallel Operation	-	-	
	Series Operation	-	Possible	
	Operating Temperature (*12)	-	-10 - +60°C (-10 - +50°C:100%, +60°C:60%)	
	Operating Humidity	-	30 - 90%RH (No dewdrop)	
	Storage Temperature	-	-30 - +85°C	
	Storage Humidity	-	10 - 95%RH (No dewdrop)	
	Cooling	-	Convection Cooling	
30	Withstand Voltage	-	Input - FG : 2kVAC (20mA), Input - Output : 3kVAC (20mA)	
31	Isolation Resistance	-	Output - FG : 500VAC (100mA) for 1min More than 100MΩ at 25°C and 70%RH Output - FG 500VDC	
	Vibration	-	At no operating, 10 - 55Hz (Sweep for 1min)	
52	v loration	-	19.6 m/s^2 Constant, X, Y, Z 1h each.	
32	Shock (In package)		Less than 196.1 m/s^2	
		-	Less than 196.1 m/s ⁻ Approved by UL60950-1, CSA C22.2 No.60950 & EN60950-1.	
54	34 Safety (*13)		Designed to meet DENAN.	
35	Conducted Emission	-	Designed to meet EN55011/EN55022-A, FCC-ClassA, VCCI-A.	
	Radiated Emission	-	Designed to meet EN55011/EN55022-A, FCC-ClassA, VCCI-A.	
	Weight(Typ.)	-	700g	
	Size (W x H x D)	mm	50 x 92 x 188 (Refer to Outline Drawing)	
		d instruction manual carefully, before using the nower supply unit		

*Read instruction manual carefully, before using the power supply unit.

=NOTES=

*1. Operating time at peak output is less than 10sec.(Duty<=0.5)

*2. At 100/200VAC, Ta=25°C and average output power.

*3. For cases where conformance to various safety specifications (UL, CSA, EN) are required, input voltage range will be 100 - 240VAC(50/60Hz).

- *4. Measure with JEITA RC-9131 probe, Bandwidth of scope :100MHz.
- *5. 85 265VAC , constant load.
- *6. No load Average load, constant input voltage.
- *7. Constant current limit with automatic recovery.
- *8. OVP circuit will shut down output, manual reset (Line recycle).
- *9. At 100/200VAC nominal output voltage and average output current.
- *10. Measured by the each measuring method of UL, CSA, EN and DENAN(at 60Hz).
- *11. Power Supply will recover in case of lower the temperature.
- *12. Ratings Derating at standard mounting.
 - Load (%) is percent of average output power or average output current, whichever is greater.
 - As for other mountings, refer to derating curve (A180-01-02_).
- *13. As for DENAN, designed to meet at 100VAC.

DENSEI-LAMBDA

<u>JWS 70P</u>

OUTPUT DERATING

