

# KS15 Specifications

PA759-01-01A

NEMIC-LAMBDA

\*: For delivery, contact to our sales office.

ITEMS	MODEL		KS15-5	KS15-12
1 Nominal Output Voltage	V		5	12
2 Minimum Output Current	A		0	0
3 Maximum Output Current	A		3.0	1.3
4 Maximum Output Power	W		15.0	15.6
5 Efficiency (typ)	(*1) %		74	76
6 Input Voltage Range	(*2)	-	85 ~ 132VAC ( 47~440Hz ) or 110 ~ 175VDC	
7 Input Current (typ)	(*1)	A	0.4A at 100VAC	
8 Inrush Current (typ)	A		10A at 100VAC, Ta = 25°C	
9 Output Voltage Range	-		FIXED ±5% (Max)	
10 Maximum Ripple & Noise	(*3)	mV	120	150
11 Maximum Line Regulation	(*3,*4)	mV	20	48
12 Maximum Load Regulation	(*3,*5)	mV	40	96
13 Maximum Temperature Drift	(*3,*6)	mV	50	120
14 Over Current Protection	(*7)	-	105% ~	
15 Over Voltage Protection	(*8)	-	110% ~	
16 Parallel Operation	-		_____	
17 Series Operation	-		Possible	
18 Hold-Up Time (typ)	-		17mS at 15W, 100VAC, Ta = 25°C	
19 Operating Temperature	-		-10°C ~ +70°C ( -10°C : 80%, 0~+50°C : 100%, +70°C : 25%)	
20 Operating Humidity	-		30 ~ 90%RH (No dewdrop)	
21 Storage Temperature	-		-30 ~ +85°C	
22 Storage Humidity	-		20%RH ~ 95%RH (No dewdrop)	
23 Cooling	-		Convection Cooling	
24 Withstand Voltage	-		Input-Output : 2kVAC(20mA), Input-FG : 2kVAC(20mA) Output-FG : 500VAC(100mA) for 1 minute each.	
25 Isolation Resistance	-		More than 100MΩ at 25°C and 70%RH Output-FG 500VDC	
26 Vibration	-		10~55Hz, Constant Amplitude 1.65mm p-p (Max 10G), sweep 1 Minute X,Y,Z 1 hour each	
27 Shock	-		Less than 50G for 11±5mS on ± (X, Y, Z) axis each 3 times	
28 Safety	-		Approved by UL1950, CSA234	
29 Conducted Radio Noise	-		Built to meet VCCI-Class A, FCC class B	
30 Weight	g		100g	
31 Size (WxHxD)	mm		45 x 20.5 x 64 (Refer to Outline Drawing)	

\* Read Instruction manual carefully, before using the power supply unit.

## = NOTES =

- \*1. At 100VAC and Maximum Output Power, Ta=25C.
- \*2. For cases where conformance to various safety specs (UL, CSA) are required to be described as 100-120VAC, 50/60Hz on name plate.
- \*3. Please refer to Fig. A for measurement determination of line & load regulation and output ripple & noise voltage.
- \*4. From 85~132VAC, constant load.
- \*5. From Min load - Full load (Maximum power), constant input Voltage.
- \*6. From 0~50°C, constant input voltage and load.
- \*7. Current limiting with automatic recovery. Avoid to operate over load or dead short for more than 30seconds.
- \*8. Over Voltage Clamping by Zener Diode.





Fig.A

# KS15 OUTPUT DERATING

NEMIC-LAMBDA

Ta (°C)	LOAD (%)				
	MOUNTING : A	MOUNTING : B	MOUNTING : C	MOUNTING : D	MOUNTING : E
-10	80	80	80	80	80
0 ~ +20	100	100	100	100	100
25	100	100	100	100	100
40	100	100	100	100	100
50	100	100	100	100	100
60	60	60	60	60	60
70	25	25	25	25	25

OUTPUT DERATING CURVE



MOUNTING : A

MOUNTING : B

MOUNTING : C

MOUNTING : D

MOUNTING : E

(STANDARD MOUNTING)

