## HWS80A/R

## **SPECIFICATIONS**


## A264-01-01/R-B

MODEL			HWS80A	HWS80A	HWS80A	HWS80A	HWS80A	HWS80A	
	ITEMS			-3/R	-5/R	-12/R	-15/R	-24/R	-48/R
1	Nominal Output Voltage		V	3.3	5	12	15	24	48
2	Maximum Output Current		A	16	16	6.7	5.4	3.4	1.7
3	Maximum Output Power		W	52.8	80.0	80.4	81.0	81.6	81.6
4		100VAC	%	81	83	85	85	86	87
		200VAC	%	83	85	87	87	88	89
5	Input Voltage Range	(*2)	ı		85 - 265	VAC (47 - 63	Hz) or 120 - 3	370VDC	
6	Input Current (Typ.)	(*1)	Α	0.72/0.36 1.04/0.52					
7	Inrush Current (Typ.)	(*1)(*3)	-	14A at 100VAC, 28A at 200VAC, Ta=25°C, Cold Start					
8	PFHC		-	Designed to meet IEC61000-3-2					
9	Power Factor (Typ.)	(*1)	-	0.96/0.87			0.98/0.91		
10	Output Voltage Range		V	2.97 - 3.96	4.0 - 6.0	9.6 - 14.4	12.0 - 18.0	19.2 - 28.8	38.4 - 52.8
11	Maximum Ripple & Noise	0 <u>≤</u> Ta <u>≤</u> 70°C	mV	120	120	150	150	150	200
		-10 <u>≤</u> Ta<0°C	mV	160	160	180	180	180	240
12	Maximum Line Regulation	(*5)	mV	20	20	48	60	96	192
13	Maximum Load Regulation	(*6)	mV	40	40	96	120	150	240
14	Temperature Coefficient		-				0.02% / °C		
15	Over Current Protection	(*7)	A	16.8 <u>≤</u>	16.8 ≤	7.04 <u>&lt;</u>	5.67 <u>≤</u>	3.57 ≤	1.79 <u>&lt;</u>
16	Over Voltage Protection	(*8)	V	4.13 - 4.95	6.25 - 7.25	15.0 - 17.4	18.8 - 21.8	30.0 - 34.8	55.2 - 64.8
17	Hold-up Time (Typ.)	(*1)	-				ms		
18	Leakage Current	(*9)	-	Less than 0.5mA. 0.2mA (Typ) at 100VAC / 0.4mA (Typ) at 230VAC					
19	Remote Sensing		-	Possible					
20	Remote ON/OFF Control	(*10)	-	Possible					
21	Parallel Operation		-	-					
22	Series Operation		-	Possible					
23	Operating Temperature	(*11)	-	-10 to +70°C (-10 to +50°C:100%, +60°C:80%, +70°C:60%)					
24	Operating Humidity		-	30 to 90%RH (No Condensing)					
25	Storage Temperature		-	-30 to +85°C					
26	Storage Humidity		-	10 to 95%RH (No Condensing)					
27	Cooling		-	Convection Cooling					
28	Withstand Voltage		-	Input - FG: 2kVAC (20mA), Input - Output: 3kVAC (20mA)				nA)	
				Output - FG: 500VAC (20mA) for 1min					
29	Isolation Resistance		-	More than 100MΩ at 25°C and 70%RH Output - FG: 500VDC At no operating, 10 - 55Hz (Sweep for 1min)					
30	Vibration		-						
					19.6ı		X,Y,Z 1hour	each.	
31	Shock		-	Less than 196.1m/s <sup>2</sup>					
32	Safety		-	- Approved by UL62368-1, CSA62368-1, EN62368-1, UL60950-1, CS EN60950-1 (Expire date of 60950-1 : 20/12/2020)			SA60950-1,		
				Designed to meet Den-an Appendix 8 at 100VAC only.					
33	Line DIP	(dia es	-	Designed to meet SEMI-F47 (200VAC Line only)					
34	Conducted Emission	(*12)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B					
35	Radiated Emission	(*12)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B					
36	Immunity	(*12)	-	Designed to meet IEC61000-6-2 IEC61000-4-2, -3, -4, -5, -6, -8, -11					
37	Weight (Typ)		-	420g 28.5 x 83 x 160.5 ( Refer to Outline Drawing )					
38	Size (W x H x D)		mm		28.5 x 83	x 160.5 ( Ref	er to Outline l	Drawing)	

\*Read instruction manual carefully, before using the power supply unit. =NOTES=

- \*1. At 100VAC/200VAC, Ta=25°C, nominal output voltage and maximum output power.
- \*2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 240VAC(50 60Hz).
- \*3. Not applicable for the inrush current to Noise Filter for less than 0.2ms.
- \*4. Measure with JEITA RC-9131B probe, Bandwidth of scope :100MHz.
- \*5. 85 265VAC, constant load.
- \*6. No load-Full load, constant input voltage.
- \*7. Constant current limit and Hiccup with automatic recovery. Avoid to operate at over load or short circuit condition.
- \*8. OVP circuit will shut down output, manual reset (Re power on).
- \*9. Measured by the each measuring method of UL, CSA, EN and Den-an (at 60Hz), Ta=25°C.
- \*10. As for ON/OFF control mode, see the right figure.
- \*11. Output Derating
  - Derating at standard mounting. Refer to OUTPUT DERATING CURVE (A264-01-02).
  - Load (%) is percent of maximum output power or maximum output current, do not exceed its derating of maximum load.
- \*12. The power supply is considered a component which will be installed into a final equipment.

  The final equipment should be re-evaluated that it meets EMC directives.



The control mode is shown below.

+R & -R terminal condition	Output condition
SW ON (Higher than 4.5V)	ON
SW OFF (Lower than 0.8V)	OFF

External voltage level : E	External resistance : R		
4.5 ~ 12.5VDC	No required		
12.5 ~ 24.5VDC	1.5kΩ		