**SPECIFICATIONS** 

## PA607-01-01E

	ITEMS	DDEL		LS200-3.3	LS200-5	LS200-7.5	LS200-12	LS200-15	LS200-24	LS200-36	LS200-48
1	Nominal Output Voltage	Ĩ	V	3.3	5	7.5	12	15	24	36	48
2	Maximum Output Current		Α	40	40	26.7	16.7	13.4	8.4	5.6	4.2
3	•	* 12)	A			-			10.4	6.9	-
4	Maximum Output Power		W	132	200	200.3	200.4	201	201.6	201.6	201.6
5	•	* 12)	W			-			250	250	-
6		(*1)	%	67 / 68	72 / 75	74 / 77	76 / 79	80 / 83	82 / 84	82 / 85	82 / 85
7		(*2)	-				VAC (47 ~ 6				
		` /		(Withstand 300VAC Surge for 5 seconds)							
8	Input Current (Typ.) (115/230VAC)	(*1)	Α			`		1.7			
9		(*3)	-	60A at 230VAC, Ta=25°C (Cold Start)							
10		(*1)	-		Designed to meet IEC61000-3-2, -3						
11		(*1)	-	> 0.98 / 0.95							
12	Output Voltage Range		V	3 ~ 3.6	4.75 ~ 5.5	6.8 ~ 8.2	10.8 ~ 14.4	13.5 ~ 16.5	22 ~ 28.8	32 ~ 40	42 ~ 57.6
	1 5 5	* 1, 4)	mV	80	80	80	120	120	120	150	200
14		* 5, 6)	mV	16	20	20	48	60	96	144	192
		- /	mV	50	50	50	96	120	192	288	384
	Temperature Coefficient		-	Less than 0.02%/°C							
17	Over Current Protection	(*8)	Α	105% - (n	naximum outp	ut current) for 3	3.3V ~ 15V &	48V and 105%	6 - (peak outpu	it current) for 2	4V ~ 36V
18	Over Voltage Protection	(*9)	V	3.8 ~ 4.45	5.75 ~ 6.75		15.1 ~ 17.75				60 ~ 72.5
19	Over Temperature Protection	(*9)	-	Yes							
	Remote ON/OFF		-	CN2: $3 \sim 12$ VDC POWER OFF, $< 0 \sim 0.8$ VDC POWER ON							
21	Hold-up Time (Typ.) (115/230VAC)	(*1)	-	20ms							
22	Leakage Current (	* 10)	-	< 1mA at 230VAC, 60Hz							
23	Series Operation		-	Possible							
24	Operating Temperature (	* 11)	-	- 25 ~ + 70 °C (Refer to Output Derating Curve)							
			-				20 ~ 90%RH	(No Dewdrop)	1		
26	Storage Temperature		-				-40°C ~	+85°C			
27	Storage Humidity		-				10 ~ 95%RH	(No Dewdrop)	1		
28	Cooling (	* 11)	-				Forced Ai	r (Exhale)			
29				Input - Output : 3.0kVAC (20mA), Input - FG : 1.5kVAC (20mA).							
			-			Output	- FG: 500VA	C (100mA) fo	or 1min.		
30	Isolation Resistance		-	Inpu	t - FG, Input -	Output and Ou	tput - FG: Mo	re than 100Mg	Ω (500VDC) a	t 25°C and 70°	%RH
31	Vibration		-			At no o	perating, 10 - 5	5Hz (sweep fo	or 1min)		
				19.6m/s2 Constant, X, Y, Z 1hour each.							
32	Shock (In package)		-	Less than 196.1m/s <sup>2</sup>							
33	Safety			Approved by UL62368-1, CSA62368-1, IEC62368-1,							
			_			IEC60	950-1, CE, UK	CA, IS 13252	(Part 1)		
	EMI		-	Designed to meet EN55011/EN55032-B, FCC-B							
35	Immunity		-		Desig	ned to meet EN	V61000-4-2 (L	evel 2,3), -3 (L	evel 3), -4 (Le	vel 3),	
					-5 (Lev	-5 (Level 3,4), -6 (Level 3), -8 (Level 4), -11					
36	Weight (Typ.)		g				70	00			
37	Warranty		-				3 Y	ear			
38	Dimension (L x W x H)		mm			199 x	98 x 41 (Refer	to Outline Dra	awing)		

st Read instruction manual carefully , before using the power supply unit.

- \* 1 : At Maximum Output Power, nominal input voltage,  $\,$  Ta=25°C.
- \* 2: For cases where conformance to various safety specs ( UL, CSA, IEC) are required, to be described as  $100 \sim 240 \text{VAC}$ , 50 / 60 Hz on name plate.
- st 3 : Not applicable for the in-rush current to Noise Filter for less than 0.2ms.
- \* 4: Ripple & noise are measured at 20MHz by using a 300mm twisted pair of load wires terminated with a 0.1uF film capacitor and a 47uF electrolytic capacitor.
- \* 5: Measure line & load regulation at output terminal M3.5 tapped point.
- \* 6:  $85 \sim 264 VAC$ , constant load.
- \* 7: No load ~ Full load (Maximum power ), constant input voltage.
- \* 8 : Constant current limiting with automatic recovery. Avoid to operate at overload and dead short for more than 30 seconds
- st 9 : OVP, OTP circuit will shutdown output, manual reset (Re-power on).
- \* 10: Measured by each measuring method of UL and IEC (at 60Hz), Ta=25  $^{\circ}\text{C}.$
- \* 11: Refer to Output Derating Curve (PA607-01-02-\_) for details of output derating versus ambient temperature.
- \* 12: Operating period at peak output current is less than 10sec., duty < 0.35%
- \* 13: All parameters NOT specifically mentioned are measured at 230VAC input, rated load and Ta=25°C.

<sup>=</sup> NOTES=

## PA607-01-02

*COOLING:	FORCED	$\Delta$ IR	(EXHALE)
· COOLING.	FURUED	AIK	LEADALE

*COOLING: FORCED AIR (EXHALE)		
Ta ( °C)	LOAD (%)	STANDARD MOUNTING
-25 ∼ + 50	100	STANDARD MOUNTING (A)
		(F N)(⊕)(-A -A +A +A)(A'')
70	60	
		THE WAY HE WOULD THE THE

LS200 - 3.3V, 5V, 7.5V, 12V, 15V, 24V, 36V & 48V

