### **ZWD100PAF/A SPECIFICATIONS**

#### PA572-01-01/A-B


#### (This specifications sheet also apply to option model /JA, /TA.)

MODEL			ZWD100PAF-0524/A		
ITEMS			V1 V2		
1 Nominal Output Voltage		V	5	24	
2 Maximum Output Current		Α	5	4	
3 Peak Output Current (100/200)	VAC) (*1)	Α	-	7 / 8	
4 Total Average Output Power		W	100		
5 Max. Peak Output Power (100/	200VAC) (*1)	W	- 168 / 192		
6 Total Peak Output Power (100/	200VAC) (*1)	W	172 / 196		
7 Efficiency (100/200VAC)	(Typ) (*2)	%	79 / 81		
8 Input Voltage Range	(*3)	-	85 - 265VAC (47-63Hz) or 120 - 370VDC		
9 Input Current (100/200VAC)	(Typ) (*2)	Α	1.28 / 0.65		
10 Inrush Current	(Typ) (*4)	-	15A at 100VAC, 30A at 200VAC, Ta=25°C, Cold Start		
11 PFHC		-	Designed to meet IEC61000-3-2		
12 Power Factor (100/200VAC)	(Typ) (*2)	-	0.99/0.95		
13 Output Voltage Accuracy	(*2)		4.9 - 5.1	23.52 - 24.48	
14 Output Voltage Adjustable Ran	ige	V	4.5 - 5.5	22.8 - 27.6	
15 Maximum Ripple & Noise	0≤Ta≤60°C	mV	120	150	
**	(*5)-10 <u>&lt;</u> Ta<0°C		160	180	
6 Maximum Line Regulation	(*5,6)	mV	20	96	
7 Maximum Load Regulation	(*5,7)	mV	40	150	
8 Temperature Coefficient		-	0.02	2%/o/°C	
9 Over Current Protection	(*8)	%	> 105	> 205	
20 Over Voltage Protection	(*9)	%	120 - 145	120 - 145	
1 Hold-Up Time	(Typ) (*2)	ms	40	20	
22 Leakage current	(*10)		0.75 max (Low leakage current option av	ailable> /FG. Refer to application note	
23 Remote ON/OFF Control		-	-	Possible	
24 Parallel Operation		-	Not possible		
25 Series Operation		-	Not possible		
26 Operating Temperature	(*11)	-	$-10 \text{ to} + 60 ^{\circ}\text{C}$		
	( )		Convection: $-10$ to $+40^{\circ}$ C : $100\%$ , $+50^{\circ}$ C : $50\%$ , $+60^{\circ}$ C : $0\%$		
27 Operating Humidity		-	20 - 90 %RH (No dewdrop)		
28 Storage Temperature		-	- 30 to +85°C		
29 Storage Humidity		-	10 - 95%RH (No dewdrop)		
30 Cooling		-	Convection cooling		
31 Withstand Voltage		-		A), Input - FG : 2.0kVAC (20mA)	
i wind voluge				AC (100mA) for 1 min.	
32 Isolation Resistance		-		nd 70%RH, Output - FG : 500VDC	
33 Vibration (Non-Operating)		-	$\frac{10-55\text{Hz}(\text{sweep for 1 min})}{10-55\text{Hz}(\text{sweep for 1 min})}$		
			Less than 19.6m/s <sup>2</sup> Constant, X, Y, Z 1 hour each		
34 Shock (In package)		-	Less than 19.011/s Constant, X, 1, 2 Thou each Less than 196.1m/s <sup>2</sup>		
35 Safety		-			
Survey	alety -		Approved by UL62368-1, CSA62368-1, EN62368-1,UL60950-1, CSA60950-1, EN60950-1 (Expire date of 60950-1 : 20/12/2020), EN50178,		
36 EMI		-	Designed to meet DEN-AN at 100VAC only		
37 Immunity		-	Complies with FCC-B, CISPR22-B, EN55032-B, VCCI-B		
38 Weight (Typ)			Designed to meet EN61000-4-2,-3,-4,-5,-6,-8,-11		
		g	780		
39 Size (W.H.D.)		mm	85 x 46 x 252 (Refer to Outline Drawing)		

\* Read instruction manual carefully, before using the power supply unit. = NOTES=


\* 1 : Operating period at peak output current is less than 10sec; Duty < 0.35. For peak load derating method, please refer to instruction manual for details. Component side

Fig. B



\* 3 : For cases where conformance to various safety specs ( UL, CSA, EN ) are required, to be described as 100 - 240VAC, 50 / 60Hz on name plate.

\* 4 : Not applicable for the in-rush current to Noise Filter for less than 0.2ms.




\* 6 : 85 - 132VAC and 170 - 265VAC, constant load.

\* 7 : No load - Full load, constant input voltage.

- \* 9 : OVP circuit will shutdown output, manual reset. (Line recycle) (OVP for V1, V1 & V2 shutdown, OVP for V2, only V2 shutdown)
- \*10: Measured by each measuring method of UL, CSA, EN and DEN-AN (at 60Hz).

\*11: At standard mounting method, Fig B.

- Load(%) is percent of maximum output load (Item 2 and 4), do not exceed derating in both Maximum Output Current and Power.
- For other mountings, refer to derating curve PA572-01-02/A
- When forced air cooling, refer to derating curve PA572-01-03/A\_



<sup>\* 8 :</sup> Current limiting with automatic recovery. Avoid to operate at overload or dead short for more than 30seconds.

# **OUTPUT DERATING**


### PA572-01-02/A


(This specifications sheet also apply to option model /JA, /TA.)

## ZWD100PAF-0524/A

#### **\*COOLING: CONVECTION COOLING**

LOADING CONDITION(%)						
Ta (°C)	Mounting A,B,C	Mounting D,E				
-10~30	100	100				
40	100	60				
50	50	20				
55	25	0				
60	0	-				





# **OUTPUT DERATING**

### PA572-01-03/A


(This specifications sheet also apply to option model /JA, /TA.)

## ZWD100PAF-0524/A

\*COOLING: FORCED AIR COOLING

	LOADING CONDITION (%)		
Ta (°C)	Mounting A,B,C,D,E		
-10~50	100		
60	50		

Recommended Minimum Air Velocity: 0.7m/s (Measured at component side of PCB, Air must flow through component side.)



( MOUNTING A )	( MOUNTING B )	( MOUNTING C )	( MOUNTING D )	(MOUNTING E)	
Component side	Input connector	Input connector CN1	Input connector CN1	Output connector CN2	