RWS1000B/R

A273-01-01/R-B

SPECIFICATIONS(1/2)

MODEL				RWS1000B -12/R	RWS1000B -15/R	RWS1000B -24/R	RWS1000B -36/R	RWS1000B -48/R
1	Nominal Output Voltage		V	12	15	24	36	48
2	Maximum Output Current		А	84	67	42	28	21
3	Maximum Output Power		W	1008	1005	1008	1008	1008
4	Efficiency (Typ)	100/115VAC	%	81/82	81/82	84/85	84/85	83/85
	(*13)		%	85/85	85/85	88/88	88/88	87/88
5	Input Voltage Range	(*2)(*11)	-		85 - 265VAC	(47 - 63Hz) or 1	20 - 340VDC	
6	Input Current (Typ) 100/115VAC		А	13 / 11				
	(*13)	200/230VAC	Α			7 / 5.5		
7	Inrush Current (Typ)	(*1)(*3))(*3) - 20A / 40A at 1st Inrus		Inrush , 60A / 60	rush , 60A / 60A at 2nd Inrush		
8	PFHC		-	Designed to meet IEC61000-3-2				
9	Power Factor (Typ) (*1)		-	0.98/0.95				
10	Output Voltage Range		V	10.2 - 13.8	12.8 - 17.2	20.4 - 28.8	30.6 - 41.4	40.8 - 57.6
11	Maximum Ripple & Noise	0 <u>≤</u> Ta <u>≤</u> 60°C	mV	150	150	180	250	300
	(*4)	-20 <u><</u> Ta<0°C	mV	180	180	200	300	400
12	Maximum Line Regulation	(*5)(*11)	mV	48	60	96	144	192
13	Maximum Load Regulation	(*6)(*11)	mV	96	120	144	216	288
14	Temperature Coefficient		-	Less than 0.02% / °C				
15	Over Current Protection	(*7)	Α	88.2 -	70.4 -	44.1 -	29.4 -	22.1 -
16	Over Voltage Protection	(*8)	V	14.4 - 17.4	18.0 - 21.8	30.0 - 36.0	43.2 - 52.2	60.0 - 72.0
17	Hold-up Time (Typ)	(*1)	-	20ms				
18	Leakage Current	(*9)	-	Less than 1.2mA				
19	Remote Sensing	(*14)	-	Possible				
20	Monitoring Signal	(*14)	-	Option				
21	Remote Control (*14)(*15)		-	Possible				
22	Parallel Operation (*14) -		-	Option				
23	Series Operation (*14)		-	Possible				
24	Operating Temperature (*10)(*11)		-	-20 - +60°C (-20 - +50°C:100%, +60°C:60%)				
25	Operating Humidity -		-	20 - 90%RH (No Condensing)				
26	Storage Temperature		-	-30 - +75°C				
27	Storage Humidity -		10 - 90%RH (No Condensing)					
28	Cooling		-	Forced Air Cooling				
29			-	Input - FG : 2kVAC (20mA), Input - Output : 4kVAC (20mA)				
			┟───╂	Output - FG : 1.5kVAC (20mA) for 1min				
30	Isolation Resistance		-	More than 100MΩ at 25°C and 70%RH Output to Chassis : 500VDC At no operating, 10 - 55Hz (Sweep for 1min)				
31	Vibration		-				• ·	
	<u>a</u> 1 1			19.6m/s ² Constant, X,Y,Z 1hour each.				
32	Shock		-	Less than 196m/s ² Approved by UL62368-1, CSA62368-1, EN62368-1, UL60950-1,				
33	Safety		-					
						1 (Expire date o		-
					-	Den-an Appendi		
34	Line DIP		-	Designed to meet SEMI-F47 (200VAC Line only)				
35	Conducted Emission	(*12)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B				
36	Radiated Emission	(*12)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B				
37	Immunity	(*12)	-	Designed to meet IEC61000-6-2 IEC61000-4-2, -3, -4, -5, -6, -8, -11				
38	Weight (Typ)							
39	Size (W x H x D)		mm		127 x 63 x 19	8 (Refer to Outl	ine Drawing)	


SPECIFICATIONS(2/2)

*Read instruction manual carefully, before using the power supply unit.

=NOTES=


- *1. At 100VAC/200VAC, Ta=25°C, nominal output voltage and maximum output power.
- *2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 240VAC(50-60Hz).
- *3. Not applicable for the in-rush current to Noise Filter for less than 0.2ms.
- *4. Please refer to Fig. A for measurement of Vo, line & load regulation and ripple voltage.
- *5. 85 265VAC, constant load.
- *6. No load-Full load, constant input voltage.
- *7. Constant current limit with automatic recovery. Over current condition for more than 5 seconds will cause the output to shut down. Avoid to operate at over load or short circuit condition.
- *8. OVP circuit will shut down output, manual reset (Re power on).
- *9. Measured by the each measuring method of UL, CSA, EN and Den-an(at 60Hz), Ta=25°C.
- *10. Output Derating
 - Refer to LOAD vs. AMBIENT TEMPERATURE(A273-01-02_).
 - Load (%) is percent of maximum output power or maximum output current, do not exceed its derating of maximum load.
- *11. Output derating needed when input voltage less than 90VAC. Refer to LOAD vs. INPUT VOLTAGE(A273-01-02_).
- *12. The power supply is considered a component which will be installed into a final equipment.
- The final equipment should be re-evaluated that it meets EMC directives.
- *13. Ta=25°C, nominal output voltage and maximum output power.
- *14. Refer to instruction manual(A273-04-01).
- *15. As for Remote control mode, please refer to Fig. B.

```
Fig.A
```



 $\begin{array}{l} C1:Film\ Cap.\ 0.1\mu F\\ C2:Elect.\ Cap.\ 47\mu F \end{array}$

Fig.B



+R & -R terminal condition	Output condition	Fan condition	
SW ON (Higher than 4.5V)	ON	Operate	
SW OFF (Lower than 0.5V)	OFF	Not Operate	

External voltage : E	External resistance : R		
4.5 ~ 12.5VDC	No required		
12.5 ~ 24.5VDC	1.5kΩ		