RWS150B/I

SPECIFICATIONS

A260-01-01/I

MODEL				RWS150B-12	RWS150B-24	RWS150B-48
_	Part No			RWS150B-12/I	RWS150B-24/I	RWS150B-48/I
1	Nominal Output Voltage		- V	12	24	48
2	Maximum Output Current		Ā	13	6.5	3.3
3	Maximum Output Power		W	156	156	158.4
4	Efficiency (Typ) (*1)(*11)	100/115VAC	%	84 / 84.5	86 / 86.5	86 / 86.5
'		200/230VAC	%	87 / 87.5	89 / 89.5	89 / 89.5
5	Input Voltage Range	(*2)(*11)	-		VAC (47 - 63Hz) or 120 - 3	
6	Input Current (Typ) 100/115VAC		Α	1.9/1.8		
	(*1)(*11)	200/230VAC	A	1.0 / 0.9		
7	Inrush Current (Typ) (*1)(*3)(*11)		-	16A at 100VAC, 32A at 200VAC, Ta=25°C, Cold Start		
8	PFHC		_	Designed to meet IEC61000-3-2		
9	Power Factor (Typ) (*1)(*11)		_	0.95 at 100VAC, 0.90 at 200VAC		
10	Output Voltage Range		V	10.8 - 13.8	21.6 - 27.6	43.2 - 52.8
11	Maximum Ripple & Noise	0 <u>≤</u> Ta <u>≤</u> 70°C		150	150	200
	(*4)	-20 <u><</u> Ta<0°C		180	180	300
12	Maximum Line Regulation	(*5)(*11)		48	96	192
13	Maximum Load Regulation	(*6)(*11)		96	192	384
14	Temperature Coefficient		_	Less than 0.02% / °C		
15	Over Current Protection	(*7)	Α	13.65 <	6.83 <	3.47 <u><</u>
16	Over Voltage Protection	(*8)	V	14.4 - 16.8	28.8 - 33.6	55.2 - 64.8
17	Hold-up Time (Typ)	(*12)	_		20ms	
18	Leakage Current	(*9)	-	Less than 0.75mA		
19	Parallel Operation		-	-		
20	Series Operation		-	Possible		
21	Operating Temperature (*10)(*11)		-	-20 to +70°C (-20°C:50%, -10 to +40°C:100%, +70°C:20%)		
22	Operating Humidity			30 to 90%RH (No Condensing)		
23	Storage Temperature			-30 to +75°C		
24	Storage Humidity			10 to 90%RH (No Condensing)		
25	Cooling		-	Convection Cooling		
26				Input - FG: 2kVAC (20mA), Input - Output: 3kVAC (20mA)		
				Output - FG: 500VAC (100mA) for 1min		
27	Isolation Resistance		-	More than $100M\Omega$ at 25°C and $70\%RH$ Output - FG : $500VDC$		
28				At no operating, 10 - 55Hz (Sweep for 1min)		
				19.6m/s ² Constant, X,Y,Z 1hour each.		
29	Shock		-	Less than 196.1m/s ²		
30	Safety		- Approved by UL62368-1, CSA62368-1, EN62368-1, UL60950-1, CSA60950-1,			
				UL508 (12V,24V), CSA C22.2 No.107.1-01. (12V,24V), IS13252 (Part 1).		
			Designed to meet Den-an Appendix 8 at 100VAC only.			
31	Line DIP		-	Designed to meet SEMI-F47 (200VAC Line only)		
32	Conducted Emission	(*13)	-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B		
33						
	3		1	Designed to meet IEC61000-6-2 IEC61000-4-2, -3, -4, -5, -6, -8, -11		
35	Weight (Typ)			480		
36	Size (W x H x D)			41 x 94 x 128 (Refer to Outline Drawing)		

*Read instruction manual carefully, before using the power supply unit.

=NOTES=

- *1. At Ta=25°C, nominal output voltage and maximum output power.
- *2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 240VAC (50-60Hz).
- *3. Not applicable for the inrush current to Noise Filter for less than 0.2ms.
- *4. Please refer to Fig. A for measurement of Vo, line & load regulation and ripple voltage.
- *5. 85 265VAC, constant load.
- *6. No load-Full load, constant input voltage.
- *7. 12V model: Constant current limit and hiccup with automatic recovery. 24V, 48V model: Constant current limit with automatic recovery. Avoid to operate at over load or short circuit condition.
- *8. OVP circuit will shut down output, manual reset (Re power on).
- *9. Measured by the each measuring method of UL, CSA, EN and Den-an(at 60Hz), Ta=25°C.

*10. Output Derating

- Derating at standard mounting. Refer to LOAD vs. AMBIENT TEMPERATURE (A260-01-02_).

- Load (%) is percent of maximum output power or maximum output current, do not exceed its derating of maximum load.

- *11. Output derating needed when input voltage less than 110VAC. Refer to LOAD vs. INPUT VOLTAGE (A260-01-02_).
- *12. At 110VAC/200VAC, Ta=25°C, nominal output voltage and maximum output power.
- *13. The power supply is considered a component which will be installed into a final equipment. The final equipment should be re-evaluated that it meets EMC directives.




Fig.A

C1 : Film Cap. 0.1μF C2 : Elect. Cap. 100μF