## ZWS150BAF/R

## **SPECIFICATIONS**

## A250-01-01/R-A


	0-01-01/K-A	MODEL		ZWS150BAF	ZWS150BAF	ZWS150BAF	ZWS150BAF	ZWS150BAF	ZWS150BAF
	ITEMS			-3/R	-5/R	-12/R	-15/R	-24/R	-48/R
1	Nominal Output Voltage		V	3.3	5	12	15	24	48
	Maximum Output Current		A	30	30	12.5	10.0	6.3	3.2
	Maximum Output Power		W	99.0	150.0	150.0	150.0	151.2	153.6
4		100VAC	%	82	85	85	86	88	89
٠ ا	l lineiency (1yp)	200VAC	%	84	87	88	89	90	91
5	Input Voltage Range	(*2)	-	85 - 265VAC (47 - 63Hz) or 120 - 370VDC					
6	Input Current (Typ)	(*1)	Α	1.3/0.65 1.9/0.95					
7	Inrush Current (Typ)	(*1)(*3)	_	14A at 100VAC, 28A at 200VAC, Ta=25°C, Cold Start					
8	PFHC		-	Designed to meet IEC61000-3-2					
9	Power Factor (Typ)	(*1)	-	0.96/0.89			0.98/0.93		
10	Output Voltage Range		V	2.97 - 3.63	4.5 - 5.5	10.8 - 13.2	13.5 - 16.5	21.6 - 26.4	39.5 - 52.8
11	Maximum Ripple & Noise	0≤Ta≤70°C	mV	120	120	150	150	150	200
	(*4)	-10 <u>≤</u> Ta<0°C	mV	160	160	180	180	180	240
12	Maximum Line Regulation	(*4)(*5)	mV	20	20	48	60	96	192
13	Maximum Load Regulation	(*4)(*6)	mV	40	40	96	120	150	240
14	Temperature Coefficient	(*4)	-			Less than	0.02% / °C	_	
15	Over Current Protection	(*7)	Α	31.5 -	31.5 -	13.13 -	10.5 -	6.62 -	3.36 -
16	Over Voltage Protection	(*8)	V	3.79 - 4.95	5.75 - 7.00	13.8 - 16.2	17.3 - 20.3	27.6 - 32.4	55.2 - 64.8
17	Hold-up Time (Typ)	(*1)	-	20ms					
18	Leakage Current	(*9)	-	Less than 0.5mA. 0.2mA(Typ) at 100VAC / 0.4mA(Typ) at 230VAC					
/	Remote Control	(*10)	-	Possible					
20	Parallel Operation		-	-					
21	Series Operation	(1.1.1)	-	Possible					
22	Operating Temperature	(*11)	-	Convection: -10 to +70°C (-10 to +50°C:100%, +60°C:75%, +70°C:50%)					
23	Operating Humidity		-	30 to 90%RH (No Condensing)					
24	Storage Temperature		-	-30 to +75°C					
25	Storage Humidity		-	10 to 90%RH (No Condensing)					
26	Cooling		-	Convection Cooling Input - FG: 2kVAC (10mA), Input - Output: 3kVAC (10mA)					
27	Withstand Voltage		-	Output - FG : 2kVAC (10mA), input - Output : 3kVAC (10mA)  Output - FG : 500VAC (20mA) for 1min					
28	Isolation Resistance		_	Output - FG: 300 VAC (20mA) for 1min  More than 100MΩ at 25°C and 70%RH Output - FG: 500VDC					
29	Vibration			At no operating, 10 - 55Hz (Sweep for 1min)					
23	Violation		_						
30	Shock		_	19.6m/s <sup>2</sup> Constant, X,Y,Z 1hour each.  Less than 196.1m/s <sup>2</sup>					
31	Safety		_	Less than 196.1m/s Approved by UL62368-1, CSA62368-1, EN62368-1, UL60950-1, CSA60950-1,					
51	l					date of 60950			
				11100					~ · · · · · · · ·
32	Conducted Emission		_	Designed to meet DENAN at 100VAC Only.  Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B					
33	Radiated Emission		-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B					
	Immunity		-	Designed to meet IEC61000-4-2(Level 2,3), -3(Level 3), -4(Level 3),					
34				8-					- ,,
34					-5(Leve	el 3,4), -6(Lev	el 3), -8(Level	l 4), -11	
34	Weight (Typ)		g		-5(Leve	el 3,4), -6(Lev	el 3), -8(Level 90	14), -11	


\*Read instruction manual carefully, before using the power supply unit. =NOTES=

- \*1. At 100VAC/200VAC, Ta=25°C, nominal output voltage and maximum output power.
- \*2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 240VAC(50/60Hz).
- \*3. Not applicable for the in-rush current to Noise Filter for less than 0.2ms.
- \*4. Please refer to Fig. A for measurement of Vo, line & load regulation and ripple voltage.
- \*5. 85 265VAC, constant load.
- \*6. No load-Full load, constant input voltage.
- \*7. 3.3, 5V model: Constant current limit and hiccup with automatic recovery.
  - 12 48V model: Constant current limit with automatic recovery.

Avoid to operate at over load or short circuit condition for more than 30seconds.

- \*8. OVP circuit will shut down output, manual reset (Re power on).
- \*9. Measured by the each measuring method of UL, CSA, EN and DENAN(at 60Hz), Ta=25°C.
- \*10. As for Remote control mode, refer to Fig. B.
- \*11. Output Derating
  - Derating at standard mounting. Refer to output derating curve(A250-01-02\_).
  - When forced air cooling, refer to output derating curve(A250-01-03).
  - Load (%) is percent of maximum output power or maximum output current, whichever is greater.





The control mode is shown below.

The control mode is shown below.					
+R & R terminal condition	Output condition				
SW ON (Higher than 4.5V)	ON				
SW OFF (Lower than 0.8V)	OFF				

External voltage level : E	External resistance : R		
4.5 ~ 12.5VDC	No required		
12.5 ~ 24.5VDC	1.5kΩ		