## SPECIFICATIONS (1/2)

FA012-01-01/P

ITEMS	MODEL		ZWS15C-5/P	ZWS15C-12/P	ZWS15C-15/P	ZWS15C-24/P	
INPUT							
Input Voltage Range (*2) -				85 - 265VAC	C (47 ~ 63Hz)		
Efficiency (Typ.) (*1)		%	76 / 78	80 / 83	81 / 84	82 / 85	
Input Current (Typ.) (*1)		A	0.34 / 0.17		0.34 / 0.24	I.	
Inrush Current (Typ.) (*1)(*3)		-	30A / 60A at Cold Start				
PFHC		_	-				
Power Factor (Typ.)		_			-		
OUTPUT							
Nominal Output Voltage		V	5	12	15	24	
Output Voltage Range		_	-	ent condition: 5V: ±2			
Maximum Output Current 100VAC		A	Tixed (Shiphi	1.30	1.00	0.70	
200VAC		А	3.00	1.70	1.35	0.85	
Maximum Output Power 100VAC		***		15.6	15.0	16.8	
		W 15.0	15.0	20.4	20.3	20.4	
200VAC			0.40				
Maximum Line Regulation (*4)(*5)		%	0.40	0.40	0.40	0.40	
Maximum Load Regulation (*4)(*6)		%	0.80	0.80	0.80	0.63	
Temperature Coefficient (*4)		-	Less than 0.02% / °C			1	
	a≤70°C, 35 ~ 100% Load		120	150	150	150	
• •	Γa<0°C, 35 ~ 100% Load		160	180	180	180	
` ′	Ta≤70°C, 0 ~ 35% Load	mV	200	240	240	240	
Hold-up Time (Typ.) (*10)		-	20ms				
Leakage Current (*9)		-	Less than 0.15/0.30mA. (100VAC/230VAC, 60Hz)				
Over Current Protection (*7)		-	> 105%				
Over Voltage Protection (*8)		-	> 115% > 112%				
FUNCTION							
Remote ON/OFF Cor	ntrol	-		No	one		
Remote Sensing		-	None				
Parallel Operation		_	Not Possible				
Series Operation		_	Possible				
ENVIRONMENT							
Operating Temperature (*11)		-	-10 to +70°C (-10 to +50°C : 100% ; +60°C : 75% ; +70°C : 50%)				
Storage Temperature		-	-30 to +75°C				
Operating Humidity		_	30 to 90%RH (No Condensing)				
Storage Humidity		-	10 to 95%RH (No Condensing)				
Vibration (*12)			At no operating, 10 to 55Hz (Sweep for 1min)				
( 12)		_	19.6m/s <sup>2</sup> Constant, X,Y,Z 1hour each.				
Shock (*12)							
Shock (*12) Cooling		-	At no operating, Less than 196.1m/s <sup>2</sup> Convection Cooling / Forced Air Cooling				
ISOLATION		-		Convection Cooling	, I ofect All Cooling		
	a of Drotostic:			Class I (I NEC)	or Class II (I. M)		
Isolation Class / Class of Protection		-	Class I (L,N,FG) or Class II (L,N)				
Withstand Voltage		-	Input - Output : 3kVAC (10mA), Input - FG : 2kVAC (10mA),				
T 1 1 7 7	T. Leis D. Lei			Output - FG : 750VAC (20mA) for 1min  More than 100MΩ at 25°C and 70%RH Output - FG : 500VDC			
Isolation Resistance	N. L. N.CE	-	More than	100MI2 at 25°C and	/0%KH Output - FG	: 500 V D C	
STANDARD AND COMP	LIANCE	-			20.1.772.4.00.4.4.4.4.4.4.4.4.4.4.4.4.4.4.4.4.4	1 1000	
Safety		-	Approved by EN60335-1, IEC/UL/CSA/EN62368-1 (Atitude ≤4,000m)				
			Approved by IEC/EN61558-1, IEC/EN61558-2-16 (Atitude ≤ 2,000m)				
				Design to mee			
			Den-an appendix 12 (J62368-1, J61558-1, J61558-2-16, J60335-1)				
Conducted Emission (*12)		-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B				
Radiated Emission (*12)		-	Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B				
Immunity (*12)			Designed to meet IEC61000-6-2, IEC61000-4-2, -3, -4, -5, -6, -8, -11				
MECHANICAL							
VILCHANICAL							
Weight (Typ.)		g		4	7		

## SPECIFICATIONS (2/2)

\*Read instruction manual carefully, before using the power supply unit.

## =NOTES=

- \*1. At 100VAC/200VAC, Ta=25°C, nominal output voltage and maximum output power.
- \*2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100-240Vac (50-60Hz).
- \*3. Not applicable for the inrush current to noise filter for less than 0.2ms.
- \*4. Please refer to Fig.A for measurement of Vo, Line&Load regulation and ripple voltage.
- \*5. 85 265VAC, constant load.
- \*6. No load to full load, constant input voltage.
- \*7. Current limiting (Hiccup) with automatic recovery.

  Avoid to operate at over load or short circuit condition.
- \*8. Over voltage clamping by zener diode.
- \*9. Measured by the each measuring method of UL, CSA, EN and DENAN (at 60Hz), Ta=25°C.
- \*10. At 100VAC, Ta=25°C, nominal output voltage and 80% output power.
- \*11. Output Deratings,
  - Convection cooling output derating. Refer to OUTPUT DERATING vs. AMBIENT TEMPERATURE (FA012-01-02 ).
  - Forced air cooling output derating. Refer to OUTPUT DERATING vs. AMBIENT TEMPERATURE (FA012-01-03\_).

Load (%) is persent of maximum output power or maximum output current, whichever is greater.

It must not exceed its specification and derating.

\*12. The result is evaluated by TDK-Lambda standard measurement condition.

The power supply is considered a component which will be installed into a final equipment.

The final equipment should be re-evaluated that it meets EMC, Vibration and Shock directives.

Fig. A

